



# MASTER Actinic BL TL-D(-K) - the most effective way to eliminate insects

## MASTER Actinic BL TL-D

The Philips MASTER Actinic BL TL-D(-K) family is an ideal choice for insect traps. These lamps have the perfect spectrum for attracting insects. Also, they have virtually no UV-B output, and so are perfectly safe. Furthermore, they have the special "MASTER" coating to improve the efficiency, initial UV-A output and maintenance of the lamp. What's more, with the lowest mercury content in the industry and being 100% lead-free, combined with their high efficiency, these lamps represent the best choice for the environment. Optionally, for extra safety you can apply a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements.

### Benefits

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Safe for use
- Good environmental choice
- Good environmental choice
- High UV-A output during entire season
- High UV-A output during entire season

# MASTER Actinic BL TL-D

## Features

- Emits long-wave UV-A radiation in the 350–400nm range
- Emits long-wave UV-A radiation in the 350–400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280–315nm)
- UV-B/UV-A ratio less than 0.1 % (UV-B 280–315nm)
- 100% lead-free
- 100% lead-free
- Low mercury content
- Low mercury content
- Special maintenance coating
- Special maintenance coating

## Application

- Insect traps, Electronic Fly Killers (EFKs)
- Insect traps, Electronic Fly Killers (EFKs)

## Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Versions



XPPR XUBTLD 0001

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER Actinic BL TL-D 15W/10 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
MASTER Actinic BL TL-D 18W/10 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

# MASTER Actinic BL TL-D

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Actinic
Color Code	10
Mechanical and Housing	
Bulb Shape	T26
Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg

## Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928022601003	MASTER Actinic BL TL-D 15W/10 1SL/25	0.335 A	15.9 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928044601003	MASTER Actinic BL TL-D 18W/10 1SL/25	0.36 A	18 W

