



Product Description

Actinic BL TL(-K) / TL-D(-K)

Tubular low-pressure mercury vapour fluorescent lamps

Benefits

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- Design freedom

Features

- Emit long-wave UV-A radiation in the 350 – 400 nm range
- UV-B/UV-A ratio less than 0.1% (UV-B: 280 – 315 nm)
- R (Reflector) lamps have a 200° internal reflector

Application

- Photopolymerisation processes
- Reprography
- Insect traps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Versions



XPPR_XUVATLRS_10_10-R_G13-
Product photo

Actinic BL TL(-K) / TL-D(-K)

Dimensional drawing



Product	D (max)	A (max)	B	C (max)
Actinic BL TL 40W/10 SLV/25	37.25 mm	1,198.4 mm	1,205.4 mm	1,212.4 mm

