



Product Description

Actinic BL TL(-K) / TL-D(-K)

Tubular low-pressure mercury vapour fluorescent lamps

Benefits

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Safe for use
- Good environmental choice
- Good environmental choice
- Design freedom
- Design freedom

Features

- Emits long-wave UV-A radiation in the 350-400nm range
- Emit long-wave UV-A radiation in the 350 - 400 nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280-315nm)
- UV-B/UV-A ratio less than 0.1% (UV-B: 280 - 315 nm)
- 100% lead-free
- R (Reflector) lamps have a 200° internal reflector
- Low mercury content
- Wide power range

Application

- Insect traps, Electronic Fly Killers (EFKs)
- Photopolymerisation processes
- Reprography
- Insect traps

Actinic BL TL(-K) / TL-D(-K)

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



Actinic BL TL-D 15W/10 1SL/25

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 18W/10 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

