


1 x TLED 26W 4000K 9290043073

1 x 3900 lm

Polar intensity diagram




Light output ratio 1.00
 Service upward 0.27
 Service downward 0.73

CIE flux code 35 62 84 73 100

UGRcen (4Hx8H, 0.25H) 21

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80		0.70		0.50		0.30		0.10		0.00	
	0.80	0.70	0.70	0.50	0.50	0.30	0.30	0.10	0.10	0.10	0.10	0.00
0.60	0.40	0.38	0.38	0.37	0.36	0.29	0.27	0.22	0.24	0.20	0.17	
0.80	0.49	0.46	0.47	0.45	0.44	0.36	0.33	0.28	0.31	0.26	0.22	
1.00	0.57	0.53	0.54	0.52	0.50	0.43	0.39	0.34	0.36	0.31	0.26	
1.25	0.65	0.59	0.61	0.59	0.57	0.49	0.45	0.40	0.41	0.37	0.31	
1.50	0.71	0.64	0.67	0.64	0.61	0.54	0.50	0.45	0.45	0.41	0.34	
2.00	0.80	0.72	0.75	0.72	0.68	0.62	0.57	0.52	0.52	0.48	0.41	
2.50	0.87	0.76	0.81	0.77	0.73	0.67	0.62	0.57	0.56	0.53	0.45	
3.00	0.91	0.80	0.86	0.81	0.76	0.71	0.65	0.61	0.60	0.56	0.48	
4.00	0.98	0.85	0.92	0.86	0.81	0.76	0.70	0.67	0.64	0.61	0.53	
5.00	1.02	0.88	0.96	0.89	0.84	0.80	0.73	0.70	0.67	0.65	0.56	

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	4344	4303	4549	5202	6596	10281	31974
50.0	3965	3895	4086	4640	5818	9043	30671
55.0	3649	3553	3695	4160	5131	7893	29096
60.0	3381	3264	3362	3750	4521	6814	27164
65.0	3152	3016	3077	3399	3974	5791	24726
70.0	2955	2802	2831	3094	3479	4816	21595
75.0	2782	2616	2619	2832	3033	3889	17429
80.0	2631	2455	2435	2606	2640	3045	12007
85.0	2499	2315	2278	2416	2322	2369	5575
90.0	2382	2194	2144	2255	2118	2026	1286

(cd/m²)