





Clear LED lustre adds comfort sparkle to your home

Experience warm white LED light

Sustainable choice

- · Lasts up to 15 years
- Very low energy consumption; saving at least 80%

Create a warm atmosphere

• True incandescent-like warm white light (2700 K)

Instant light (LED)

· Instant light when switched on

Highlights

Lasts up to 15 years

With a lifetime of up to 15.000 hours, this Philips LED lamp will ensure your desired atmosphere for up to 15 years.*

Very low energy consumption



When you switch to a Philips LED light bulb, you immediately use up to 80% less energy without sacrificing light output and quality.

Warm white light (2700K)

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

Instant light when switched on

No need to wait: Philips LED light bulbs provide their full level of brightness immediately upon switching on.

Specifications

Bulb characteristics

· Shape: Luster

· Lamp shape: Non directional luster

· Socket: E14

Type of glass: Clear
Lamp shape code: P45
Bulb Finish: Clear
Dimmable: No

Bulb dimensions

Height: 8.8 cmWidth: 4.5 cm

Durability

Number of switch cycles: 50,000Nominal lifetime: 15,000 hour(s)

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

· Color rendering index (CRI): 80

· Color temperature: 2700 K

· Nominal luminous flux: 250 lm

 Warm-up time to 60% light: instant full light

Miscellaneous

EveComfort: Yes

· LED Innovations: EyeComfort

Packaging information

• Product family: EyeComfort

Power consumption

Power factor: 0.4Voltage: 220-240 V

Wattage: 4 W

· Wattage equivalent: 25 W

Product dimensions and weight

· Length: 8.8 cm

Technical specifications

• Frequency: 50-60 Hz

Packaging dimensions and weight

• EAN/UPC - product: 8718696475225

Net weight: 0.04 kgGross weight: 0.05 kgHeight: 12.6 cm

- Length: 4.6 cmWidth: 4.6 cm
- Material number (12NC): 929001142307



Issue date: 2024-07-07 Version: 0.708 © 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V