


MAG L FLOOD 7W 600LM 1 x 9290032069 4000K


1 x 600 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00

CIE flux code 61 89 98 100 100


UGRcen (4Hx8H, 0.25H) 24

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80				0.70				0.50			
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00

0.60	0.57	0.54	0.56	0.55	0.54	0.47	0.47	0.43	0.46	0.42	0.41	
0.80	0.68	0.63	0.67	0.65	0.63	0.56	0.56	0.51	0.55	0.51	0.49	
1.00	0.76	0.71	0.75	0.72	0.70	0.64	0.63	0.59	0.62	0.59	0.57	
1.25	0.84	0.77	0.83	0.80	0.77	0.71	0.70	0.66	0.69	0.66	0.64	
1.50	0.90	0.82	0.88	0.85	0.81	0.76	0.75	0.71	0.74	0.71	0.69	
2.00	0.99	0.89	0.97	0.92	0.88	0.84	0.82	0.79	0.81	0.78	0.76	
2.50	1.05	0.93	1.03	0.97	0.92	0.88	0.87	0.84	0.86	0.83	0.81	
3.00	1.09	0.96	1.06	1.00	0.95	0.92	0.90	0.88	0.89	0.87	0.84	
4.00	1.14	0.99	1.11	1.04	0.98	0.95	0.94	0.92	0.92	0.91	0.88	
5.00	1.17	1.01	1.14	1.06	1.00	0.98	0.96	0.94	0.94	0.93	0.90	

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	27417	27102	26820	26588	26419	26323	26303
50.0	23144	22828	22547	22316	22148	22052	22033
55.0	19249	18935	18657	18430	18265	18172	18153
60.0	16247	15926	15645	15416	15251	15157	15138
65.0	13159	12840	12561	12337	12176	12085	12066
70.0	11197	10852	10555	10318	10150	10055	10036
75.0	9831	9425	9082	8813	8625	8519	8498
80.0	8783	8247	7811	7479	7252	7126	7101
85.0	6359	5633	5100	4725	4482	4353	4327
90.0	2298	467	270	200	167	153	150

(cd/m²)

2022-03-10