


MAG SPOTLIGHT 9.5W 740LM 1 x 9290032083 4000K


1 x 740 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 95 99 100 100 100

UGRcen (4Hx8H, 0.25H) 17

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.82	0.78	0.81	0.79	0.78	0.74	0.74	0.71	0.73	0.71	0.70	0.70
0.80	0.89	0.83	0.88	0.85	0.83	0.79	0.79	0.76	0.78	0.76	0.75	0.75
1.00	0.95	0.88	0.94	0.91	0.88	0.84	0.84	0.81	0.83	0.81	0.80	0.80
1.25	1.00	0.92	0.99	0.95	0.91	0.88	0.88	0.85	0.87	0.85	0.84	0.84
1.50	1.04	0.95	1.03	0.98	0.94	0.91	0.90	0.88	0.90	0.88	0.86	0.86
2.00	1.11	0.99	1.09	1.03	0.98	0.96	0.95	0.94	0.94	0.93	0.91	0.91
2.50	1.15	1.02	1.13	1.07	1.01	0.99	0.98	0.97	0.97	0.96	0.94	0.94
3.00	1.18	1.04	1.16	1.09	1.03	1.02	1.00	0.99	0.99	0.98	0.96	0.96
4.00	1.22	1.06	1.19	1.11	1.05	1.04	1.02	1.02	1.01	1.00	0.98	0.98
5.00	1.24	1.07	1.20	1.13	1.06	1.05	1.03	1.03	1.02	1.01	0.99	0.99

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	42781	42781	42781	42781	42781	42781	42781
50.0	32523	32523	32523	32523	32523	32523	32523
55.0	22149	22149	22149	22149	22149	22149	22149
60.0	12315	12315	12315	12315	12315	12315	12315
65.0	8371	8371	8371	8371	8371	8371	8371
70.0	5083	5083	5083	5083	5083	5083	5083
75.0	1859	1859	1859	1859	1859	1859	1859
80.0	0	0	0	0	0	0	0
85.0	0	0	0	0	0	0	0
90.0	0	0	0	0	0	0	0

(cd/m²)

2022-03-10