

- Do not stare into LED light beam.
- The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
- The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.
- Above average concentration of sulfur effects the useful lifetime of the product. E.g. Light color changes from white to blue. Typically in chicken & pig farms.
- For use in environments where an accumulation of conductive dust on the luminaire may be expected.

- Do not install the luminaire on the location where it is exposed to heavily grease, esp. mineral oil and distillates (petroleum), heavy naphthenic treated with hydrogen.

- This product is not suitable for cold & humid storage areas, especially where obvious temperature gradients are present, such as ventilation opening, door, etc.

- Do not install the luminaire on locations where it is exposed to direct sunlight. UV radiation will damage the material over time resulting in loss of waterproof sealing and IP65 rating.

- Do not install the luminaire on the location where it is exposed to (animal) grease, oil, esp. cooking or mineral oil and distillates (petroleum), heavy naphthenic treated with hydrogen, or swimming pool applications (with chlorine present), or carwash (due to chemicals and/or salt presence).



Additional Through wiring options:						
12NC	Description	EOC				
911401816587	WT120Z TW-3x2.5-L600	872016975515499				
911401816787	WT120Z TW-3x2.5-L1200	872016975517899				
911401816987	WT120Z TW-3x2.5-L1500	872016975519299				
911401816687	WT120Z TW-5x2.5-L600	872016975516199				
911401816887	WT120Z TW-5x2.5-L1200	872016975518599				
911401817087	WT120Z TW-5x2.5-L1500	872016975520899				

© 07/2024 Signify Holding.

All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeneess of the information included herein is given and any liability for any action in reliance thereon is disclaimed. The information presented in this document is not intended as any commercial ofer and does not form part of any quotation or contract. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Signify Holding. The Netherlands





				eg	
WT120C G2 LED20S/840 PSU L600	2000	4000	12.8	D	0.8
WT120C G2 LED40S/840 PSU L600	4000	4000	25	С	0.8
WT120C G2 LED60S/840 PSU L1200	6000	4000	37.5	С	1.3
WT120C G2 LED80S/840 PSU L1200	8000	4000	50	С	1.3
WT120C G2 LED100S/840 PSU L1500	10000	4000	62	С	1.73
WT120C G2 LED120S/840 PSU L1500	12000	4000	75	С	1.73
WT120C G2 LED40S/840 PSD L600	4000	4000	25	С	0.83
WT120C G2 LED60S/840 PSD L1200	6000	4000	37.5	С	1.33
WT120C G2 LED80S/840 PSD L1200	8000	4000	50	С	1.33
WT120C G2 LED100S/840 PSD L1500	10000	4000	62	С	1.73
WT120C G2 LED120S/840 PSD L1500	12000	4000	75	С	1.73



Туре	Dimension (mm)				Nr.of					
	А	В	С	D	E min	E max	F	clips		
WT120C G2 L600	76	665			308	512		6		
WT120C G2 E000								10		
WT120C G2 L1200		76 1	76	1215	80	38	538	1062	85	10
			1215	80	30	558	1002	0.5		
WT120C G2 L1500		1515			838	1362		12		



4/4

1/4





