

PHILIPS

Bulb 75W Stick B22

LED

6500K

1050lm

15000h

8718699605377



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- No visible flicker
- Light all around

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

Light all around

Thanks to its innovative but vintage design shape, this LED bulb prevents the shadow that normally appears at the beam spread edge. The result? Natural warm white light all around.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000
- Ambient temperature range: -20 to +45 °C

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 200 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 1050 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 865 | CCT of 6500K
- Correlated Color Temperature (Nom): 6500 K
- Luminous Flux: 1,050 lm
- Luminous Efficacy (rated) (Nom): 110

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699605377
- EOC: 871869960537700
- Product title: LEDStick 9.5W B22 6500K 1PF/6 AU

Power

- Power Factor (Fraction): 0.51

Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage equivalent: 75 W
- Power: 9.5 W
- Energy Consumption kWh/1000 h: 10

Product dimensions and weight

- Overall height: 113 mm
- Overall length: 113 mm
- Overall width: 37.2 mm

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 50–60
- Diameter: 37.2 mm
- Dimmable: No
- Cap-Base: B22

Packaging dimensions and weight

- EAN/UPC - product: 8718699605377
- Net weight: 0.04 kg
- Gross weight: 0.06 kg
- Height: 14.7 cm
- Length: 3.9 cm
- Width: 3.9 cm



Issue date: 2026-02-25
Version: 0.233

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com