

PHILIPS

Bulb 83W A60M
B22

LED

3000K

1020lm

15000h

8718699651732



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

High quality LED light that lasts for decades

- Reduced glare. Increased comfort.

Highlights

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Contains no mercury

EyeComfort with Interlaced optics

Interlaced optics technology enhances the overall lighting experience in your every-day life. Imprinted with 3D patterns to help diffuse light, the micro-lens technology produce an

even distribution of light which reduces glare significantly. This illumination is not only a soft and uniform light which brings more comfort to your eyes, but it also cleverly redistributes light for less glaring illumination in the lit area.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Type of glass: Frosted
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

Bulb dimensions

- Height: 11 cm
- Width: 6 cm

Design and finishing

- Material: Plastic

Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 25,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Nominal luminous flux: 1150 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 930 | CCT of 3000K
- Correlated Color Temperature (Nom): 3000 K
- Luminous Flux: 1,020 lm
- Luminous Efficacy (rated) (Nom): 102 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 115 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699651732
- EOC: 871869965173200
- Product title: LEDBulb 10W B22 930 230V 1PF/6 AU

Power

- Power Factor (Fraction): 0.5

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage: 10 W
- Wattage equivalent: 89 W
- Power Consumption: 10 W

Product dimensions and weight

- Length: 11 cm

Rated values

- Rated lifetime: 15,000 hour(s)

Technical specifications

- Frequency: 50-60 Hz
- Dimmable: No
- Cap-Base: B22

Packaging dimensions and weight

- EAN/UPC - product: 8718699651732
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 13.7 cm
- Length: 6.1 cm
- Width: 6.1 cm
- Material number (12NC):
929003007699



Issue date: 2024-07-25
Version: 0.64

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com