



## Appliance Oven Tubular

Reliable operation when used in special lampholders at high oven temperatures (up to 300°C). Application in electrical and standard ovens, rotisseries and similar places subject to high operating temperatures.

#### Special purpose lighting

• For use in ovens

### Highlights

#### For use in ovens



This Philips appliance bulb is specifically designed for use in ovens, resisting high heat up to 300 degrees Celcius.

### Specifications

#### **Bulb characteristics**

Socket: E14

· Lamp shape code: T25

#### **Durability**

Average life (at 2.7 hrs/day): 1 year(s)

· Nominal lifetime: 1.000

#### **Light characteristics**

 Application: Special application, General light

Color rendering index (CRI): 100
Color temperature: 2700 K
Nominal luminous flux: 172 lm

• Starting time: 0.0 s

#### Luminaire fit

· Shape: T25

#### **Power consumption**

Voltage: 230 - 240 VPower Consumption: 25

• Energy Consumption kWh/1000 h: 25

#### **Technical specifications**

· Lamp holder: E14

· Number of light sources: 2

## Packaging dimensions and weight [App 25W E14 230-240V T25 CL OV 2PF/10]

• EAN/UPC - product: 8718699754693

Net weight: 0.03 kgGross weight: 0.03 kg

Height: 6 cm

Length: 2.6 cmWidth: 5.2 cm

# Packaging dimensions and weight [App 25W E14 230-240V T25 CL OV 2PF/6 SRT]

• EAN/UPC - product: 8718699754693

Net weight: 0.03 kgGross weight: 0.03 kg

Height: 6 cmLength: 2.6 cmWidth: 5.2 cm



Issue date: 2025-11-15 Version: 0.88 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips