

PHILIPS

Bulb 60W A60 B22

LED

6500K

850lm

15000h

8718699773533



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Contains no mercury



No mercury allows for non-hazardous waste disposal, so this characteristic provides a simple way to make your current space more sustainable.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +30 °C
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 280 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 850 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 865 | CCT of 6500K
- Correlated Color Temperature (Nom): 6500
- Luminous Flux: 850 lm
- Luminous Efficacy (rated) (Nom): 106

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699773533
- EOC: 871869977353300
- Product title: LED Sensor 8-60W B22 CDL FR 1PF/6 APR

Power

- Power Factor (Fraction): 0.5

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage equivalent: 60
- Power: 8
- Energy Consumption kWh/1000 h: 8

Product dimensions and weight

- Overall height: 120 mm
- Overall length: 120 mm
- Overall width: 62.5 mm

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 50-60
- Diameter: 62.5 mm
- Bulb technology: LED
- Dimmable: No
- Cap-Base: B22

Packaging dimensions and weight

- EAN/UPC - product: 8718699773533
- Net weight: 0.07 kg
- Gross weight: 0.09 kg
- Height: 14.8 cm
- Length: 6.2 cm
- Width: 6.2 cm



Issue date: 2026-03-21
Version: 0.53

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com