

PHILIPS

Filament Candle
Clear 40W P45 E14

LED

2700K

470lm

15000h

Dimming

8719514377394



Experience dimmable, warm white LED light

Philips LED clear candles provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and off, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

Choose for a sustainable solution

- Saves up to 90% Energy

Create the right light for your home

- Perfect for decorative fixtures

Highlights

Saves up to 90% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen bulbs

Perfect for decorative fixture



Contemporary lighting in Philips LED lustres for use in decorative fixtures such as chandeliers, ceiling fans, vanity strips, and post lights.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: E14
- Bulb Finish: Clear
- Dimmable: Yes
- Bulb Material: Glass

Durability

- Number of switch cycles: 20,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700
- Luminous Flux: 470 lm
- Luminous Efficacy (rated) (Nom): 134

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514377394
- EOC: 871951437739400
- Product title: LEDclassic 40W P45 2700K E14 D CL AU

Power

- Power Factor (Fraction): 0.6

Power consumption

- Power factor: 0.6
- Voltage: 220–240 V
- Wattage equivalent: 40
- Power: 3.5
- Energy Consumption kWh/1000 h: 4

Product dimensions and weight

- Overall height: 80 mm
- Overall length: 80 mm
- Overall width: 45 mm

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 50–60
- Diameter: 45 mm
- Bulb technology: LED
- Dimmable: Only with specific dimmers
- Cap-Base: E14

Packaging dimensions and weight

- EAN/UPC – product: 8719514377394
- Net weight: 0.01 kg
- Gross weight: 0.03 kg
- Height: 10.1 cm
- Length: 5.5 cm
- Width: 5.5 cm



Issue date: 2026-03-21
Version: 0.53

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com