



# Experience dimmable, warm white LED light

Philips LED clear candles provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and off, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

# Choose for a sustainable solution

· Saves up to 90% Energy

# Create the right light for your home

· Perfect for decorative fixtures

# Highlights

### Saves up to 90% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen bulbs

#### Perfect for decorative fixture



Contemporary lighting in Philips LED lustres for use in decorative fixtures such as chandeliers, ceiling fans, vanity strips, and post lights.

# Specifications

#### **Bulb characteristics**

· Intended use: Indoor

· Lamp shape: Non directional luster

Socket: B15Dimmable: YesBulb Finish: ClearBulb Material: Glass

#### **Durability**

• Number of switch cycles: 20,000

• Nominal lifetime: 15,000

• Ambient temperature range: -20 to +45 °C

#### **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## **Light characteristics**

· Color rendering index (CRI): 90

· Color temperature: 2700 K

· Nominal luminous flux: 470 lm

· Warm-up time to 60% light: 0.5 s

· Color Code: 927 | CCT of 2700K

Correlated Color Temperature (Nom):
 2700 K

• Luminous Flux: 470 lm

Luminous Efficacy (rated) (Nom): 134

#### Miscellaneous

EveComfort: Yes

· LED Innovations: EyeComfort

• Extra Features: Dimmable

#### Other characteristics

• EU RoHS compliant: Yes

# Packaging information

• EAN: 8719514377455

• EOC: 871951437745500

 Product title: LEDclassic 40W P45 2700K B15 D CL AU

#### **Power**

• Power Factor (Fraction): 0.6

#### **Power consumption**

Power factor: 0.6Voltage: 220-240 V

· Wattage equivalent: 40 W

• Power: 3.5 W

• Energy Consumption kWh/1000 h: 4

#### Product dimensions and weight

Overall height: 79 mmOverall length: 79 mmOverall width: 45 mm

#### **Rated values**

· Rated lifetime: 15,000

# **Technical specifications**

Frequency: 50-60Diameter: 45 mm

• Dimmable: Only with specific

dimmers
• Cap-Base: B15

#### Packaging dimensions and weight

• EAN/UPC - product: 8719514377455

Net weight: 0.01 kgGross weight: 0.03 kgHeight: 10.1 cm

Length: 5.5 cmWidth: 5.5 cm



Issue date: 2025-12-13 Version: 0.53

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips