

PHILIPS

Bulb 40W A60 E27
x8

LED

3000K

470lm

10000h

8721103093622



State-of-the-art LED light bulb for the home

Philips LED light bulbs provide a beautiful, warm white light, a long lifetime, and immediate, significant energy savings. With its modern and elegant design, this dimmable bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- No visible flicker

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

Replaces standard incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect

sustainable replacement for traditional standard incandescent bulbs.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

Bulb dimensions

- Height: 10.7 cm
- Width: 6 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 10,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 180 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 470 lm

Miscellaneous

- EyeComfort: No

Other characteristics

- Efficacy: 95 lm/W

Packaging information

- EAN: 8721103093622
- EOC: 872110309362200
- Product title: ESS LEDBulb 4.9W E27 3000K ND 8CT/5 AU

Power consumption

- Power factor: 0.54
- Voltage: AC 220-240 V
- Wattage: 4.9 W
- Wattage equivalent: 40 W

Product dimensions and weight

- Length: 10.7 cm

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8721103093622
- Net weight: 0.24 kg
- Gross weight: 0.3 kg
- Height: 16.6 cm
- Length: 6.2 cm
- Width: 24.4 cm



Issue date: 2025-05-27
Version: 0.84

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com