



State-of-the-art LED for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

No visible flicker

Create the right light for your home

 $\boldsymbol{\cdot}$ A simple LED for everyday use

Light beyond illumination

· Instant on

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response

to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

Instant on

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non directional luster

Socket: E27Dimmable: NoBulb Finish: FrostedBulb Material: Plastic

Durability

Number of switch cycles: 50,000

· Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

Beam angle: 150 degree(s)

Color rendering index (CRI): 80

· Color temperature: 3000 K

· Nominal luminous flux: 339 lm

• Warm-up time to 60% light: instant

tull light

Color Code: 830 | CCT of 3000K
Luminous Efficacy (rated) (Nom): 113 lm/W

Miscellaneous

EyeComfort: No

Packaging information

• EAN: 8719514451650

• EOC: 871951445165000

 Product title: ESSLEDBulb 3W E27 3000K 230V P45 PH

Power consumption

· Power factor: 0.41

• Voltage: AC 220-240 V

· Wattage equivalent: 40 W

• Power Consumption: 3 W

Product dimensions and weight

• Overall height: 87 mm

• Overall length: 87 mm

· Overall width: 45 mm

Technical specifications

• Frequency: 50-60

Packaging dimensions and weight

• EAN/UPC - product: 8719514451650

· Net weight: 0.02 kg

· Gross weight: 0.03 kg

· Height: 8.8 cm

· Length: 4.7 cm

• Width: 4.7 cm



Issue date: 2025-08-30 Version: 0.122

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not