PHILIPS

Fortimo

LED

Fortimo LED Strip 1ft LF 8xx HV6

Datasheet

The Fortimo LED Strip is a uniquely wide portfolio which can be used in all kind of linear indoor luminaire types. Its form factor makes it easy to design-in and handle in production as it complies to Zhaga standards. Due to the availability from 0.25ft up to 5ft lengths only one product family is needed to cover a wide range of needs.

Key features and benefits

- Typical module efficiency of 186 Lm/W (at 4000K CRI80)
- CRI90 High Efficiency typical performance of 174 Lm/W (at 4000K CRI90)
- Long life-time: >72,000 hours
- Excellent color consistency of 3 SDCM
- Two lumen packages per length available: LF (650 lm/ft) and MF (1100 lm/ft)
- Wide range of CCTs available: 2700K, 3000K, 3500K, 4000K, 5000K and 6500K
- Available in High Voltage (HV) and Low Voltage (LV)
- Options in front connector (FC) or back connector (BC)
- Small LED module width of only 20mm
- Available lengths: 0.25ft / 0.5ft / 1ft / 2ft / 4ft (1120mm) / 4ft extended (1150mm) / 5ft (1400mm) / 5ft extended 1450mm)
- Wide temperature (Tc) range -40°C to +80°C
- Five year system warranty

March 2023



Ordering data

Commercial product name	EOC	12NC	EPREL registration #	Box quantity
Fortimo LED Strip 1ft LF 830 FC HV6	8719514 486942 00	9290 029 40406	1413390	110
Fortimo LED Strip 1ft LF 840 FC HV6	8719514 486966 00	9290 029 40506	1413391	110

Drive currents

Parameter	Nominal*	Life**	Max***	Unit
Fortimo LED Strip 1ft LF 8xx HV6	90	240	240	mA

Module temperatures

Parameter	Nominal*	Life**	Max***	Unit
T_c (case temperature at T_c point)	45	75	85	°C

* Nominal value at which typical performance is specified

** Value at which life time is specified

*** Maximum value for safe operation, do not operate above this value

Optical characteristics - table per color (CCT)

Fortimo LED Strip 1ft LF 830 FC HV6

Parameter	Min	Typ	Max	Unit
Luminous flux	590	610	650	lm
Efficacy	166	175	197	lm/W
Correlated color temperature (CCT)		3000		K
Color coordinates (CIEx, CIEy)		(0.433, 0.400)		-
Color consistency			3	SDCM
CRI	80			
R9	0			
Photometric code		830/339		
Photobiological safety			RG1 unlimited	

Measurement precision ± 5% for the flux data and ± 6% for the efficacy data. Measurement precision for color coordinates ± 0.005. Measurement precision for CRI ± 1.5.

Operation point	830	lm	lm/W
80% I-nom 72mA	Tc 25 °C	507	182
	Tc-nom 45 °C	494	179
	Tc-max 85 °C	465	171
I-nom 90mA	Tc 25 °C	626	178
	Tc-nom 45 °C	610	175
	Tc-max 85 °C	573	167
I-max 240mA	Tc 25 °C	1537	154
	Tc-nom 45 °C	1498	151
	Tc-max 85 °C	1405	144



Fortimo LED Strip 1ft LF 840 FC HV6

Parameter	Min	Typ	Max	Unit
Luminous flux	630	650	720	lm
Efficacy	178	187	219	lm/W
Correlated color temperature (CCT)		4000		K
Color coordinates (CIEx, CIEy)		(0.381, 0.377)		-
Color consistency			3	SDCM
CRI	80			
R9	0			
Photometric code		840/339		
Photobiological safety			RG1 unlimited	

Measurement precision ± 5% for the flux data and ± 6% for the efficacy data. Measurement precision for color coordinates ± 0.005. Measurement precision for CRI ± 1.5.

Operation point	840	lm	lm/W
80% I-nom 72mA	Tc 25 °C	540	194
	Tc-nom 45 °C	526	191
	Tc-max 85 °C	494	182
I-nom 90mA	Tc 25 °C	667	190
	Tc-nom 45 °C	650	187
	Tc-max 85 °C	610	178
I-max 240mA	Tc 25 °C	1647	165
	Tc-nom 45 °C	1603	161
	Tc-max 85 °C	1503	153



Electrical characteristics

Parameter	Min	Typ	Max	Unit
Forward voltage	36.6	38.7	39.4	V
Power consumption	3.3	3.5	3.5	W = kWh/1000h
Number of modules in series per chain			8	
Number of modules in parallel			4	

Measurement precision for Vf +/- 3%. Measurement precision for power +/- 3.3%

Tuning information

Flux and efficacy versus current (at Tc nominal)

I [mA]	Flux [%]	Efficacy [%]
240	246	86
165	175	92
90	100	100
72	81	102
45	52	106



Flux and efficacy versus temperature at Tc (at I nominal)

Tc [°C]	Flux [%]	Efficacy [%]
85	94	95
45	100	100
25	103	102
0	105	104



Lumen maintenance

Operation point	Lumen maintenance	L70			L80			L90		
	x 1000 hours	B50	B20	B10	B50	B20	B10	B50	B20	B10
80% Inom=72mA	Tc=25°C	>72	>72	>72	>72	>72	>72	>68	>68	>68
	Tc_nom=45°C	>72	>72	>72	>72	>72	>72	>68	66	64
	Tc_life=75°C	>72	>72	>72	>72	>72	>72	47	45	44
Inom=90mA	Tc=25°C	>72	>72	>72	>72	>72	>72	>68	>68	>68
	Tc_nom=45°C	>72	>72	>72	>72	>72	>72	>68	64	62
	Tc_life=75°C	>72	>72	>72	>72	>72	>72	47	45	44
Ilife=240mA	Tc=25°C	>72	>72	>72	>72	>72	>72	>41	>41	>41
	Tc_nom=45°C	>72	>72	>72	>72	>72	>72	>41	>41	>41
	Tc_life=75°C	>72	>72	>72	>72	>72	>72	41	39	38

Lifetime

Parameter	Value	Unit
M70F50 nominal	>72000	hours
M70F50 life	>72000	hours

Performance Window



Wiring

Specification item	Value	Unit	Condition
Input wire cross-section	0.25…0.75	mm^2	solid wire
	18…24	AWG	solid wire
Input wire strip length	7.5…8.5	mm	
Input wire cross-section	0.33…0.5	mm^2	stranded wire
	20…22	AWG	stranded wire
Input wire strip length	7.5…8.5	mm	

Mechanical characteristics

Parameter	Min	Typ	Max	Unit
Length	279	279.2	279.8	mm
Width	19.8	20	20.2	mm
Height PCB	1.45	1.6	1.75	mm
Height Total		4.3		mm
Product mass		17.4		gram



Absolute ratings

Parameter	Min	Max	Unit
Current through the LED module (I-max)		240	mA
Case temperature (Tc-max)		85	°C
ESD (direct contact)	8		kV
Working voltage		350	V_{dc}

Application information

Certificates and Standards
CE
ENEC
ENEC+

Environmental
RoHS/REACH

Application	
Dimming	Yes

© 2023 Signify Holding, IBRS 10461, 5600VB, NL. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.
UK importer address: Signify Commercial UK Limited, 3 Guildford Business Park, GU2 8XG

02/03/2023

www.philips.com/oem