



Deep Recessed Spot 1 x 9290032242 3000K

1 x 540 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.00
Service downward 1.00

CIE flux code 100 100 100 100 100

EN12464-1 55 deg, 200 cd/m²
CIBSE: LG3 55 deg, 200 cd/m²
DIN 5035/7: BAP60

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)									
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30
0.60	0.86	0.81	0.85	0.83	0.81	0.78	0.78	0.75	0.77	0.75
0.80	0.92	0.86	0.91	0.88	0.86	0.83	0.82	0.80	0.82	0.80
1.00	0.98	0.91	0.96	0.93	0.90	0.87	0.87	0.85	0.86	0.84
1.25	1.03	0.94	1.01	0.97	0.94	0.91	0.90	0.88	0.89	0.88
1.50	1.06	0.97	1.05	1.00	0.96	0.93	0.93	0.91	0.92	0.90
2.00	1.13	1.00	1.10	1.05	1.00	0.98	0.97	0.95	0.96	0.95
2.50	1.17	1.03	1.14	1.08	1.02	1.01	1.00	0.99	0.98	0.98
3.00	1.20	1.05	1.17	1.10	1.04	1.03	1.02	1.01	1.00	1.00
4.00	1.23	1.06	1.20	1.12	1.05	1.05	1.03	1.03	1.02	1.01
5.00	1.25	1.07	1.21	1.13	1.06	1.06	1.04	1.04	1.03	1.03

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	524	524	524	524	524	524	524
50.0	232	232	232	232	232	232	232
55.0	152	152	152	152	152	152	152
60.0	35	35	35	35	35	35	35
65.0	0	0	0	0	0	0	0
70.0	0	0	0	0	0	0	0
75.0	0	0	0	0	0	0	0
80.0	0	0	0	0	0	0	0
85.0	0	0	0	0	0	0	0
90.0	0	0	0	0	0	0	0

(cd/m²)

2022-12-27