

PHILIPS

Reflector

Halogen

50W

GU10

Sparkling light

Dimmable



046677415792



Brilliant alternative to incandescents

Philips 35W dimmable indoor halogen mini reflector flood provides bright sparkling accent light. An efficient alternative to 35W incandescents, it has no mercury, can last up to 1.8 years* and has an estimated yearly energy cost of \$6.02**.

Easy to use

- Dimmable
- Instant On

Sparkling light

- Bright alternative to incandescent

Highlights

Dimmable

This bulb can be used with most dimmers to create your desired ambience.

Alternative to incandescent

This halogen light bulb provides a bright, sparkling light, ideal for adding brilliance and drama to your home.

Instant On



Just by turning the switch, the light is at full brightness. No slow starting or waiting.

Specifications

Bulb characteristics

- Shape: Mini Reflector Flood
- Socket: GU10
- Base: GU10
- Lamp shape code: TWISTLINE
- Dimmable: Yes
- Bulb Finish: Clear

Bulb dimensions

- Height: 2 inch
- Width: 2 inch

Durability

- Average life (at 2.7 hrs/day): 1.8 year(s)
- Nominal lifetime: 2,000

Light characteristics

- Application: Accent light
- Color rendering index (CRI): 100
- Color temperature: 2800 K
- Light Color Category: Clear
- Nominal luminous flux: 430 lm
- Correlated Color Temperature (Nom): 2800 K

Power consumption

- Voltage: 120 V
- Power Consumption: 50

Rated values

- Rated lifetime: 2,000

Technical specifications

- Dimmable: Yes
- Cap-Base: GU10



Issue date: 2025-08-30
Version: 0.606

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com