

# PHILIPS

Incandescent bulb


Incandescent reflector  
lamp

60 W


E27 cap

Low voltage

Clear



8711500090188



## Brilliantly clear light wherever you need it


Philips low voltage incandescent bulbs are suited for remote, isolated areas where mains power is not available and energy has to be supplied by private generating plants, batteries or other low voltage sources.

### Special purpose lighting

- For specific applications

# Highlights

## For specific applications



Philips special purpose incandescent light bulbs are meant to be used for specific applications. Light bulbs for general home lighting are available in the Philips halogen, energy-saving, and LED ranges.

# Specifications

## Bulb characteristics

- Shape: Standard
- Socket: E27
- Bulb Finish: Clear
- Dimmable: Yes

## Bulb dimensions

- Height: 4-1/4 inch
- Width: 2-3/8 inch

## Durability

- Average life (at 2.7 hrs/day): 1 year(s)
- Number of switch cycles: 4,000
- Nominal lifetime: 1,000

## Light characteristics

- Application: Special application
- Color rendering index (CRI): 100
- Warm-up time to 60% light: instant full light s
- Correlated Color Temperature (Nom): 2700
- Luminous Flux: 970 lm

## Power consumption

- Voltage: 24 V
- Power Consumption: 60.0
- Energy Consumption kWh/1000 h: 60

## Rated values

- Rated lifetime: 1,000

## Technical specifications

- Dimmable: Yes
- Cap-Base: E27



Issue date: 2025-08-30  
Version: 0.803

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)