





Dimming



Experience dimmable, warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

Choose for a sustainable solution

· Saves up to 90% Energy

Create the right light for your home

· Perfect for general room lighting

Highlights

Saves up to 90% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen bulbs

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non directional bulb

Socket: E27

· Bulb Finish: Clear

· Dimmable: Yes

· Bulb Material: Glass

Durability

• Number of switch cycles: 20,000

· Nominal lifetime: 15,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

· Color rendering index (CRI): 90

· Color temperature: 2200-2700 K

· Nominal luminous flux: 806 lm

· Warm-up time to 60% light: 0.5

· Color Code: 922-927 | CCT of

2200K-2700K

· Luminous Efficacy (rated) (Nom): 136 lm/W

Miscellaneous

EveComfort: Yes

· LED Innovations: EyeComfort

· Extra Features: Dimmable,

WarmGlow

Packaging information

. EAN: 8719514323919

• EOC: 871951432391900

· Product title: LED classic 60W ST64

E27 CL WGD90 SRT4

Power consumption

• Power factor: 0.6

· Voltage: 220-240 V

· Wattage equivalent: 60 W

· Energy Efficiency Label (EEL): D

Power Consumption: 5.9 W

· Energy Consumption kWh/1000 h: 6

Product dimensions and weight

· Overall height: 140 mm

· Overall length: 140 mm

· Overall width: 64 mm

Technical specifications

• Frequency: 50-60

• EPREL Registration Number: 453250

Packaging dimensions and weight

• EAN/UPC - product: 8719514323919

Net weight: 0.04 kgGross weight: 0.07 kg

Height: 17.7 cmLength: 7 cmWidth: 7.5 cm



Issue date: 2025-09-13 Version: 0.438 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.