

PHILIPS


Recessed panel

ProjectLine

60x60 cm

4000K natural white light

3200 lm



Professional quality for your project

Reliable, energy efficient, recessed light, professional LED panels. ProjectLine LED panel support energy saving and fits standard sized visible profile ceilings, used in office and (commercial) working locations with its high natural white light.

Sustainable choice

- Save energy from the moment you turn the switch

Choose for high quality light

- You can trust what the Philips packaging is saying

Durability

- Long life span up to 35,000 hours

Highlights

Energy efficient

All Philips energy savers save energy from the moment you turn the switch. During their lifetime they use fewer kW and thus also result in a lower energy bill. The level of energy saving differs per lamp type and technology.

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Long life span up to 35,000 hours

Philips LED technology extends your product's lifetime up to 35,000 hours.

Specifications

Design and finishing

- Color: White
- Material: Metal
- Optical cover finish: Opal
- Optical cover material: Acrylate

Durability

- Ambient temperature range: -10 to +35 °C

Light characteristics

- Color rendering index (CRI): 80
- Luminous flux tolerance: +/-10%
- Color Code: 840 neutral white
- Constant light output: No
- Correlated Color Temperature (Nom): 4000
- Initial chromaticity: (0.3818, 0.3797) SDCM≤5
- Luminaire light beam spread: 120°
- Luminous Flux: 3,200 lm
- Optic material: Polystyrene
- Optic type: Beam angle 120°
- Reflector material: Acrylate
- Performance ambient temperature Tq: 25 °C
- Saturated Red (R9): <50
- Stroboscopic effect visibility measure (SVM): 1.6
- Luminous Efficacy (rated) (Nom): 88 lm/W
- Unified glare rating CEN: 22

Miscellaneous

- Especially designed for: Hotel, Restaurant, Garden, Patio
- Extra Features: ProjectLine, Water Resistant

Other characteristics

- Lamp current: 135 mA
- CE mark: Yes
- EU RoHS compliant: Yes
- Photobiological risk: Photobiological risk group 0 @200mm to EN62778
- Photobiological risk specification: 0.2 m

Power

- Input Voltage: 220-240
- Inrush current: 15
- Inrush time: 0.2
- Power Factor (Fraction): 0.9

Power consumption

- Power Consumption: 36
- Power consumption tolerance: +/-10%

Product dimensions and weight

- Overall height: 59
- Overall length: 595
- Overall width: 595

Service

- Warranty: 3 year(s)

Technical specifications

- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated
- Connection: Push-in connector 2-pole
- Control gear failure rate at median useful life 35000 h: 7.5
- Dimmable: No
- Driver/power unit/transformer: Power supply unit (On/Off)
- Driver included: Yes
- Flammability mark: For mounting on normally flammable surfaces
- Flickering value (PstLM) – Flickering value as per EN 61000-3-3: 1
- Glow-wire test: Temperature 650 °C, duration 30 s
- Line Frequency: 50 or 60
- Mech. impact protection code: IK02 | 0.2 J standard
- Number of gear units: 1 unit
- Number of products on MCB of 16 A type B: 35
- Suitable for random switching: Yes

Packaging dimensions and weight

- EAN/UPC – product: 8719514955271
- Net weight: 1.35 kg
- Gross weight: 1.77 kg
- Height: 63 cm
- Length: 60 cm
- Width: 3.8 cm



Issue date: 2025-09-13
Version: 0.269

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com