

PHILIPS

Projectline
Waterproof

LED Luminaire

150 cm

4000 K natural white light

6000 lm

Through wiring



8720169500273



Professional quality for your project

Waterproof led lights, water tight (weather proof light), robust LEDs for industrial use. You can connect multiple luminaires (up to 6) in line with its through wiring feature. ProjectLine waterproof lighting is robust (IK08) and protected from dust ingress and waterspray from any direction (IP65 lighting). Can be mounted on the wall (horizontal), ceiling and suspended. Ideal for general (work) lighting, storage areas, garage and basements with its warm white light output.

Sustainable choice

- Save energy from the moment you turn the switch

Choose for high quality light

- You can trust what the Philips packaging is saying

Durability

- Long life span up to 35,000 hours

Highlights

Energy efficient

All Philips energy savers save energy from the moment you turn the switch. During their lifetime they use fewer kW and thus also result in a lower energy bill. The level of energy saving differs per lamp type and technology.

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Long life span up to 35,000 hours

Philips LED technology extends your product's lifetime up to 35,000 hours.

Specifications

Design and finishing

- Housing Color: White
- Housing Material: Polycarbonate
- Optical cover finish: Opal
- Optical cover material: Polycarbonate

Durability

- Ambient temperature range: -20 to +40 °C

Environmental

- Sustainability rating: -

Guarantee

- Warranty period: 2 years

Light characteristics

- Color rendering index (CRI): >80
- Beam angle of light source: -
- Luminous flux tolerance: +/-10%
- Color Code: 840 neutral white
- Constant light output: No
- Correlated Color Temperature (Nom): 4000
- Initial chromaticity: (0.38, 0.38)
SDCM≤6
- Light source replaceable: No
- Luminaire light beam spread: 110°
- Luminous Flux: 6,000 lm
- Maximum dim level: Not applicable
- Optic material: Polycarbonate
- Optic type: Symmetrical
- Reflector material: -
- Saturated Red (R9): <50
- Performance ambient temperature Tq: 25 °C
- Stroboscopic effect visibility measure (SVM): 0.4
- Luminous Efficacy (rated) (Nom): 113 lm/W
- Unified glare rating CEN: 31

Miscellaneous

- Especially designed for: Hotel & Restaurant
- Extra Features: ProjectLine, MultiColor Temperature

Other characteristics

- CE mark: Yes
- ENEC mark: -
- EU RoHS compliant: Yes
- Photobiological risk: Photobiological risk group 0 @200mm to EN62778
- Photobiological risk specification: 0.2 m

Power

- Input Voltage: 220-240
- Inrush current: 21 A
- Inrush time: 0.29 ms
- Power Factor (Fraction): 0.9

Power consumption

- Average CLO power consumption: - W
- Initial CLO power consumption: - W
- Power Consumption: 53 W
- Power consumption tolerance: +/-10%

Product dimensions and weight

- Overall height: 60 mm
- Overall length: 1,485 mm
- Overall width: 60 mm

Technical specifications

- Cable: -
- Connection: Push-in connector 2-pole
- Control gear failure rate at median useful life 35000 h: 7.5 %
- Control interface: -
- Driver/power unit/transformer: Power supply unit (On/Off)
- Driver included: Yes
- Fixation material: -
- Flammability mark: For mounting on normally flammable surfaces
- Flickering value (PstLM) - Flickering value as per EN 61000-3-3: 1
- Glow-wire test: Temperature 850 °C, duration 30 s
- Ingress protection code: IP65 | Dust penetration-protected, jet-proof
- Line Frequency: 50 or 60
- Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h: -
- Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h: -
- Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h: -
- Mech. impact protection code: IK08 | 5 J vandal-protected
- Number of gear units: 1 unit
- Number of products on MCB of 16 A type B: 18
- Protection class IEC: Safety class II
- Suitable for random switching: Yes
- Dimmable: No

Packaging dimensions and weight

- EAN/UPC - product: 8720169500273
- Net weight: 0.83 kg
- Gross weight: 0.98 kg
- Height: 6.5 cm
- Length: 151 cm
- Width: 6.5 cm



Issue date: 2025-02-20
Version: 0.190

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com