

PHILIPS

Projectline Batten


LED Luminaire

Select 1 temperature using your wall switch – 3000K/6500K/4000K

Easy to install with the plug, use default color temperature: 3000K

30 cm

Connectable up to 8 luminaires



8720169510401



Professional quality for your project

Energy efficient LED lighting battens, professional LEDs for varied applications. ProjectLine batten light supports energy saving and is applicable for a wide range of applications. Our new generation of battens now allows to select the most comfortable color temperature from the three predefined scenes in line with your preferred time of the day. The lighting batten is suitable for wall (horizontal) and ceiling mounting.

Sustainable choice

- Save energy from the moment you turn the switch

Choose for high quality light

- You can trust what the Philips packaging is saying

Durability

- Long life span up to 30,000 hours

Highlights

Energy efficient

All Philips energy savers save energy from the moment you turn the switch. During their lifetime they use fewer kW and thus also result in a lower energy bill. The level of energy saving differs per lamp type and technology.

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

Specifications

Design and finishing

- Color: White
- Material: PVC
- Optical cover finish: Opal
- Optical cover material: Polycarbonate

Durability

- Ambient temperature range: -20 to +40 °C

Light characteristics

- Color rendering index (CRI): >80
- Luminous flux tolerance: +/-10%
- Color Code: 3000/4000/6500
- Constant light output: No
- Correlated Color Temperature (Nom): 3000, 4000, 6500
- Initial chromaticity: (0.44, 0.40)
SDCM≤6
- Light source replaceable: No
- Luminaire light beam spread: 120°
- Luminous Flux: 400 lm
- Maximum dim level: Not applicable
- Optic material: Polycarbonate
- Optic type: Beam angle 120°
- Performance ambient temperature Tq: 25 °C
- Saturated Red (R9): <50
- Stroboscopic effect visibility measure (SVM): 1.6
- Luminous Efficacy (rated) (Nom): 120 lm/W
- Unified glare rating CEN: 25

Miscellaneous

- Especially designed for: Hotel, Restaurant, Garden, Patio
- Extra Features: ProjectLine, Water Resistant

Other characteristics

- CE mark: Yes
- EU RoHS compliant: Yes
- Photobiological risk: Photobiological risk group 0 @ 200mm to EN62471
- Photobiological risk specification: 0.2 m

Power

- Input Voltage: 220 to 240
- Inrush current: 3.55 A
- Inrush time: 0.111 ms
- Power Factor (Fraction): 0.5

Power consumption

- Power Consumption: 3.4
- Power consumption tolerance: +/-10%

Product dimensions and weight

- Overall height: 32 mm
- Overall length: 325 mm
- Overall width: 20 mm

Service

- Warranty: 2 year(s)

Technical specifications

- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated
- Cable: –
- Connection: Mains outlet socket
- Control gear failure rate at median useful life 35000 h: 7.5
- Dimmable: No
- Driver included: Yes
- Fixation material: –
- Flammability mark: For mounting on normally flammable surfaces
- Flickering value (PstLM) – Flickering value as per EN 61000-3-3: 1
- Glow-wire test: Temperature 650 °C, duration 30 s
- Line Frequency: 50 or 60
- Mech. impact protection code: IK02 | 0.2 J standard
- Number of gear units: 1 unit
- Number of products on MCB of 16 A type B: 284
- Suitable for random switching: Yes



Issue date: 2025-09-13
Version: 0.219

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com