



LyteProfile downlights and wall washers provide a perfect balance of functionality with glare control. The robust and versatile UniFrame frame-in kit makes changes and updates easy to manage and install. High optical efficiency reinforced with Accurender technology provides an optimum balance of performance and quality of light. Ideal for use in a variety of applications including open office, institutional, healthcare, and retail.

Standard luminaire: Complete luminaire = Frame + Engine + Trim + Accessories (optional)

Flex install luminaire: Complete luminaires = Engine (F) + Trim + Accessories (optional)

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Qty: _____
 Notes: _____

Frame

Example: 4RN

Series	Aperture	Installation	Options
4	R		
4 Uniframe 4" Non-IC	R Round	N New construction (Non-IC)	— Universal 120/277/347V LC Chicago Plenum EM6 Emergency, 6W Self-Test/Self-Diagnostic (not available for BAC) ¹ BAC Meets the requirements of the Buy American Act of 1933 (BAA) ^{14,15} BABAF Meets the requirements of the Build America Buy America Act for projects funded through FHWA that are obligated before October 1, 2026, and meets the Buy America preferences for FTA ^{14,15}
		R Remodeler (Non-IC)	— Universal 120/277/347V
		A AirSeal (IC)	— Universal 120/277/347V

Engine / Trim

Example: P4RDL20935WCDZ10U

Series	Style	Lumen	CRI/CCT	Beam	Reflector	Flange
P4R						
P4R LyteProfile 4" round downlight	DL Downlight	05 500lm	927 90CRI/2700K	N Narrow M Medium W Wide ²	CL Specular clear	— White (matte)
	LW Lensed Wall Wash ²	10 1000lm 15 1500lm	930 90CRI/3000K 935 90CRI/3500K		CC Comfort clear	B Black (matte) ⁹
	SL Shower light ³ (non-conductive lens)	20 2000lm ⁴ 25 2500lm ⁴ 30 3000lm ⁵ 35 3500lm ⁵ 40 4000lm ⁵	940 90CRI/4000K 9D2W 3000-1800K (dim to warm) ⁶ 96T 2700-6500K (tunable white) ^{7,8}		CD Comfort clear diffuse	P Polished (matches aperture) F Flangeless (requires CA4RFT) ⁹
					WH White (matte) BK Black (matte)	— White (matte) B Black (matte) F Flangeless (requires CA4RFT) ⁹
					WHAMF White (gloss antimicrobial) ⁹	— White (gloss) F Flangeless (requires CA4RFT) ⁹
Dimming / Options			Voltage	Options		
Z10 0-10V 1%	Z10D20 0-10V 1% (dim to Off) (up to 3500lm)		U 120/277V 3 347V (Z10 only) (up to 3000lm) ⁹	— None R Retrofit ¹¹ (not compatible with IEM6) F Flex install (no frame required) ¹² IEM6 Trim mounted EM test switch (for DL style only) BAC Meets the requirements of the Buy American Act of 1933 (BAA) ^{14,15} BABAF Meets the requirements of the Build America Buy America Act for projects funded through FHWA that are obligated before October 1, 2026, and meets the Buy America preferences for FTA ^{14,15}		
L1 Lutron LDE1 EcoSystem 1% (500lm not available)	RA Integral Interact Pro RF sensor (up to 2500lm) ¹⁰		U 120/277V			
E Forward & Reverse Phase (up to 2500lm)			1 120V			

Accessories¹⁴

- SWCS** New or remodel construction, integral RADIO or remote (recessed or surface) sensing with 0-10v luminaires. See SWCS spec sheet¹³
- CAEM6** Field installable Bodine BSL6 6W battery pack with self-test/self-diagnostic for use with new construction frames, 120-277V
- CA4RFT** Mud-in ring for use in 4" round flangeless trim installations (ordered with a flangeless (F) light engine)
- CAEM6TSCP** Remote switch cover plate. Order with EM6 frame for remote mounted test switch (Required for LW and SL styles).
- C4RVPWH** IP65 rated vandal proof matte white accessory mounts onto flangeless light engines (F) and non-IC (N) frame only
- 4RNSR** 4" round/square non-IC frame with Flex (F) light engine (provides mechanical support for rough-in construction only, no junction box)
- LCEM6** Field installable Bodine BSLO6 emergency battery pack (for Flex (F) light engine only, includes switch mounting plate)
- T347-75VA** 347-120V step-down transformer for non-IC (N) frame only (see page 2 for details)
- 7920** 4" sloped ceiling adapter (refer to SCA spec sheet for slope options). Must order 4RN frame and flanged trim.

*See page 2 for footnotes.



P4R LyteProfile 4"

Round Downlight & Lensed Wall Wash

Footnotes

- Emergency (EM6) frame is compatible with reflector mounted test switch when light engine is ordered with IEM6 (not compatible w/347V).
- Lensed wall wash (LW) style only available with Wide (W) beam (2000lm max).
- Shower light (SL) in only available with White (WH) reflector finish and Wide (W) beam. Not available with flangeless option.
- Not available with AirSeal (A) frame.
- Not available with AirSeal (A) frame. Available with CL, CC, and CD reflector finishes only.
- Specify 9D2W with Z10U dimming only (up to 2000lm max). Not compatible with Z10D20 or 347V (3) options. Not available with wide (W) beam.
- Specify 96T with Z10U or RAU dimming only (up to 2000lm max). Not compatible with Z10D20 or 347V (3) options. Not available with wide (W) beam.
- The 500lm (05) option is not available.
- Consult factory with ETO request for antimicrobial reflector finish (WHAMF) and black (B) flange for all styles, and flangeless (F) for LW style.
- Linear driver profile. See dimensional data following. Specify only with non-IC (N) frame, not for use with LC or EM6 options.
- Retrofits select legacy Lightolier luminaires (see pages 2 for details). Z10 dimming only. Consult factory for other dimming options.
- Flex install requires light engine & trim only (up to 4000lm only). Accessory frames available. Not compatible with standard frames and associated options. Not available with Interact (RA) dimming and IEM6 trim.
- Requires IRT9015 IR remote and Interact Pro App for commissioning (requires above ceiling access).
- BAA and compliance requires that BAC option be selected for each of frame, engine/trim. BABA compliance requires that BABAF option be selected for each of frame, engine/trim. Frame and engine will be ordered/shipped together; trim will be ordered/shipped separately. Accessories (optional) are not currently BAA- or BABA-compliant.
- Failure to properly select the "BAC" suffix could result in you receiving product that is not BAA compliant product with no recourse for an RMA or refund. This BAC designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies. Genlyte's products with a BAC option code designation are manufactured in the US and utilize a BAA COTS exemption rule for compliance. "BABAF" designates the product will meet the standards set by FHWA for BABA and FTA for Buy America. As noted, for FHWA BABA compliance, applicable projects must be funded by October 1, 2026.

Features

Optics

- Provides a 60° cutoff (physical and reflected)
- Available in wide (80°), medium (65°), and narrow (55°) beam options.
- Spun and anodized reflectors available in specular (clear), semi-specular (comfort clear and diffuse finishes. Also available in white and black painted finishes.
- Consult factory for RAL finishes.
- Quality of light
- Color consistency: 2 SDCM
- 90 CRI minimum (Accurender)

Construction (New Construction)

- Galvanized stamped steel for dry / plaster ceilings.
- Pre-installed telescoping mounting bars (13"-24")
- Frame accommodates C- channel, black iron, and 3/4" EMT for mounting distances greater than 24" between joists.
- Manufactured from 20 gage galvanized steel construction with rolled edge aperture to guide cutting tools for perfect hole cutting.

Max ceiling thickness is 1.5" (38 mm).

Patented install Mounting frame

- Pre-installed mounting bars allow for fast and tool-less install into T-grid & hat channel ceilings
- Close-cut aperture design eliminates an undesired gap between ceiling material and reflector.
- Simple plug-and-play connection between frame and light engine from below the ceiling allows for:
 - Easy upgrades
 - Technology changes
 - Repairs and troubleshooting

Retrofit

- Easily updates legacy LyteProfile LED downlights to the latest technology. Includes light engine, trim, and driver mounted on cover plate that mounts to previous generations of LyteProfile LED luminaires. Order with R option code at end of light engine/trim catalog number.

Dimming

- Advance 0-10v 1% (Z10) logarithmic curve is standard. Specify D2O for factory-set dim-to-off function (consult factory for linear dimming curve).
- Lutron LDE1 (L1) EcoSystem 1%
- Electronic low voltage (E) offers forward or reverse phase dimming
- Dim to Warm (D2W): changes CCT from 3000-1800K gradually as it dims. Use with Z10U dimming only. Fixture-to-fixture consistency of ≤3SDCM at 2700K & 3000K, & ≤5SDCM at 1800K
- Tunable white (6T): 2700K to 6500K CCT. Use with Z10U or RAU dimming only. Fixture-to-fixture consistency of ≤3SDCM at 2700K, 5000K, & 6500K CCT.

Light engine

Quick connect power pack allow for easy installation and replacement from below ceiling with no need for additional wiring. This allows for:

- Frame and ceiling installation to be performed while still finalizing details such as lumen packages, CCT and control type.
- Easy replacement of electronics at end of life with minimal wasted material and labor required.
- Ease and upgradability of technology.

Flex engine (F)

- Frame-optional engine suited for new construction, remodel, and retrofit applications.
- 4RNSR new construction frame accessory available as required to support ceiling construction.
- All wiring is done on the integral j-box to the engine.

Options and Accessories

Sloped ceilings: Compatible with sloped ceiling adapters (see SCA spec sheet).

Flangeless mud-in ring: Use CA4RFT For use with flangeless plaster installations.

Field Installed Emergency: Field install EM6 kit with Bodine BSL6 6W battery pack with self-test/self-diagnostic. Includes remote ceiling plate for test switch. To mount test switch to trim for new construction frame, order trim with IEM6 option code (e.g. C4RDLCCEM6). Refer to Calculte-LyteProfile-EasyLyte Emergency Battery Pack specification sheet for more details.

- CAEM6:** For use with UniFrame frame in kits.
- LCEM6:** For use with Flex intall (F) light engines.

C4RVPWH: Includes machined aluminum ring painted white, gasketed for IP65 protection, and impact resistant polycarbonate lens (IK10). Locks in place with discrete setscrew (key included). Available also with antimicrobial finish (C4RVPWHAMF).

CAEM6TSCP: Ceiling cover plate for remote mounted EM6 test switch. 1/2" (25mm) hole, 4 3/8" (109mm) x 2 3/4" (69mm) rectangular. Includes two mounting screws. Required for lensed wall wash (LW) and shower light (SL) styles.

T347-75VA: Field installable 347:120V 75VA step-down transformer, attaches to knock out on frame junction box, for use with non-IC (N) or remodel (R) frames.

SWCS: Interact Ready System Bridge Accessory. Requires IRT9015 IR remote and Interact Pro App for commissioning. Refer to [SWCS spec sheet](#) for details.

P4R LyteProfile 4"

Round Downlight & Lensed Wall Wash

Emergency

Bodine BSL6 6W battery pack with self-test/ diagnostic functionality. Factory or field mounted to frame.

- For trim with integral emergency test switch, order light engine with IEM6 option (ex: P4RDL20935WCDZ10UIEM6). DL style only.
- For remote ceiling mounted test switch, order standard light engine (ex: P4RDL20935WCDZ10U). Optional accessory ceiling mounting plate available (CAEM6TSCP) for remote mounted test switch.
- Refer to Calculite-LyteProfile-EasyLyte Emergency Battery Pack specification sheet for more details.
- Tunable white (96T) with EM6 frame option wired for emergency lighting on 6500K CCT circuit.
- CEC Title 24 JA8 Certified.

Performance & Construction

- Soft focus acrylic lens minimizes pixilated glare from LED source, shapes light beam to desired effect, mixes light sources for homogeneous color temperature, and mitigates color over angle deviations.
- Lumen Maintenance: L80 @ 60,000 hours.
- 347V light engines are Z10 dimming only and include dedicated 347V driver. For 347V non-Z10 dimming, order T347-75VA field-installable step-down transformer accessory.

Labels and Listings

- cULus listed for wet locations
- CCEA (frames with *LC suffix)
- ENERGY STAR® certified (except 500lm configurations & Black finishes)
- RoHS certified
- Red List Declare label certified, ID SIG-0021 ([View full Declare label](#))

Warranty




5 year limited warranty
Visit [Signify.com/warranties](https://www.signify.com/warranties)
for more information on Signify's
standard 5-year limited warranty
on complete luminaire systems.

P4R LyteProfile 4"

Round Downlight & Lensed Wall Wash

Signify interact Easy. Effective. Smart.



Meet Interact

A smart, wireless luminaire level lighting control system (LLLC). A complete solution that combines modern and intuitive technologies for easy installation and specification.


- Works with or without gateway
- **No** IT
- **No** light point restrictions
- **Up to 75%** out of the box savings
- **Fast & easy**
- **Code & rebates** compliant

Capabilities



*Grouping, zoning, dimming, high-end trimming, scenes, scheduling, manual controls

Benefits



1. Versus legacy systems based on installer interviews
2. Based on installer analysis done by Signify for a typical multi-zone space
3. Utility programs across US

Just lights and an App



1. Install the Interact ready fixtures with embedded smart sensor
2. Install the wireless wall switch
3. Configure your setup with the Interact App
4. Leverage the IRT9015 remote accessory to accelerate your setup process
5. Optionally add a gateway for insights and management

Learn more about Interact:

Interact includes an app, a web portal, and a comprehensive range of Interact ready wireless luminaires, lamps, retrofit kits, and control devices like switches and sensors that operate within the same system.



P4R LyteProfile 4"

Round Downlight & Lensed Wall Wash

Controls Options

Interact radio node for Standalone, Gateway & Gateway + IoT tiers (RA)

RA sensor option is a connected radio node supporting wireless mesh connectivity.

Compatible with standalone and gateway modes of Interact.

Interact occupancy & daylight sensor for Standalone, Gateway & Gateway + IoT tiers (CS)

The CS sensor option is a connected sensor with built-in occupancy and daylight detection, along with wireless mesh connectivity.

Compatible with standalone and gateway modes of Interact.

Interact advanced sensor bundle for Gateway + IoT tier (SB)

SB sensor option offers occupancy and daylight sensing and supports advanced IoT capabilities, such as desk-level temperature and humidity monitoring, noise classification, and Bluetooth Low Energy (BLE) beacon functionality.

Setup requires a compatible gateway and internet connectivity.

With compatible gateway and software analytics, SB sensor option enables greater building efficiency, seamless system integration, and optimized space utilization through occupancy and environmental insights.

Interact for intelligent buildings sensor option codes across Genlyte product lines*

	Sensor part #	Daybrite	Ledalite	Lightolier
Zigbee + Bluetooth	SC100B	RADIO	RA	RA
Zigbee + Bluetooth + Sensing	SC200B	SWZCS	CS	SBA or SWCS accessory
Zigbee + Bluetooth + Sensing + Environmental data	SC1500	IAOSB	SB	SBA or SWCS accessory
Zigbee + Highbay + Bluetooth + Sensing	SNH210 IA	SWZCSH	-	-

P4R LyteProfile 4"

Round Downlight & Lensed Wall Wash



AccuRender Technology (CRI 90+)

The right light brings colors to life. Our new AccuRender technology helps ensure colors are rendered more accurately and consistently, while doing so as efficiently as CRI 80 products.



Standard CRI 80
Good color rendering and high efficacy



Standard CRI 90
Better color rendering and low efficacy



AccuRender
Best color rendering, color preference and high efficacy

Enjoy design flexibility

Full range of products and options:

- Available soon in across Lightolier portfolio for application flexibility
- Multiple color temperatures (CCTs) and lumen packages offered

Promote savings

High efficacy, with no penalty:

- Energy efficacy compares well to conventional 80 CRI
- Up to 25% more energy savings vs competitor 90 CRI¹
- Helps meet Title 24 requirements

Show your true colors

High color rendering:


- True to life colors to help energize your environment and render better flesh tones critical for healthcare hospitality and retail applications.
- R_a up to 94 CRI
- R_g up to 67 CRI
- G_s up to 99 CRI
- C₉ up to 94 CRI
- R_r up to 92 TM-30
- R_{r,hi} up to 91 TM-30
- R_g up to 100 TM-30
- R_{ca,hi} up to -5% TM-30

Achieve color balance


Best in class color consistency:

- Promote aesthetic harmony in your space with ≤ 2 SDCM

Tunable white binning chart



Dim-to-Warm: CCT vs Dimmed level



P4R LyteProfile 4"

Round Downlight & Lensed Wall Wash

Electrical - Static White

Input frequency of 50/60Hz, Power Factor @ Max Load >0.9

Product	Input Volts (V)	Input Freq. (Hz)	Input Current (A)	LED Drive Current (A)	Input Power (W)	LED Power (W)	THD Factor @ Max Load	Power Factor @ Max Load
P4RDL05_Z10U/3	120V	50/60	0.041A	0.12A	4.9W	3.9W	<10%	>0.9
	277V	50/60	0.019A	0.12A	5.1W	3.9W	<30%	>0.9
	347V	50/60	0.017A	0.12A	5.8W	3.9W	<30%	>0.9
P4RDL10_Z10U/3	120V	50/60	0.070A	0.20A	8.3W	6.8W	<10%	>0.9
	277V	50/60	0.031A	0.20A	8.6W	6.8W	<20%	>0.9
	347V	50/60	0.028A	0.20A	9.7W	6.8W	<30%	>0.9
P4RDL15_Z10U/3	120V	50/60	0.102A	0.30A	12.2W	10.2W	<10%	>0.9
	277V	50/60	0.044A	0.30A	12.3W	10.2W	<10%	>0.9
	347V	50/60	0.040A	0.30A	14.0W	10.2W	<25%	>0.9
P4RDL20_Z10U/3	120V	50/60	0.134A	0.40A	16.1W	13.6W	<10%	>0.9
	277V	50/60	0.058A	0.40A	16.2W	13.6W	<10%	>0.9
	347V	50/60	0.052A	0.40A	17.9W	13.6W	<20%	>0.9
P4RDL25_Z10U/3	120V	50/60	0.175A	0.53A	21.0W	17.9W	<10%	>0.9
	277V	50/60	0.076A	0.53A	21.1W	17.9W	<10%	>0.9
	347V	50/60	0.064A	0.53A	22.3W	17.9W	<20%	>0.9
P4RDL30_Z10U/3	120V	50/60	0.208A	0.63A	25.0W	21.3W	<10%	>0.9
	277V	50/60	0.091A	0.63A	25.1W	21.3W	<10%	>0.9
	347V	50/60	0.077A	0.63A	26.6W	21.3W	<20%	>0.9
P4RDL35_Z10U/3	120V	50/60	0.247A	0.75A	29.7W	25.5W	<10%	>0.9
	277V	50/60	0.107A	0.75A	29.7W	25.5W	<10%	>0.9
	347V	50/60	0.087A	0.75A	30.4W	25.5W	<20%	>0.9
P4RDL40_Z10U/3	120V	50/60	0.288A	0.88A	34.6W	29.8W	<10%	>0.9
	277V	50/60	0.125A	0.88A	34.6W	29.8W	<10%	>0.9
	347V	50/60	0.102A	0.88A	35.4W	29.8W	<20%	>0.9

Electrical - Dim-to-Warm (9D2W)

Input frequency of 50/60Hz, Power Factor @ Max Load >0.9

Product	Input Volts (V)	Input Freq. (Hz)	Input Current (A)	LED Drive Current (A)	Input Power (W)	LED Power (W)	THD Factor @ Max Load	Power Factor @ Max Load
P4RDL059D2W_Z10U	120V	50/60	0.067A	0.175	8.1W	6.3W	<15%	>0.9
P4RDL059D2W_Z10U	277V	50/60	0.031A	0.175	8.6W	6.3W	<25%	>0.8
P4RDL109D2W_Z10U	120V	50/60	0.118A	0.315	14.2W	11.3W	<10%	>0.9
P4RDL109D2W_Z10U	277V	50/60	0.055A	0.315	15.1W	11.3W	<20%	>0.9
P4RDL159D2W_Z10U	120V	50/60	0.161A	0.450	19.3W	16.2W	<10%	>0.9
P4RDL159D2W_Z10U	277V	50/60	0.074A	0.450	20.5W	16.2W	<20%	>0.9
P4RDL209D2W_Z10U	120V	50/60	0.212A	0.600	25.4W	21.6W	<10%	>0.9
P4RDL209D2W_Z10U	277V	50/60	0.094A	0.600	26.0W	21.6W	<10%	>0.9

Electrical - Tunable White (96T)





Input frequency of 50/60Hz, Power Factor @ Max Load >0.9

Product	Input Volts (V)	Input Freq. (Hz)	Input Current (A)	LED Drive Current (A)	Input Power (W)	LED Power (W)	THD Factor @ Max Load	Power Factor @ Max Load
P4RDL0596T_Z10U	120V	50/60	0.044A	0.114	5.3W	4.1W	<15%	>0.9
P4RDL0596T_Z10U	277V	50/60	0.020A	0.114	5.6W	4.1W	<25%	>0.8
P4RDL1096T_Z10U	120V	50/60	0.088A	0.235	10.6W	8.5W	<10%	>0.9
P4RDL1096T_Z10U	277V	50/60	0.041A	0.235	11.3W	8.5W	<20%	>0.9
P4RDL1596T_Z10U	120V	50/60	0.131A	0.362	15.7W	13.0W	<10%	>0.9
P4RDL1596T_Z10U	277V	50/60	0.060A	0.362	16.7W	13.0W	<20%	>0.9
P4RDL2096T_Z10U	120V	50/60	0.178A	0.497	21.3W	17.9W	<10%	>0.9
P4RDL2096T_Z10U	277V	50/60	0.079A	0.497	21.8W	17.9W	<10%	>0.9

P4R LyteProfile 4"

Round Downlight & Lensed Wall Wash

New construction




	Downlight/Showerlight		Lensed Wall Wash
	500-2500lm	3000-4000lm	
A	5 3/4" (146mm)	5 3/4" (146mm)	5 3/4" (146mm)
B	4 1/2" (114mm)	4 1/2" (114mm)	4 1/2" (114mm)
C	3 3/8" (86mm)	5 1/4" (133mm)	3 3/8" (86mm)
D	2 1/4" (54mm)	2 1/4" (54mm)	2 1/8" (54mm)
E	2 3/8" (60mm)	2 3/8" (60mm)	N/A
F	5" (127mm)	5 1/4" (133mm)	4 7/8" (127mm)


* Center point location for integral emergency test switch (IEM6)

- Lower end of LW lens is 3/16" (5mm) above flange.

Flangeless mud-in ring (CA4RFT) accessory




Vandal Proof (VP) accessory




P4R LyteProfile 4"

Round Downlight & Lensed Wall Wash

AirSeal (A) / Chicago plenum (LC)




Linear driver (RA)




Requires either top access or 19" plenum space without sensor, and 22" with sensor.


Flex Install (F)



4RNSR Flex install non-IC frame



LCEM6 Flex install (F) engine only



A	B	C	D	E	F
13 1/4"	9 5/8"	13 3/8"	1 1/4"	6 3/8"	5 3/8"
334mm	244mm	345mm	37mm	162mm	169mm

P4R LyteProfile 4"

Round Downlight & Lensed Wall Wash

Reflectors



Specular clear (CL): Most specular and most efficient finish, delivers maximum photometric performance but can produce a mirror image effect of the interior space.



Comfort clear (CC): Semi-specular finish that softens the light at the source of the reflector and creates a subtle, even luminance from the reflector cone.



Comfort clear diffuse (CD): Slightly diffuse clear finish, which eliminates iridescence and reduces the mirror image effect inherent with a specular finish.



Vandal proof (VP): Provides an elegant solution for vandal resistant needs. One piece machined aluminum ring with impact resistant clear lens. Flangeless (F) flange must be ordered. Provides the luminaire with an IK10 impact and IP65 rating.



White (-): (matte) Brightest aperture when illuminated and provides the smoothest transition to most ceilings when off (white is only available with a white flange).



Black (BK): Painted matte finish that provides the lowest aperture brightness possible and reduces source identification in a ceiling significantly.



Shower light (SL): Wet location rated shower light applicable in any installation requiring dead front trims, interior or exterior non-corrosive applications, or where a diffused lens at the ceiling is required (non-conductive).


Flanges



White (-): (matte) Provides the smoothest transition to ceilings when off.



Black (BK): Painted matte finish that provides the lowest aperture brightness possible.



Polished (P): (matches aperture) Produces a continuous look throughout the reflector (aperture matching).



Flangeless (F): (flush-mount) Creates a flush, virtually seamless transition from aperture to ceiling.



Mud-in ring (FT): Low profile, machined aluminum mud-in ring provides a raised rib to plaster up to and a 3/16" flange thickness. The ring is attached to the ceiling material as opposed to the frame-in kit to avoid conduction of heat and vibration which can cause yellowing or cracking of the plaster.

P4R LyteProfile 4"


Round Downlight & Lensed Wall Wash

Adjustment Factors

Finish	CRI/CCT	Lumens	
CL = 100%	90CRI 4000K = 106%	4000lm = 200%	2000lm = 100%
CC = 86%	90CRI 3500K = 104%	3500lm = 175%	1500lm = 75%
CD = 91%	90CRI 3000K = 100%	3000lm = 150%	1000lm = 50%
WH = 90%	90CRI 2700K = 96%	2500lm = 125%	500lm = 25%
BK = 54%			

Downlight, Narrow beam, 19W LED, 90CRI, 3000K

Candela Curves



Zonal lumens & percentages

Zone	Lumens	%Luminaire
0-30	1474	74.9%
0-40	1838	93.4%
0-60	1965	99.8%
0-90	1968	100.0%

Report!:
P4RDL20930NCLZ10U.ies

Output Lms:	1968 lms
Input Watts ² :	18.6W
Efficacy:	105.8 lm/w
CCT ³ :	3000K
CRI:	90 min
Beam Angle:	54°
Spacing Crit.:	0.66

Angle	Mean CP	Lms
0	2912	
5	2718	
10	2288	114
15	1855	
20	1664	318
25	1608	
30	1135	448
35	561	
40	214	461
45	115	
50	85	343
55	27	
60	5	204
65	2	
70	1	117
75	1	
80	0	66
85	0	
90	0	20

Single unit data

Height to lighted plane	Initial center beam foot-candles	Beam dia. (ft)*
5'	116	3.3'
6'	81	4.0'
7'	59	4.6'
8'	46	5.3'
9'	36	5.9'

* Beam diameter is where foot-candles drop to 50% of maximum.

Multiple unit data - RCR 2

Spacing on center	Initial center beam foot-candles	Watts per sq.ft.
5'	90.0	0.82
6'	59.0	0.54
7'	42.0	0.39
8'	35.0	0.32
9'	28.0	0.26


38'x38'x10' Room, Workplane 2.5' above floor, 80/50/20% Reflectances

Coefficients of utilization

Ceiling	80%				70%		50%		30%		0%	
	70	50	30	10	50	10	50	10	50	10	0	
Wall	70	50	30	10	50	10	50	10	50	10	0	
RCR	Zonal cavity method - Effective floor reflectance = 20%											
Room Cavity Ratio	0	119	119	119	119	116	116	111	111	106	106	100
	1	114	111	109	106	109	105	105	101	101	98	94
	2	108	103	100	96	102	95	99	93	96	91	88
	3	103	97	92	88	95	87	93	86	90	85	82
	4	98	91	85	81	89	81	87	80	85	79	76
	5	93	85	79	75	84	75	82	74	81	73	71
	6	89	80	74	70	79	70	78	69	76	69	67
	7	84	75	69	65	75	65	73	65	72	64	63
	8	80	71	65	61	71	61	69	61	68	61	59
	9	77	67	61	58	67	57	66	57	65	57	56
	10	73	64	58	54	63	54	63	54	62	54	53

Downlight, Medium beam, 19W LED, 90CRI, 3000K

Candela Curves



Zonal lumens & percentages

Zone	Lumens	%Luminaire
0-30	1271	65.4%
0-40	1740	89.5%
0-60	1941	99.8%
0-90	1944	100.0%

Report!:
P4RDL20930MCLZ10U.ies

Output Lms:	1944 lms
Input Watts ² :	18.6W
Efficacy:	104.5 lm/w
CCT ³ :	3000K
CRI:	90 min
Beam Angle:	66°
Spacing Crit.:	1.06

Angle	Mean CP	Lms
0	1925	
5	1857	
10	1739	173
15	1580	
20	1465	446
25	1449	
30	1235	653
35	745	
40	361	468
45	192	
50	122	160
55	35	
60	6	41
65	2	
70	1	3
75	1	
80	0	1
85	0	
90	0	0

Single unit data

Height to lighted plane	Initial center beam foot-candles	Beam dia. (ft)*
5'	77	5.3'
6'	53	6.4'
7'	39	7.4'
8'	30	8.5'
9'	24	9.5'

* Beam diameter is where foot-candles drop to 50% of maximum.

Multiple unit data - RCR 2

Spacing on center	Initial center beam foot-candles	Watts per sq.ft.
5'	88.0	0.82
6'	58.0	0.54
7'	41.0	0.39
8'	25.0	0.32
9'	27.0	0.26

38'x38'x10' Room, Workplane 2.5' above floor, 80/50/20% Reflectances

Coefficients of utilization

Ceiling	80%				70%		50%		30%		0%	
	70	50	30	10	50	10	50	10	50	10	0	
Wall	70	50	30	10	50	10	50	10	50	10	0	
RCR	Zonal cavity method - Effective floor reflectance = 20%											
Room Cavity Ratio	0	119	119	119	119	116	116	111	111	106	106	100
	1	113	110	108	106	108	104	104	101	100	98	93
	2	107	102	98	95	101	94	97	91	94	90	86
	3	102	95	90	86	94	85	91	84	88	82	79
	4	96	88	82	78	87	78	85	77	83	76	73
	5	91	82	76	72	81	71	79	71	78	70	68
	6	86	77	70	66	76	66	74	65	73	65	63
	7	81	72	65	61	71	61	70	60	68	60	58
	8	77	67	61	57	67	56	65	56	64	56	54
	9	73	63	57	53	63	53	62	52	61	52	51
	10	70	59	53	49	59	49	58	49	57	49	47

1. Tested using absolute photometry as specified in LM79: IESNA Approved Method for the Electrical and Photometric Measurements of Solid-State Lighting Products.
2. Wattage: controlled to within 5%
3. Correlated Color Temperature: within specs as defined in ANSI_NEMA_ANSI C78.377-2008: Specifications for the Chromaticity of Solid State Lighting Products.

P4R LyteProfile 4"


Round Downlight & Lensed Wall Wash

Adjustment Factors

Finish	CRI/CCT	Lumens	
CL = 100%	90CRI 4000K = 106%	4000lm = 200%	2000lm = 100%
CC = 86%	90CRI 3500K = 104%	3500lm = 175%	1500lm = 75%
CD = 91%	90CRI 3000K = 100%	3000lm = 150%	1000lm = 50%
WH = 90%	90CRI 2700K = 96%	2500lm = 125%	500lm = 25%
BK = 54%			

Downlight, Wide beam, 19W LED, 90CRI, 3000K

Candela Curves



Zonal lumens & percentages

Zone	Lumens	%Luminaire
0-30	875	49.8%
0-40	1422	81.0%
0-60	1752	99.8%
0-90	1756	100.0%

Report!:

P4RDL20930WCLZ10U.ies
 Output Lms: 1756 lms
 Input Watts²: 16.1W
 Efficacy: 109.1lm/w
 CCT³: 3000K
 CRI: 90min
 Beam Angle: 82°
 Spacing Crit.: 1.42

Angle	Mean CP	Lms
0	997	
5	983	
10	996	94
15	1049	
20	1048	296
25	1045	
30	1052	485
35	919	
40	584	547
45	332	
50	185	266
55	56	
60	9	64
65	3	
70	1	3
75	1	
80	0	1
85	0	
90	0	0

Single unit data

Height to lighted plane	Initial center beam foot-candles	Beam dia. (ft)*
5'	40	7.1'
6'	28	8.5'
7'	20	9.9'
8'	16	11.4'
9'	12	12.8'

*Beam diameter is where foot-candles drop to 50% of maximum.

Multiple unit data - RCR 2

Spacing on center	Initial center beam foot-candles	Watts per sq.ft.
5'	78.0	0.71
6'	51.0	0.47
7'	37.0	0.33
8'	31.0	0.28
9'	20.0	0.22


38'x38'x10' Room, Workplane 2.5' above floor, 80/50/20% Reflectances

Coefficients of utilization

Ceiling	80%				70%		50%		30%		0%	
	70	50	30	10	50	10	50	10	50	10	0	
Wall	70	50	30	10	50	10	50	10	50	10	0	
RCR	Zonal cavity method - Effective floor reflectance = 20%											
Room Cavity Ratio	0	119	119	119	119	116	116	111	111	106	106	100
	1	113	110	107	104	107	103	103	99	100	96	92
	2	106	100	96	92	99	91	95	89	92	87	83
	3	100	92	86	82	91	81	88	80	85	79	76
	4	93	85	78	73	83	73	81	72	79	71	69
	5	87	78	71	66	77	66	75	65	73	64	62
	6	82	72	65	60	71	60	69	59	68	59	57
	7	77	66	59	54	65	54	64	54	63	54	52
	8	72	61	54	50	61	50	59	49	58	49	47
	9	68	57	50	45	56	45	55	45	54	45	43
	10	64	53	46	42	53	42	52	42	51	42	40

Lensed Wall Wash, Wide beam, 19W LED, 90CRI, 3000K

Candela Curve



Report!:

P4RLW20930WCLZ10U.ies
 Output Lms: 1966 lms
 Input Watts²: 19.0W
 Efficacy: 103.5lm/w
 CCT³: 3000K
 CRI: 90min

Multiple unit data

Distance from ceiling in feet	Footcandles on wall		
	2' from wall		
	2' on ctr.		
1	41	41	41
2	73	74	73
3	74	76	74
4	61	63	61
5	46	48	46
6	34	36	34
7	26	27	26
8	20	21	20
9	16	17	16
10	13	14	13
12	11	11	11
14	9	10	9

Multiple unit data

Distance from ceiling in feet	Footcandles on wall		
	3' from wall		
	3' on ctr.		
1	12	11	12
2	26	25	26
3	34	33	34
4	36	35	36
5	32	33	32
6	27	28	27
7	23	23	23
8	19	19	19
9	15	16	15
10	13	13	13
12	11	11	11
14	9	10	9

1. Tested using absolute photometry as specified in LM79: IESNA Approved Method for the Electrical and Photometric Measurements of Solid-State Lighting Products.
2. Wattage: controlled to within 5%
3. Correlated Color Temperature: within specs as defined in ANSI_NEMA_ANSI C78.377-2008: Specifications for the Chromaticity of Solid State Lighting Products.