



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering Guide

Example: DWL1 N

<b>Product Code</b>	DWL1	Beacon
<b>Finish</b>	N	Natural Bronze

### Spacing Chart

### Specifications

**HOUSING:**

Single-piece compression molded fiberglass reinforced polyester composite lower housing. Die cast brass upper housing. Fasteners are 300 series stainless steel. Two (2) 1/2" conduit inlets at bottom. Note: Watertight connectors and potting compound (by others) must be used to maintain a watertight seal at conduit entry points.

**FINISH:**

Natural Brass (N) is as-cast and tumble polished. Composite is pressure formed, molded-in color.

**OPTICAL ASSEMBLY:**

Frosted borosilicate glass.

**LAMPING:**

20W maximum T3 bi-pin lamp. Lamp is included with fixture. Lower wattage lamps are acceptable.

**ELECTRICAL ASSEMBLY:**

Bi-pin socket type (G4) with 250° C high temperature teflon coated wire leads. 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

**WARRANTY:**

Lifetime limited warranty.

**CERTIFICATIONS:**

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

**Height :** 8 3/4" (222mm)      **Width:** 5" (127mm)      **Max. Weight:** 5.5 lb.

