

LIGHTOLIER


by @signify

Track Lighting

Alcyon Line Voltage

22OR2 Open Ring PAR20

Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____



Ordering Information

Catalog No.	Finish	Mounting	Lamps
22OR2WH 22OR2BK 22OR2AL	Matte White Matte Black Metallic Aluminum	All Lytespan Track Systems. Does not mount on ProSpec Track.	PAR20 Maximum 50W

Features

- Track Attachment Fitting:** Locking lever for mechanical/electrical connection
- Brass Contact:** Extends for connection to second circuit (Advent Lytespan track only)
- Horizontal Pivot:** Wireless stem profile with 365° horizontal rotation
- Vertical Pivot:** 0-90° vertical adjustment
- Socket:** Porcelain socket, medium base, nickel-plated screw shell
- Housing:** Die cast aluminum
- Accessory cartridge:** Included; rotate clockwise to attach; retaining ring included

Finish

All Painted finishes are baked enamel.

Dimming

Fixture may be used on a track with a dimmer.
Consult dimmer manufacturer for correct dimmer selection.

Accessories

Accessory Holder: Integral
Accessories: Accepts two total
(1 lens + 1 louver or 2 lenses)
Lens: AF25, ADF25. Not compatible with AF25IR
Louver: AL25HC

Labels

UL, cUL

22OR2 Alcyon Line Voltage


Open Ring PAR20

AIMING ANGLE:

L Beam length
W Beam Width
C Distance to center beam
D Distance
A Aiming Angle
FC Footcandles

L and **W** are the outer points where the candle power drops to 50% of the maximum. **FC** are the initial footcandles at the center of the beam.

Lamp data shown is typical. Consult lamp manufacturers for availability and performance. CBCP= Center Beam Candle Power.



LAMP

	Beam Spread (To 50% CBCP)	CBCP	Rated Life (Hrs.)	D	FC	L	W	D	C	FC	L	W	D	C	FC	L	W	D	C	FC	L	W
50W PAR20 SP	10°	4,600	2,500	6'	128	1.0'	1.0'	8'	4.6'	47	1.9'	1.6'	2'	3.5'	144	1.4'	0.7'	4'	4.0'	102	1.4'	1.0'
				8'	72	1.4'	1.4'	3'	5.2'	64	2.1'	1.0'	5'	5.0'	65	1.8'	1.2'	5'	5.0'	65	1.8'	1.2'
				10'	46	1.7'	1.7'	4'	6.9'	36	2.9'	1.4'	6'	6.0'	45	2.1'	1.5'	6'	6.0'	45	2.1'	1.5'
				12'	32	2.1'	2.1'	5'	8.7'	23	3.6'	1.7'	7'	7.0'	33	2.5'	1.7'	7'	7.0'	33	2.5'	1.7'
50W PAR20 NFL	25°	1,500	2,500	4'	116	1.9'	1.9'	3'	1.7'	134	2.0'	1.7'	1'	1.7'	231	2.3'	1.0'	3'	3.0'	73	3.1'	2.0'
				6'	51	2.9'	2.9'	5'	2.9'	48	3.3'	2.8'	2'	3.5'	58	4.6'	1.9'	4'	4.0'	41	4.1'	2.7'
				8'	29	3.8'	3.8'	7'	4.0'	25	4.6'	3.9'	3'	5.2'	26	7.0'	2.9'	5'	5.0'	26	5.1'	3.4'
				10'	19	4.8'	4.8'	9'	5.2'	15	5.9'	5.0'	4'	6.9'	14	9.3'	3.8'	6'	6.0'	18	6.1'	4.1'
50W PAR30 FL	35°	1,400	3,000	6'	39	3.8'	3.8'	6'	3.5'	25	5.2'	4.4'	2'	3.5'	44	7.2'	2.5'	3'	3.0'	55	4.2'	2.7'
				7'	29	4.4'	4.4'	7'	4.0'	19	6.1'	5.1'	3'	5.2'	19	10.8'	3.8'	4'	4.0'	31	5.6'	3.6'
				8'	22	5.0'	5.0'	8'	4.6'	14	7.0'	5.8'	4'	6.9'	11	14.4'	5.0'	5'	5.0'	20	7.0'	4.5'
				9'	17	5.7'	5.7'	9'	5.2'	11	7.8'	6.6'	5'	8.7'	7	18.0'	6.3'					
60W PAR16 NSP	10°	5,000	2,000	6'	139	1.0'	1.0'	5'	2.9'	130	1.2'	1.0'	2'	3.5'	156	1.4'	0.7'	3'	3.0'	196	1.1'	0.7'
				8'	78	1.4'	1.4'	7'	4.0'	66	1.6'	1.4'	3'	5.2'	69	2.1'	1.0'	5'	5.0'	71	1.6'	1.2'
				10'	50	1.7'	1.7'	9'	5.2'	40	2.1'	1.8'	4'	6.9'	39	2.9'	1.4'	7'	7.0'	36	2.5'	1.7'
				12'	35	2.1'	2.1'	11'	6.4'	27	2.6'	2.2'	5'	8.7'	25	3.6'	1.7'	9'	9.0'	22	3.2'	2.2'
60W PAR16 NFL	30°	1,300	2,000	3'	144	1.6'	1.6'	3'	1.7'	94	2.2'	1.9'	1'	1.7'	163	2.7'	1.1'	2'	2.0'	115	2.3'	1.5'
				5'	52	2.7'	2.7'	5'	2.9'	34	3.7'	3.1'	2'	3.5'	41	5.5'	2.1'	3'	3.0'	51	3.5'	2.3'
				7'	27	3.8'	3.8'	7'	4.0'	17	5.1'	4.3'	3'	5.2'	18	8.2'	3.2'	4'	4.0'	29	4.6'	3.0'
				9'	16	4.8'	4.8'	9'	5.2'	10	6.6'	5.6'	4'	6.9'	10	10.9'	4.3'	5'	5.0'	18	5.8'	3.8'
75W PAR30 NSP	10°	13,000	3,000	8'	219	1.3'	1.3'	7'	4.0'	186	1.5'	1.3'	3'	5.2'	194	1.9'	0.9'	5'	5.0'	196	1.6'	1.1'
				12'	97	1.9'	1.9'	10'	5.8'	91	2.1'	1.8'	4'	6.9'	109	2.6'	1.3'	7'	7.0'	101	2.2'	1.6'
				16'	55	2.5'	2.5'	13'	7.5'	54	2.7'	2.4'	5'	8.7'	70	3.2'	1.6'	9'	9.0'	61	2.9'	2.0'
				20'	35	3.1'	3.1'	16'	9.2'	36	3.4'	2.9'	6'	10.4'	49	3.6'	1.9'	11'	11.0'	41	3.5'	2.4'
75W PAR30 NFL	25°	3,800	3,000	6'	106	2.7'	2.7'	6'	3.5'	69	3.6'	3.1'	2'	3.5'	119	4.2'	1.8'	4'	4.0'	84	3.7'	2.5'
				8'	59	3.5'	3.5'	8'	4.6'	39	4.8'	4.1'	3'	5.2'	53	6.2'	2.7'	5'	5.0'	54	4.7'	3.1'
				10'	38	4.4'	4.4'	10'	5.8'	25	6.0'	5.1'	4'	6.9'	30	8.3'	3.5'	6'	6.0'	37	5.6'	3.8'
				12'	26	5.3'	5.3'	12'	6.9'	17	7.2'	6.1'	5'	8.7'	19	10.4'	4.4'	7'	7.0'	27	6.5'	4.4'
90W PAR38 NSP	9°	19,500	2,500	10'	195	1.6'	1.6'	8'	4.6'	198	1.7'	1.5'	4'	6.9'	152	2.6'	1.3'	6'	6.0'	192	1.9'	1.3'
				15'	87	2.4'	2.4'	12'	6.9'	88	2.5'	2.2'	6'	10.4'	60	3.8'	1.9'	9'	9.0'	85	2.9'	2.0'
				20'	49	2.4'	2.4'	16'	9.2'	49	3.4'	2.9'	8'	13.9'	38	5.1'	2.5'	12'	12.0'	48	3.8'	2.7'
				25'	31	3.9'	3.9'	20'	11.5'	32	4.2'	3.6'	10'	17.3'	24	6.4'	3.1'	15'	15.0'	31	4.8'	3.3'
90W PAR38 SP	12°	14,500	2,500	8'	227	1.7'	1.7'	7'	4.0'	192	2.0'	1.7'	3'	5.2'	201	2.6'	1.3'	5'	5.0'	205	2.1'	1.5'
				12'	101	2.5'	2.5'	10'	5.8'	94	2.8'	2.4'	4'	6.9'	113	3.5'	1.7'	7'	7.0'	105	3.0'	2.1'
				16'	57	3.4'	3.4'	13'	7.5'	56	3.7'	3.2'	5'	8.7'	73	4.3'	2.1'	9'	9.0'	63	3.8'	2.7'
				20'	36	4.2'	4.2'	16'	9.2'	37	4.5'	3.9'	6'	10.4'	50	5.2'	2.5'	11'	11.0'	42	4.7'	3.3'
90W PAR38 NFL	28°	4,500	2,500	6'	125	3.0'	3.0'	5'	2.9'	117	3.4'	2.9'	2'	3.5'	141	4.9'	2.0'	3'	3.0'	177	3.2'	2.1'
				8'	70	4.0'	4.0'	7'	4.0'	60	4.8'	4.0'	3'	5.2'	63	7.4'	3.0'	5'	5.0'	64	5.3'	3.5'
				10'	45	5.0'	5.0'	9'	5.2'	36	6.1'	5.2'	4'	6.9'	35	9.8'	4.0'	7'	7.0'	32	7.4'	4.9'
				12'	31	6.0'	6.0'	11'	6.4'	24	7.5'	6.3'	5'	8.7'	23	12.3'	5.0'	9'	9.0'	20	9.6'	6.3'
90W PAR38 WFL	55°	2,250	2,500	6'	63	6.2'	6.2'	6'	3.5'	41	9.2'	7.2'	2'	3.5'	70	44.5'	4.2'	3'	3.0'	88	8.6'	4.4'
				7'	46	7.3'	7.3'	7'	4.0'	30	10.7'	8.4'	3'	5.2'	31	66.8'	6.2'	4'	4.0'	50	11.4'	5.9'
				8'	35	8.3'	8.3'	8'	4.6'	23	12.2'	9.6'	4'	6.9'	18	89.1'	8.3'	5'	5.0'	32	14.3'	7.4'
				9'	28	9.4'	9.4'	9'	5.2'	18	13.7'	10.8'	5'	8.7'	11	111.3'	10.4'					
120W PAR38 NSP	10°	25,000	3,000	10'	250	1.7'	1.7'	8'	4.6'	254	1.9'	1.6'	4'	6.9'	195	2.9'	1.4'	6'	6.0'	246	2.1'	1.5'
				15'	111	2.6'	2.6'	12'	6.9'	113	2.8'	2.4'	6'	10.4'	87	4.3'	2.1'	9'	9.0'	109	3.2'	2.2'
				20'	63	3.5'	3.5'	16'	9.2'	63	3.7'	3.2'	8'	13.9'	49	5.7'	2.8'	12'	12.0'	61	4.2'	3.0'
				25'	40	4.4'	4.4'	20'	11.5'	41	4.7'	4.0'	10'	17.3'	31	7.2'	3.5'	15'	15.0'	39	5.3'	3.7'
120W PAR38 FL	30°	4,600	3,000	6'	139	3.2'	3.2'	5'	2.9'	130	3.7'	3.1'	2'	3.5'	156	5.5'	2.1'	3'	3.0'	196	3.5'	2.3'
				8'	78	4.3'	4.3'	7'	4.0'	66	5.1'	4.3'	3'	5.2'	69	6.2'	3.2'	4'	4.0'	71	5.8'	3.8'
				10'	50	5.4'	5.4'	9'	5.2'	40	6.6'	5.6'	4'	6.9'	39	10.9'	4.3'	5'	5.0'	22	8.1'	5.3'
				12'	35	6.4'	6.4'	11'	6.4'	27	8.1'	6.8'	5'	8.7'	25	13.7'	5.4'	6'	6.0'	36	10.4'	6.8'

22OR2 Alcyon Line Voltage

Open Ring PAR20

LAMP

	Beam Spread (To 50% CBCP)	CBCP	Rated Life (Hrs.)	D	FC	L	W	D	C	FC	L	W	D	C	FC	L	W	D	C	FC	L	W
120W PAR38 WFL	55°	2,000	3,000	4'	125	3.7'	3.7'	3'	1.7'	144	4.0'	3.2'	1'	1.7'	250	10.7'	1.9'	3'	3.0'	79	7.2'	4.0'
				6'	56	5.6'	5.6'	5'	2.9'	52	6.7'	5.4'	2'	3.5'	63	21.5'	3.7'	4'	4.0'	44	9.5'	5.3'
				8'	31	7.5'	7.5'	7'	4.0'	27	9.4'	7.5'	3'	5.2'	28	32.2'	5.6'	5'	5.0'	28	11.9'	6.6'
				10'	20	9.3'	9.3'	9'	5.2'	16	12.1'	9.7'	4'	6.9'	16	42.9'	7.5'	6'	6.0'	20	14.3'	7.9'
250W PAR38 SP	10°	46,500	4,500	12'	323	2.1'	2.1'	12'	6.9'	210	2.8'	2.4'	6'	10.4'	161	4.3'	2.1'	6'	6.0'	457	2.1'	1.5'
				16'	182	2.8'	2.8'	16'	9.2'	118	3.7'	3.2'	8'	13.9'	91	5.7'	2.8'	8'	8.0'	257	2.8'	2.0'
				20'	116	3.5'	3.5'	20'	11.5'	76	4.7'	4.0'	10'	17.3'	58	7.2'	3.5'	10'	10.0'	164	3.5'	2.5'
				24'	81	4.2'	4.2'	24'	13.9'	52	5.6'	4.8'	12'	20.8'	40	8.6'	4.2'	12'	12.0'	114	4.2'	3.0'
250W PAR38 FL	30°	9,000	4,500	8'	141	4.3'	4.3'	8'	4.6'	91	5.9'	5.0'	3'	5.2'	125	8.2'	3.2'	4'	4.0'	199	4.6'	3.0'
				10'	90	5.4'	5.4'	10'	5.8'	58	7.3'	6.2'	4'	6.9'	70	10.9'	4.3'	5'	5.0'	127	5.8'	3.8'
				12'	63	6.4'	6.4'	12'	6.9'	41	8.8'	7.4'	5'	8.7'	45	13.7'	5.4'	6'	6.0'	88	6.9'	4.5'
				14'	46	7.5'	7.5'	14'	8.1'	30	10.2'	8.7'	6'	10.4'	31	16.4'	6.4'	7'	7.0'	65	8.1'	5.3'

