





Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

Example: CHTGG8.5S0

CH	T			8.5							
<u>Seri</u>	es In	put Voltage	Output Voltage	<u>Unit Size</u>	Battery Time	Nol	Qty Ckt Breakers	Breakers On	Qty Nol Ckt	Nol Voltage	Qty Nol 2nd
	sis CHT stem for ency g	G - 120/240 V J - 277 V L - 120/208 V	G - 120/240 V J - 277 V L - 120/208 V Y - 120/277 V	8.5 – 8.5 kVA	S – 90 min Y – 20 min	0 - None 1 - Yes T - NOL w/ TDT	00X - Hardwire 01X - 1 OCB 02X - 2 OCB 03X - 3 OCB 04X - 4 OCB 20X - 20 OCB 	2nd Voltage 00 - 2nd Voltage Hardwire or No 2nd Voltage 01 02 03 .	Breakers A - 1 B - 2 C - 3 D - 4 E - 5 F - 6 G - 7 H - 8 I - 9 J - 10 K - 11 L - 12 M - 13 N - 14	1 - First 2 - Second 3 - Both 0 - No NOL	Voltage A - 1 B - 2 C - 3 D - 4 E - 5 F - 6 G - 7 H - 8 I - 9 J - 10 K - 11 L - 12 M - 13 N - 14
Footnote Optimum operating temperature of batteries is 77°F (25°C). Temperatures above 85°F (30°C) adversely impact battery life.					O10A - 10 OCBA (maximum pole spaces 20)		O - 15 P - 16 Q - 17 R - 18 S - 19 T - 20 Z - None		O - 15 P - 16 Q - 17 R - 18 S - 19 Z - No NOL		

unit check list

Catalog No:							
VA Rating: 8500							
Battery Type: Sealed Lead Calcium							
Operating Time: 90/20/10 Min.							
Utility Input:VAC, Single Phase							
Output Circuit Breakers:	Normally Normally Trip Alarm						
Qty:AC Volts: Amps:	Normally Normally Trip Alarm ON OFF YES NO						
Qty:AC Volts: Amps:	ON OFF YES NO						
Qty:AC Volts: Amps:	ON OFF YES NO						
Qty:AC Volts: Amps:	ON OFF YES NO						
Remarks:							
Nemarks.							



CHT Synthesis Single Phase Uniterruptible Power Supply

8.5 KVA

codes and standards

· UL 924 listed

construction

- Free standing, NEMA 1 enclosure with lockable control access panel.
- · Double conversion, no interruption.
- · Solid state pulse width modulated inverter.
- Internal, make before break maintenance by-pass.
- Standard, UL 924 compliant, 90 minute battery back up.
- UL 924 auxiliary equipment 10 and 20 minute back up available.
- · Microprocessor control and diagnostic system.
- · LCD readout system status panel.
- · Local 25 event logging/display.
- · User programmable automatic testing.
- · Load integrity testing.
- · Fault annunciating audible alarm.
- · Current limiting start sequence.
- Optional output circuit breakers (OCB) and circuit breakers with trip alarm (OCBA).
- Optional normally off load (NOL) energizes only during power outage, normally off load with time delay (TDT) also available.
- Seismic anchoring compatible.
- 87% throughput efficiency, 85% emergency efficiency.
- Operating temperature range 32°F (0°C) to 104°F (40°C)1.
- · Fault current rating 42 kAIC.
- · Audible noise less than 50 dB at 3 ft on "A" weighted scale.
- · Automatic low battery voltage disconnect.

application

- The solid state pulse width modulated (PWM) inverter offers enhanced load compatibility.
- It operates incandescent, magnetic and electronic ballast fluorescent, high power factor compact fluorescent and high intensity discharge (HID) luminaries.
- Provides conditioned, uninterruptible power for other types of critical loads.
- · Consult factory for non-lighting load applications.

electronics - input

- · Input power factor correcting to 0.99.
- Frequency range 60 Hz, ±2.5 Hz.
- Input harmonic current distortion < 5% THD.
- · UL1449, ANSI/IEEE C62.41 surge suppression.

electronics - output

- · Sine wave output.
- · Voltage regulation ±2%.
- Frequency regulation synchronized to utility, free running 60 Hz. ±0.5%.
- Output voltage distortion maximum 3% THD with linear load.
- · Load power factor capability 0.7 lead to 0.7 lag.
- · Overload capability 125% for 10 seconds.


warranty

- Standard warranty: (requires execution of factory start-up within 120 days of shipment) Chloride will provide parts and on-site labor for the first 12 months following start-up of the product, and parts only for an additional 12 months. If factory start-up is not executed within 120 days of shipment. Chloride will provide a parts warranty for 12 months from the date of shipment.
- Extended warranty available: consult factory for extended warranty and service option.

Synthesis Single Phase Uniterruptible Power Supply

8.5 KVA

dimensions



system input/output

System Rating (kW/kVA)	8.5
Input Volt. (V) : Input Curr. (A)	120 : N/A
	120/240 : 50.1
	277 : 43.3
	120/208 : 57.7
Output Volt. : Output Current*	120 : N/A
	120/240 : 70.8/35.4
	277 : 30.7
	120/208 : 70.8/40.9
	120/277 : 70.8/30.7
OCB Pole Spaces Available	
Without Trip Alarm	20
With Trip Alarm	10
Heat Rejection (btu/hr)	4058
Weight (lbs)	
Electronics	1000
Empty Battery Cabinet	400
90 Min Battery	1500
20 Min Battery	480

^{*} Multi-voltage total loads not to exceed system rating.

