


Industrial

1FD general purpose

T8 or T12 Slimline



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Day-Brite / CFI general purpose industrial is a luminaire providing 10% uplight and 13° crosswise shielding.

Ordering guide

Example: 1FD259-PP-UNV-1/2-EB

Family	No. of Lamps per Cross Section	Lamp Type	Reflector Options	Voltage	Options
1FD	2	—	—	—	
1FD Industrial (10% uplight)	(not included) 2	48 38W T12 Slimline (48") 59 59W T8 Slimline (96") 96 75W T12 Slimline (96")	PP Painted Polyester PPS Painted Polyester solid top	UNV Universal voltage 120/277V 120 120V 277 277V 347 347V	1/2 One 2-lamp ballast EB Electronic ballast, <10% THD E7 B60 emerg. ballast, 600-700 lumens, 120/277V E5 B50 emerg. ballast, U.S. or Canada market, 1100-1400 lumens, UNV E5CAN B50-CAN emerg. ballast, Canada market, 1100-1400 lumens, 120/347V E5ST B50ST emerg. ballast w/self test, 1100-1400 lumens, UNV GLR Fusing, fast blow Power Connect modular wiring available, see sheet 1604-OA for details

Accessories (order separately)

- **CS-400** Rigid Canopy
- **CS-500** 42" Top Swivel Canopy
- **CS-12** 12" Stem
- **CS-18** 18" Stem
- **CS-24** 24" Stem
- **CS-30** 30" Stem
- **CS-36** 36" Stem
- **CS-48** 48" Stem
- **FL-111** Sliding hanger, conduit/stem/screw
- **FL-117** Hook, chain (requires FL-111)
- **FL-119** Hook, messenger cable (requires FL-111)
- **FL-123** 5' chain (w/S-hooks) set
- **FL-173** 4' wire guard (use 2 for 8')
- **FL-3** Channel coupling
- **N-3381** Universal joint aligner, octagonal box, 3/4" I.P.S.

1FD General purpose industrial

T8 or T12 Slimline


Construction/Finish

- Housing and reflector are multi-stage phosphate treated for maximum corrosion resistance and finish coat is high reflectance baked white enamel.
- Multiple knockouts for convenient installation.
- Heavy duty channel of code gauge die formed steel.
- Reflectors have stiffening ribs for rigidity and provide 13° crosswise shielding.
- Twist-lock reflector thumb screws.
- Continuous rows utilize a simple concealed coupling, FL-3 (optional).
- Apertured reflector (11-13% uplight) standard.
- Solid top reflector (no uplight) optional.


Electrical

- cULus listed for direct mounting on low density ceilings and damp locations.
- Spring-loaded lampholders provide positive lamp engagement and electrical contact.

Dimensions



DIM "A"		
4' Channel	(1220mm)	48"
8' Channel	(2439mm)	96"



1FD General purpose industrial

T8 or T12 Slimline

Photometry

1FD 8' 2 Lamp F96T8

Efficiency – 93.6%

LER – 85

TER – 51

		Candlepower				Light Distribution				Average Luminance			
Catalog No.	1FD259-PP-1/2-EB	Angle	End	45	Cross	Degrees	Lumens	% Lamp	% Luminaire	Angle	End	45'	Cross
Test No.	ITL42342D1	0	3006	3006	3006	0-30	2394	20.6	22.1	45	3786	4076	4511
S/MH	1.4	5	3001	2991	3039	0-40	3986	34.4	36.7	55	3725	4419	4284
Lamp Type	F96T8	15	2910	2936	2985	0-60	7404	63.8	68.2	65	3550	4071	4007
Lumens/Lamp	5800	25	2716	2770	2829	0-90	9660	83.3	89.0	75	3115	4080	2916
Ballast Factor	0.85	35	2442	2535	2634	0-180	10858	93.6	100.0	85	2290	2024	1832
Input Watts	109	45	2079	2238	2477								
		55	1659	1968	1908								
		65	1165	1336	1315								
		75	626	820	586								
		85	155	137	124								
		95	17	35	38								
		105	124	49	116								
		115	262	30	38								
		125	400	46	34								
		135	524	167	53								
		145	626	313	196								
		155	707	441	370								
		165	769	723	575								
		175	796	783	795								

Coefficients of Utilization												
EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)												
pcc	80			70			50					
pw	70	50	30	70	50	30	50	30				
RCR												
0	109	109	109	105	105	105				97	97	
1	98	94	91	95	91	88				85	82	
2	90	81	75	85	79	72				73	68	
3	81	71	64	78	68	61				65	58	
4	73	63	55	70	60	53				56	51	
5	68	56	47	65	54	46				51	44	
6	63	50	41	59	48	40				46	39	
7	57	45	36	56	44	35				41	34	
8	54	40	33	52	40	33				38	30	
9	50	38	29	47	36	28				34	28	
10	46	34	27	45	34	27				32	26	

Comparative yearly lighting energy cost per 1000 lumens – **\$2.82** based on 3000 hrs. and \$.08 pwr KWH.

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.



Some luminaires use fluorescent or high intensity discharge (HID) lamps that contain small amounts of mercury. Such lamps are labeled, "Contain Mercury" and/or the symbol "HG". Lamps that contain mercury must be disposed of in accordance with local requirements. Information regarding lamp recycling and disposal can be found at www.lamprecycle.org

