Project	Catalog #	Туре	
Prepared by	Notes	Date	



# **Metalux**

# **22RTC**

2x2 Center Basket Troffer

## **Typical Applications**

• Commercial Office Spaces • Schools • Healthcare • Retail Merchandising Areas

# Interactive Menu

- Photometric Data page 2
- · Product Warranty

# **Product Certification**







# **Product Features**




# **Top Product Features**

- Shallow plenum under 2.5" deep RTC fits the most challenging spaces
- Standard and high lumen models up to 7000 lumens
- Up to 133 lumens per watt delivering up to 56% energy savings
- · Stock SKU available in 3500K and 4000K
- · UNV driver and 0-10V dimming standard

# Discontinued - While supplies last


# **Dimensional and Mounting Details**



## Stock SKU and Rated Performance

		ODI		Delivered		F#6	Input current (A)	
Catalog Number	UPC	CRI (Min)	ССТ	Nominal Lumens	Watts *	Efficacy (Im/W)	120V	277V
22RTC3435	080083802586	80	3500K	3638	28.6	127	25	11
22RTC3440	080083802593	80	4000K	3632	28.6	127	.25	.11
22RTC4835	080083802609	80	3500K	4780	37.7	127	.32	.14
22RTC4840	080083802616	80	4000K	4889	38.1	128	.32	

<sup>\*</sup> Watts of standard 0-10V product.





Metalux 22RTC LED

# **Product Specifications**

## Construction

- 2-1/2" housing constructed of die-formed, code gauge cold rolled steel
- Full length die-formed stiffeners and unibody endplate for added strength
- · Four auxiliary fixture end suspension points provided
- Wireway cover removable without tools
- Endplates provided with Grid-Lock feature for safety

## **LED and Light Engine**

- LED's available in 3500K or 4000K at 80 CRI minimum
- TM21 life at 60,000 hours up to L75
- · Drivers available in 120-277V
- 0-10V dimming to 10% standard

#### **Finish**

- · Multistage, iron phosphate pretreatment
- · 90% reflective, matte white enamel finish
- · Full fixture housing painted after fabrication

## Compliance


- · IC rated for insulation contact
- · cULus listed for damp locations
- · RoHS compliant
- · Tested to IESNA LM-79 and LM-80
- · Stated life tested to TM21 standards
- Can be used for State of California Title 24 high efficacy luminaire
- · NEMA 410 compliant

## Warranty

· Five-year warranty standard.

# Discontinued - While supplies last

# **Photometric Data**




## 22RTC3435

Electronic Driver Linear LED 3500K

Spacing criterion: (II) 1.21 x mounting height,

 $(\perp)$  1.28 x mounting height

Lumens: 3584.4 Input Watts: 27.8W Efficacy: 128.8 lm/W Test Report: 22RTC3435.IES



## 22RTC4835

Electronic Driver Linear LED 3500K

Spacing criterion: (II) 1.21 x mounting height,

**View IES files** 

 $(\perp)$ 1.28 x mounting height

Lumens: 4670.6 Input Watts: 36.3W Efficacy: 128.5 lm/W Test Report: 22RTC4835.IES

# **Energy and Performance Data**

# CCT Table

Approximate Color Temperature Multiplier			
3500K	1.0		
4000K	1.02		

## **Load Data**

Thd	14%
Power Factor	0.96
Weight	8.2 lbs.
Low Temp Start	-20°C

## **Shipping Data**

Size	Wt.	Pallet (30" x 53")
2x2	10.8 lbs.	26