

# LUMEC

by @signify

Urban

Capela Series

CPLM-CPLS



Inspired by movement / Inspired by the splendor of movement, the **Capella** is one of the most adaptable luminaires on the market. With it's graceful curves and sweeping lines it contributes to the beautification of any environment and enhances the visual impact of any project.

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

## CPLM


### Ordering guide sample

Luminaire	Lamp	Optical System	Voltage	Options	Finish*
CPLM	250 HPS	TH2F	120	HS	NP

The specially formulated Lumital powder coat finish is available in a range of many standard colors.  
\* Consult Lumec's Color Chart for complete specifications.

## Luminaires

Conform to the UL 1598 and CSA C22.2 No. 250.0-08 standards.



FLAT LENS OPTICS

**Weight:** 47 lbs (21.3 kg)

**EPA:** 0.83 sq. ft.

SAG LENS OPTICS

# CPLM-CPLS Urban

## Capela Series

### Lamp / HID

Wattage	TH2 / TH3	TH2F / TH3F
50 MH, medium	■	■
70 MH, medium	■	■
100 MH, medium	■	■
150 MH, medium	■	■
200 MH, mogul	■ <sup>3</sup>	■ <sup>3</sup>
320 MH, mogul	■	■ <sup>2</sup>
175 PSMH, mogul	■	N/A
250 PSMH, mogul	■	■ <sup>2</sup>
400 PSMH, mogul	■	N/A
35 HPS, mogul	■	■
50 HPS, mogul	■	■ <sup>1</sup>
70 HPS, mogul	■	■ <sup>1</sup>
100 HPS, mogul	■	■ <sup>1</sup>
150 HPS, mogul	■	■ <sup>1</sup>
200 HPS, mogul	■	■
250 HPS, mogul	■	■
400 HPS, mogul	■	■

■ Available. N/A: Not available.

1. Use only with ED17 medium base lamp.
2. Use only with short version LCL 5-3/4" of T15 mogul base lamp.
3. Use only with short version LCL 5" of T15 mogul base lamp.

### Optical System / HID

(Lamps not included)



#### FLAT LENS optics

Sealed optical chamber consisting of an hydroformed reflector permanently sealed on a flat tempered-glass lens.

**TH2F** Full cut-off (II)

**TH3F** Full cut-off (III)



#### SAG LENS optics

Sealed optical chamber consisting of an hydroformed reflector permanently sealed on a sagged tempered-glass lens.

**TH2** Cut-off (II)

**TH3** Cut-off (III)

### Voltage

HID
120
208
240
277
347
480

### Options

**HS** House shield

**PH8** Quarter-turn photoelectric cell

**SAR** Short arm for round pole  
(E.P.A.: 0.25 sq. ft. / Weight: 2.6 lbs (1.2 kg))

# CPLM-CPLS Urban

## Capella Series

### CPLS


Ordering guide sample

Luminaire	Lamp	Optical System	Voltage	Options	Finish*
CPLS	150 HPS	2HF	120	PH7	NP

The specially formulated Lumital powder coat finish is available in a range of many standard colors.  
\* Consult Lumec's Color Chart for complete specifications.

### Luminaires

Conform to the UL 1598 and CSA C22.2 No. 250.0-08 standards.



**Weight:** 30 lbs (13.6 kg)  
**EPA:** 0.47 sq. ft.



### Lamp / HID

Wattage	TH2 / TH3	TH2F / TH3F
50 MH, medium	■	■
70 MH, medium	■	■
100 MH, medium	■	■
150 MH, medium	■	■
175 MH, medium	■	■
35 HPS, medium	■	■
50 HPS, medium	■	■
70 HPS, medium	■	■
100 HPS, medium	■	■
150 HPS, medium	■	■

■ Available. N/A : Not available.

### Optical System / HID

(Lamps not included)

	<b>FLAT LENS optics</b> Sealed optical chamber consisting of an hydroformed reflector permanently sealed on a flat tempered-glass lens.	<b>2HF</b> Full cut-off (II)
	<b>SAG LENS optics</b> Sealed optical chamber consisting of an hydroformed reflector permanently sealed on a sagged tempered-glass lens.	<b>TH2</b> Cut-off (II)

### Voltage

HID
120
208
240
277
347
480

### Options

- HS** House shield
- PH** Photoelectric cell

# CPLM-CPLS Urban

## Capela Series

### Assembly examples

