





Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

Day-Brite / CFI T-Grid LED troffer is an energy efficient low profile luminaire offering excellent performance for general lighting applications such as offices, schools, healthcare, or retail. Featuring a frosted prismatic lens to enhance visual comfort, the T-Grid LED Troffer utilizes highly reliable and efficient Philips LED platform boards and dimmable driver, enabling market leading efficiency in its category.

Ordering guide

Example: 2TG30L840-2-FS-02F-UNV-DIM

	G Grid	20L 2000 nominal	830	-	2] _	_								
LED	G Grid		830	00.681	i e				-		_		-		
		delivered lumens 30L 3000 nominal delivered lumens 38L 3800 nominal delivered lumens 45L 4500 nominal delivered lumens	835 840 850	80 CRI, 3000K 80 CRI, 3500K 80 CRI, 4000K 80 CRI, 5000K	2 2'		FS Flat Steel	02F 12F 19F	Pattern 12, .100" nominal diffuse 50% DB 12 .125" nominal diffuse 50% DB 19 .156" nominal diffuse 50%	UNV 347	Universal Voltage 120-277V 347V	DIM	0-10V dimming Step dimming to 40% input power	F1 F2 F1/D F2/5W EMLED' 1W 2W 3W	3/8" flex, 3 wire, 18 gauge 6' 3/8" flex, 4 wire, 18 gauge 6' 3/8" twin flex, 3 wire, 18 gauge 6', for dimmable luminaires 3/8" single flex, 5 wire, 18 gauge 6', for dimmable luminaires Integral emergency battery pack 1—way gasket between lens & door frame (not avail. for RA door frame) 1—way & gasket between door frame & housing 2—way & gasket between housing 2—way & gasket between housing 2—way & gasket between housing 4. ceiling (field installed) Fusing, fast blow Chicago Plenum
			delivered lumens 45L 4500 nominal delivered	delivered lumens 45L 4500 nominal delivered	delivered lumens 45L 4500 nominal delivered	delivered lumens 45L 4500 nominal delivered	delivered lumens 45L 4500 nominal delivered	delivered lumens 45L 4500 nominal delivered	delivered lumens 45L 4500 nominal delivered	delivered lumens 45L 4500 nominal delivered	delivered lumens 45L 4500 nominal delivered	delivered lumens 45L 4500 nominal delivered lumens W 2W 3W			

Footnotes

1 Emergency pack mounted in enclosure on top of fixture housing. Delivers 1100 nominal lumens in DC mode.

Accessories (order separately)

- FMA22 2'x2' "F" mounting frame for NEMA "F" mounting
- FKTG822 Flange conversion kit, 2'x2'



2TG T-Grid LED troffer 2x2

2000, 3000, 3800 or 4500 lumens

Application

- High efficacy long life solid state lighting platform.
- General lighting distribution is excellent for ambient lighting.
- High CRI source provides excellent color rendering.
- LEDs are an excellent source for use with controls since frequent switching does not affect the life of the light source.

Construction/finish

- A quality low-profile troffer with specification features for NEMA "G" grid, NEMA "NFG" narrow face grid, NEMA "GR" grid regressed, or NEMA "F" flange ceiling types.
- 3" nominal housing depth, 3-3/16" maximum depth.
- Smooth rolled edges on all four sides for easy handling.
- Die-formed one piece housing includes stiffening embosses and provides increased rigidity.
- Housing is multi-stage phosphate treated for maximum corrosion resistance and finish coat is high reflectance baked white enamel.
- · Integral baffling system to prevent light leaks.
- 2 sets of integral grid clips (wraparound and fold-out) for maximum mounting flexibility.

- Integral wire hanger holes for independent wire suspension.
- Embosses with holes provided in housing end for screwing to T-bar if desired.
- 7/8" K.O.'s provided in each end cap for through wiring.
- Factory installed access plate in housing top includes 7/8" hole with rolled edge and 7/8"
- Carton includes integral carrying handle for easy handling.

Electrical


- · Standard 0-10V dimming.
- Driver and LED boards are accessible from below. LED boards are individually replaceable if required.
- Five-year luminaire limited warranty including LED boards and driver. Visit www.philips. com/warranties for complete warranty information
- High efficiency LEDs have 50,000 hour rated life (defined by testing at 70% lumen maintenance (L70)), based on 25°C ambient operating temperature.
- $\boldsymbol{\cdot}\;$ cETLus listed to UL and CSA standards, suitable for damp location.

Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.


Enclosure

- Full "C" channel door frames for improved lens support and reduced shipping damage.
- Flat steel door frame features smooth rolled edges inside and outside.
- · All door frames have mitered corners.
- All door frames use T-hinges and can be hinged and latched from either side.
- Opposable spring loaded latches are standard for easy operation and consistent retention.


Dimensions



*EMLED option adds 1-3/4" to overall height



Wraparound Grid Clips



Fold-Out Grid Clips

2TG T-Grid LED troffer 2x2

2000, 3000, 3800 or 4500 lumens

Photometry

2x2 T-Grid LED troffer, 2000 nominal delivered lumens

Light Distribution Average Luminance Angle 45 55 Degrees 0-30 % Luminaire 32.7 **End** 2442 Cross 2551 Lumens 2472 747 0-40 0-60 0-90 1191 52.1 1968 1977 2058 1915 83.7 65 75 1572 1427 1518 1384 1644 1618 2287

100.0

Catalog No.	2TG20L840-2-FS-02F-UNV
Test No.	32630
S/MH	1.2
Source	LED
Lumens/Lamp	2287
Input Watts	23

Comparative yearly lighting energy cost per 1000 lumens – **\$2.42** based on 3000 hrs. and \$.08 pwr KWH. Actual rates and usage may vary.

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology

Photometric values based on test performed in compliance with LM-79.

Angle	End	45	Cross
0	983	983	983
5	978	978	979
15	933	935	937
25	844	849	856
35	703	709	709
45	526	532	549
55	344	345	359
65	202	195	211
75	112	109	127
85	42	42	49

Candlepower

Coefficients of Utilization

EFFECT	IVE FLOOF	R CAVIT	Y REFLECTA	NCE 20 P	ER (pfc	=0.20)		
рсс		80			70		5	0
pw	70	50	30	70	50	30	50	30
RCR								
0	118	118	118	115	115	115	111	111
1	109	105	101	107	103	98	97	94
2	100	93	85	97	91	84	86	81
3	92	81	75	90	81	73	78	71
4	84	72	65	82	71	64	69	63
5	78	66	57	76	65	56	63	56
6	72	59	51	70	58	51	56	50
7	68	55	46	66	54	46	52	45
8	63	50	41	61	48	41	47	40
9	58	46	38	57	46	38	44	38
10	55	42	34	54	41	34	40	34

1831

2x2 T-Grid LED troffer, 3000 nominal delivered lumens

LER - 99

Catalog No.	2TG30L840-2-FS-02F-UNV
Test No.	32628
S/MH	1.2
Source	LED
Lumens/Lamp	2994
Input Watts	32.7

1000 lumens - \$2.61 based on 3000 hrs. and \$.08 pwr KWH. Actual rates and usage may vary.

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology

Photometric values based on test performed in compliance with LM-79.

Candle	power		
Angle	End	45	Cross
0	1285	1285	1285
5	1279	1279	1281
15	1220	1223	1228
25	1104	1110	1122
35	921	926	947
45	689	696	719
55	449	452	470
65	264	256	277
75	147	142	167
85	55	56	64

Light Dis	tribution		Avera	ige Lur	ninano	e
Degrees	Lumens	% Luminaire	Angle	End	45°	Cross
0-30 0-40	977 1558	32.7 52.0	45 55	3201 2575	3234 2589	3342 2694
0-40	2506	83.7	65	2052	1992	2153
0-90	2994	100.0	75	1865	1803	2124
			85	2063	2092	2395

Coefficients of Utilization

EFFECT	IVE FLOOI	R CAVIT	Y REFLECTA	NCE 20 P	ER (pfc	=0.20)		
рсс		80			70		5	0
pw	70	50	30	70	50	30	50	30
RCR								
0	118	118	118	115	115	115	111	111
1	109	105	101	107	103	98	97	94
2	100	93	85	97	91	84	86	81
3	92	81	73	90	81	72	78	71
4	84	72	65	82	71	64	69	63
5	78	66	57	76	65	56	63	56
6	72	59	51	70	58	51	56	50
7	68	55	46	66	54	46	52	45
8	63	50	41	61	48	41	47	40
9	58	46	38	57	46	38	44	36
10	55	41	34	54	41	34	40	34

2TG T-Grid LED troffer 2x2

2000, 3000, 3800 or 4500 lumens

Photometry

2x2 T-Grid LED troffer, 3800 nominal delivered lumens

Light Distribution

		Candle	power			Light	Distrib	oution			Ave	rage Lui	minan	ce
Catalog No.	2TG38L840-2-FS-02F-UNV	Angle	End	45	Cross	Degr	ees l	Lumens	% Lumii	naire	Angle	End	45°	Cross
Test No.	32631	0	1586	1586	1586	0-30		1206	32.7		45	3942	3990	4130
S/MH	1.2	5	1578	1578	1580	0-40 0-60		1922 3091	52.0 83.7		55 65	3177 2534	3193 2456	3330 2660
Source	LED	15 25	1505 1362	1509 1369	1514 1384	0-90		3693	100.		75	2301	2219	2625
Lumens/Lamp	3693	35	1136	1143	1169						85	2545	2588	2951
Input Watts	43.5	45 55	848 555	859 557	889 581	Coeff	icients	of Uti	lization					
		65	326	316	342	EFFECT	IVE FLOO		REFLECTA	NCE 20 P).20)		
Comparative year	ly lighting energy cost per	75	181	175	207	pcc		80			70		5	
	1.82 based on 3000 hrs. and	85	68	69	78	pw RCR	70	50	30	70	50	30	50	30
	tual rates and usage may vary.					0	118	118	118	115	115	115	111	111
3.00 pwi kwn. Ac	tudi fates affu usage filay vary.					1	109	105	101	107	103	98	97	94
The photometric r	esults were obtained in the					2	100	93	85	97	91	84	86	81
	ory which is NVLAP accredited by					3	92	81	75	90	81	73	78	71
	ute of Standards and Technology.			/		4	84	72	65	82	71	64	69	63
the National Institu	ute of Standards and Technology.					5	78	66	57	76	65	56	63	56
Dl44-1						6	72	59	51	70	58	51	56	50
	es based on test performed in					8	68 63	55 50	46 41	66 61	54 48	46 41	52 47	45 40
compliance with L	IVI-/9.					9	58	46	38	57	46	38	47	38
						10	55	42	34	54	41	34	40	34

2x2 T-Grid LED troffer, 4500 nominal delivered lumens

LER - 88

		Candle	oower			Light	Distrib	ution			Ave	rage Lur	minan	ce
Catalog No.	2TG45L840-2-FS-02F-UNV	Angle	End	45	Cross	Degre	ees L	.umens	% Lumir	naire	Angle	End	45°	Cross
Test No.	32395	0	1968	1968	1968	0-30		1489	32.7		45	4852	4887	5031
S/MH	1.2	5	1958	1957	1960	0-40 0-60		2366 3805	52.0 83.6		55 65	3959 3202	3952 3111	4127 3327
Source	LED	15 25	1864 1677	1867 1687	1873 1702	0-90		4550	100.0		75	2872	2789	3167
Lumens/Lamp	4551	35 45	1392 1044	1401 1052	1428 1083	C (C		- 6 1 143	l::		85	3038	3066	3468
Input Watts	51.5	55	691	690	720				lization					
		65	412	400	428	EFFECT	IVE FLOOI		/ REFLECTA	NCE 20 P	ER (pfc=).20)		
Comparative yearly	y lighting energy cost per	75	226	220	250	pcc	70	80	20	70	70	20	50	
	.79 based on 3000 hrs. and	85	81	81	92	pw RCR	70	50	30	70	50	30	50	30
	tual rates and usage may vary.					n RCR	119	119	119	116	116	116	111	111
J.OO PWI KWIII. ACI	tuat rates and usage may vary.					1	109	105	101	107	103	99	98	95
The photometric re	esults were obtained in the					2	100	93	86	98	91	85	87	82
	ory which is NVLAP accredited by					3	92	82	74	90	81	74	78	72
						4	85	73	65	83	72	64	70	63
ine National institt	ute of Standards and Technology.					5	78	66	58	76	65	57	63	56
DI						6	73	60	51	71	59	51	57	50
	s based on test performed in					7	68	55	46	66	54	46	52	45
compliance with L	M-/9.					8	63	50	42	62	49	42	48	41
						9	59	46	38	58	46	38	44	38
						10	55	43	35	54	42	35	41	34

