



Philips CoreLine recessed: easy installation, excellent illumination.

CoreLine recessed

Philips CoreLine recessed delivers on the CoreLine promise of innovative, easy-to-use, high-quality luminaires. It's a high-quality recessed LED that's designed to replace existing recessed luminaires with T8 or T5 technology. This CoreLine family also features an innovative new choice of multiple lumen outputs in one single luminaire, called MultiLumen. Instant energy savings and a longer lifetime, make this is an environmentally-friendly and cost-saving solution. With a quick-connector or Wieland feature, CoreLine RC136B recessed luminaires are quick and easy to install. Also available within the range are Interact Ready luminaires with integrated wireless communications, which are fully compatible with Interact gateways, sensors and software.

Benefits

- MultiLumen: a choice of different lumen outputs in one single luminaire
- New connector offers quick and simple installation
- Energy savings and longer lifetime to reduce operating costs

Features

- MultiLumen: different lumen outputs ranging from 2800 lumen to 4300 lumen in one single luminaire
- Easy connector for faster installation: quick connector or Wieland connector
- Energy efficient and long lifetime: up to 140 lm/W and 50,000 hours @L80 lifetime
- Many flicker-free drivers available: On/off (PSU), dimming (Dali) and integrated wireless connectivity (Interact Ready)
- Office compliant versions (OC) & Non-office compliant versions (NOC)
- High lumen available: up to 6000 lm (OC)
- Optional versions available: Emergency Lighting (EL) & Wieland/Adels connectors (W)

Application

- Offices
- Healthcare
- Education

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Versions



RC136B 31S_37S_43S/840 PSU
W60L60 NOC W3_SPP



RC136B 31S_37S_43S/840 PSD
W30L120 OC _SPP



RC136B 31S_37S_43S/840 PSU
W60L60 OC _SPP



RC136B 28S_34S_40S/830 PSU
W60L60 NOC W3_SPP

CoreLine recessed

Versions

RC136B 31S_37S_43S/840 PSD
W60L60 NOC W5_SPP



RC136B 28S_34S_40S/830 PSD
W60L60 OC _SPP



RC136B 31S_37S_43S/840 PSD
W60L60 OC _SPP



RC136B 28S_34S_40S/830 PSD
W30L120 OC _SPP



CoreLine Recessed



RC136B 31S_37S_43S/840 PSD
W60L60 OC W5_SPP



RC136B 28S_34S_40S/830 PSD
W60L60 OC W5 _SPP



RC136B 28S_34S_40S/830 PSU
W60L60 NOC _SPP



RC136B 31S_37S_43S/840 PSU
W60L60 NOC _SPP



RC136B 31S_37S_43S/840 PSD
W60L60 NOC _SPP




CoreLine recessed

Versions

RC136B 31S_37S_43S/840 PSU
W60L60 OC W3_SPP



Dimensional drawing




Product details

CoreLine Recessed Backside



CoreLine Recessed Backside with connector




Product details

CoreLine Recessed Backside



CoreLine Recessed connector PSD
(dali)



CoreLine Recessed in ceiling



CoreLine_Recessed_RC136B_60x
60



CoreLine Recessed Wileland




CoreLine Recessed



CoreLine Recessed connector PSU
(On/Off)



CoreLine Recessed connector PSU
(On/Off)



CoreLine Recessed Edge




CoreLine recessed

Product details

CoreLine Recessed Edge



CoreLine Recessed connector PSU (On/Off))



CoreLine Recessed Safety Cable



CoreLine Recessed in ceiling



Wieland W5 Dali Connector



General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Service tag	No
Light Technical	
All-in Type	All-in, Multi Lumen
Color rendering index (CRI)	≥80
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Housing Color	White
Approval and Application	
Mech. impact protection code	IK03
Ingress protection code	IP20/44
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Application Conditions	
Suitable for random switching	Yes

General Information

Order Code	Full Product Name	Product family code
910505101241	RC136B 31S_37S_43S/840 PSD W60L60 OCELB3	RC136B
910505101242	RC136B 31S_37S_43S/840 PSU W60L60NOCELB3	RC136B
910505101243	RC136B 31S_37S_43S/840 PSD W60L60NOCELB3	RC136B
910505101256	RC136B 31S_37S_43S/840 PSDW60L60OCELB3W5	RC136B
910505101257	RC136B 31S_37S_43S/840 PSUW60L60OCELB3W3	RC136B
911401881181	RC136B 31S_37S_43S/840 PSU W60L60 NOC W3	-
911401880981	RC136B 31S_37S_43S/840 PSD W30L120 OC	-
911401880481	RC136B 31S_37S_43S/840 PSU W60L60 OC	-
911401881081	RC136B 28S_34S_40S/830 PSU W60L60 NOC W3	-
911401881381	RC136B 31S_37S_43S/840 PSD W60L60 NOC W5	-
911401880681	RC136B 28S_34S_40S/830 PSD W60L60 OC	-
911401880781	RC136B 31S_37S_43S/840 PSD W60L60 OC	-
911401880881	RC136B 28S_34S_40S/830 PSD W30L120 OC	-
910505101244	RC136B 28S_34S_40S/830 PSD W30L120OCELB3	RC136B
910505101245	RC136B 31S_37S_43S/840 PSD W30L120OCELB3	RC136B
911401881581	RC136B 31S_37S_43S/840 PSD W60L60 OC W5	-
911401881481	RC136B 28S_34S_40S/830 PSD W60L60 OC W5	-
911401880281	RC136B 28S_34S_40S/830 PSU W60L60 NOC	-
911401880381	RC136B 31S_37S_43S/840 PSU W60L60 NOC	-
911401880581	RC136B 31S_37S_43S/840 PSD W60L60 NOC	-
911401881281	RC136B 31S_37S_43S/840 PSU W60L60 OC W3	-

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910505101241	RC136B 31S_37S_43S/840 PSD W60L60 OCELB3	4000 K	126 lm/W	3,100 lm	Wide beam
910505101242	RC136B 31S_37S_43S/840 PSU W60L60NOCELB3	4000 K	126 lm/W	3,100 lm	Wide beam
910505101243	RC136B 31S_37S_43S/840 PSD W60L60NOCELB3	4000 K	126 lm/W	3,100 lm	Wide beam
910505101256	RC136B 31S_37S_43S/840 PSDW60L60OCELB3W5	4000 K	126 lm/W	3,100 lm	Wide beam
910505101257	RC136B 31S_37S_43S/840 PSUW60L60OCELB3W3	4000 K	126 lm/W	3,100 lm	Wide beam
911401881181	RC136B 31S_37S_43S/840 PSU W60L60 NOC W3	4000 K	140 lm/W	3,100 lm	Beam angle 100°

CoreLine recessed

Order Code	Full Product Name	Correlated	Luminous	Luminous	Optic
		Color	Efficacy		
		Temperature	(rated)	Flux	type
(Nom)		(Nom)			
911401880981	RC136B 31S_37S_43S/840 PSD W30L120 OC	4000 K	140 lm/W	3,100 lm	Beam angle 84°
911401880481	RC136B 31S_37S_43S/840 PSU W60L60 OC	4000 K	140 lm/W	3,100 lm	Beam angle 84°
911401881081	RC136B 28S_34S_40S/830 PSU W60L60 NOC W3	3000 K	130 lm/W	2,800 lm	Beam angle 100°
911401881381	RC136B 31S_37S_43S/840 PSD W60L60 NOC W5	4000 K	140 lm/W	3,100 lm	Beam angle 100°
911401880681	RC136B 28S_34S_40S/830 PSD W60L60 OC	3000 K	130 lm/W	2,800 lm	Beam angle 84°
911401880781	RC136B 31S_37S_43S/840 PSD W60L60 OC	4000 K	140 lm/W	3,100 lm	Beam angle 84°
911401880881	RC136B 28S_34S_40S/830 PSD W30L120 OC	3000 K	130 lm/W	2,800 lm	Beam angle 84°
910505101244	RC136B 28S_34S_40S/830 PSD W30L120OCELB3	3000 K	118 lm/W	2,800 lm	Wide beam

Light Technical (2/2)

Order Code	Full Product Name	Stroboscopic effect
		visibility measure
		(SVM)
910505101241	RC136B 31S_37S_43S/840 PSD W60L60 OCELB3	0.4
910505101242	RC136B 31S_37S_43S/840 PSU W60L60NOCELB3	0.4
910505101243	RC136B 31S_37S_43S/840 PSD W60L60NOCELB3	0.4
910505101256	RC136B 31S_37S_43S/840 PSDW60L60OCELB3W5	0.4
910505101257	RC136B 31S_37S_43S/840 PSUW60L60OCELB3W3	0.4
911401881181	RC136B 31S_37S_43S/840 PSU W60L60 NOC W3	1.6
911401880981	RC136B 31S_37S_43S/840 PSD W30L120 OC	1.6
911401880481	RC136B 31S_37S_43S/840 PSU W60L60 OC	1.6
911401881081	RC136B 28S_34S_40S/830 PSU W60L60 NOC W3	1.6
911401881381	RC136B 31S_37S_43S/840 PSD W60L60 NOC W5	1.6
911401880681	RC136B 28S_34S_40S/830 PSD W60L60 OC	1.6

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505101241	RC136B 31S_37S_43S/840 PSD W60L60 OCELB3	34 W
910505101242	RC136B 31S_37S_43S/840 PSU W60L60NOCELB3	34 W
910505101243	RC136B 31S_37S_43S/840 PSD W60L60NOCELB3	34 W

Order Code	Full Product Name	Correlated	Luminous	Luminous	Optic
		Color	Efficacy		
		Temperature	(rated)	Flux	type
(Nom)		(Nom)			
910505101245	RC136B 31S_37S_43S/840 PSD W30L120OCELB3	4000 K	126 lm/W	3,100 lm	Wide beam
911401881581	RC136B 31S_37S_43S/840 PSD W60L60 OC W5	4000 K	140 lm/W	3,100 lm	Beam angle 84°
911401881481	RC136B 28S_34S_40S/830 PSD W60L60 OC W5	3000 K	130 lm/W	2,800 lm	Beam angle 84°
911401880281	RC136B 28S_34S_40S/830 PSU W60L60 NOC	3000 K	130 lm/W	2,800 lm	Beam angle 100°
911401880381	RC136B 31S_37S_43S/840 PSU W60L60 NOC	4000 K	140 lm/W	3,100 lm	Beam angle 100°
911401880581	RC136B 31S_37S_43S/840 PSD W60L60 NOC	4000 K	140 lm/W	3,100 lm	Beam angle 100°
911401881281	RC136B 31S_37S_43S/840 PSU W60L60 OC W3	4000 K	140 lm/W	3,100 lm	Beam angle 84°

Order Code	Full Product Name	Stroboscopic effect
		visibility measure
		(SVM)
911401880781	RC136B 31S_37S_43S/840 PSD W60L60 OC	1.6
911401880881	RC136B 28S_34S_40S/830 PSD W30L120 OC	1.6
910505101244	RC136B 28S_34S_40S/830 PSD W30L120OCELB3	0.4
910505101245	RC136B 31S_37S_43S/840 PSD W30L120OCELB3	0.4
911401881581	RC136B 31S_37S_43S/840 PSD W60L60 OC W5	1.6
911401881481	RC136B 28S_34S_40S/830 PSD W60L60 OC W5	1.6
911401880281	RC136B 28S_34S_40S/830 PSU W60L60 NOC	1.6
911401880381	RC136B 31S_37S_43S/840 PSU W60L60 NOC	1.6
911401880581	RC136B 31S_37S_43S/840 PSD W60L60 NOC	1.6
911401881281	RC136B 31S_37S_43S/840 PSU W60L60 OC W3	1.6

Order Code	Full Product Name	Power Consumption
910505101256	RC136B 31S_37S_43S/840 PSDW60L60OCELB3W5	34 W

CoreLine recessed

Order Code	Full Product Name	Power Consumption
910505101257	RC136B 31S_37S_43S/840 PSUW60L60OCELB3W3	34 W
911401881181	RC136B 31S_37S_43S/840 PSU W60L60 NOC W3	31 W
911401880981	RC136B 31S_37S_43S/840 PSD W30L120 OC	31 W
911401880481	RC136B 31S_37S_43S/840 PSU W60L60 OC	31 W
911401881081	RC136B 28S_34S_40S/830 PSU W60L60 NOC W3	31 W
911401881381	RC136B 31S_37S_43S/840 PSD W60L60 NOC W5	31 W
911401880681	RC136B 28S_34S_40S/830 PSD W60L60 OC	31 W
911401880781	RC136B 31S_37S_43S/840 PSD W60L60 OC	31 W

Temperature

Order Code	Full Product Name	Ambient temperature range
910505101241	RC136B 31S_37S_43S/840 PSD W60L60 OCELB3	0 to +25 °C
910505101242	RC136B 31S_37S_43S/840 PSU W60L60NOCELB3	-10 to +40 °C
910505101243	RC136B 31S_37S_43S/840 PSD W60L60NOCELB3	0 to +25 °C
910505101256	RC136B 31S_37S_43S/840 PSDW60L60OCELB3W5	0 to +25 °C
910505101257	RC136B 31S_37S_43S/840 PSUW60L60OCELB3W3	-10 to +40 °C
911401881181	RC136B 31S_37S_43S/840 PSU W60L60 NOC W3	-10 to +40 °C
911401880981	RC136B 31S_37S_43S/840 PSD W30L120 OC	-10 to +40 °C
911401880481	RC136B 31S_37S_43S/840 PSU W60L60 OC	-10 to +40 °C
911401881081	RC136B 28S_34S_40S/830 PSU W60L60 NOC W3	-10 to +40 °C
911401881381	RC136B 31S_37S_43S/840 PSD W60L60 NOC W5	-10 to +40 °C
911401880681	RC136B 28S_34S_40S/830 PSD W60L60 OC	-10 to +40 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
910505101241	RC136B 31S_37S_43S/840 PSD W60L60 OCELB3	Yes
910505101242	RC136B 31S_37S_43S/840 PSU W60L60NOCELB3	No
910505101243	RC136B 31S_37S_43S/840 PSD W60L60NOCELB3	Yes
910505101256	RC136B 31S_37S_43S/840 PSDW60L60OCELB3W5	Yes
910505101257	RC136B 31S_37S_43S/840 PSUW60L60OCELB3W3	No
911401881181	RC136B 31S_37S_43S/840 PSU W60L60 NOC W3	No
911401880981	RC136B 31S_37S_43S/840 PSD W30L120 OC	Yes
911401880481	RC136B 31S_37S_43S/840 PSU W60L60 OC	No
911401881081	RC136B 28S_34S_40S/830 PSU W60L60 NOC W3	No
911401881381	RC136B 31S_37S_43S/840 PSD W60L60 NOC W5	Yes
911401880681	RC136B 28S_34S_40S/830 PSD W60L60 OC	Yes

Order Code	Full Product Name	Power Consumption
911401880881	RC136B 28S_34S_40S/830 PSD W30L120 OC	31 W
910505101244	RC136B 28S_34S_40S/830 PSD W30L120OCELB3	34 W
910505101245	RC136B 31S_37S_43S/840 PSD W30L120OCELB3	34 W
911401881581	RC136B 31S_37S_43S/840 PSD W60L60 OC W5	31 W
911401881481	RC136B 28S_34S_40S/830 PSD W60L60 OC W5	31 W
911401880281	RC136B 28S_34S_40S/830 PSU W60L60 NOC	31 W
911401880381	RC136B 31S_37S_43S/840 PSU W60L60 NOC	31 W
911401880581	RC136B 31S_37S_43S/840 PSD W60L60 NOC	31 W
911401881281	RC136B 31S_37S_43S/840 PSU W60L60 OC W3	31 W

Order Code	Full Product Name	Ambient temperature range
911401880781	RC136B 31S_37S_43S/840 PSD W60L60 OC	-10 to +40 °C
911401880881	RC136B 28S_34S_40S/830 PSD W30L120 OC	-10 to +40 °C
910505101244	RC136B 28S_34S_40S/830 PSD W30L120OCELB3	0 to +25 °C
910505101245	RC136B 31S_37S_43S/840 PSD W30L120OCELB3	0 to +25 °C
911401881581	RC136B 31S_37S_43S/840 PSD W60L60 OC W5	-10 to +40 °C
911401881481	RC136B 28S_34S_40S/830 PSD W60L60 OC W5	-10 to +40 °C
911401880281	RC136B 28S_34S_40S/830 PSU W60L60 NOC	-10 to +40 °C
911401880381	RC136B 31S_37S_43S/840 PSU W60L60 NOC	-10 to +40 °C
911401880581	RC136B 31S_37S_43S/840 PSD W60L60 NOC	-10 to +40 °C
911401881281	RC136B 31S_37S_43S/840 PSU W60L60 OC W3	-10 to +40 °C

Order Code	Full Product Name	Dimmable
911401880781	RC136B 31S_37S_43S/840 PSD W60L60 OC	Yes
911401880881	RC136B 28S_34S_40S/830 PSD W30L120 OC	Yes
910505101244	RC136B 28S_34S_40S/830 PSD W30L120OCELB3	Yes
910505101245	RC136B 31S_37S_43S/840 PSD W30L120OCELB3	Yes
911401881581	RC136B 31S_37S_43S/840 PSD W60L60 OC W5	Yes
911401881481	RC136B 28S_34S_40S/830 PSD W60L60 OC W5	Yes
911401880281	RC136B 28S_34S_40S/830 PSU W60L60 NOC	No
911401880381	RC136B 31S_37S_43S/840 PSU W60L60 NOC	No
911401880581	RC136B 31S_37S_43S/840 PSD W60L60 NOC	Yes
911401881281	RC136B 31S_37S_43S/840 PSU W60L60 OC W3	No

Approval and Application

CoreLine recessed

Order Code	Full Product Name	Protection class IEC
910505101241	RC136B 31S_37S_43S/840 PSD W60L60 OCELB3	Safety class II
910505101242	RC136B 31S_37S_43S/840 PSU W60L60NOCELB3	Safety class I
910505101243	RC136B 31S_37S_43S/840 PSD W60L60NOCELB3	Safety class II
910505101256	RC136B 31S_37S_43S/840 PSDW60L60OCELB3W5	Safety class II
910505101257	RC136B 31S_37S_43S/840 PSUW60L60OCELB3W3	Safety class I
911401881181	RC136B 31S_37S_43S/840 PSU W60L60 NOC W3	Safety class I
911401880981	RC136B 31S_37S_43S/840 PSD W30L120 OC	Safety class II
911401880481	RC136B 31S_37S_43S/840 PSU W60L60 OC	Safety class I
911401881081	RC136B 28S_34S_40S/830 PSU W60L60 NOC W3	Safety class I
911401881381	RC136B 31S_37S_43S/840 PSD W60L60 NOC W5	Safety class II

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505101241	RC136B 31S_37S_43S/840 PSD W60L60 OCELB3	(0.38, 0.38) SDCM ≤3
910505101242	RC136B 31S_37S_43S/840 PSU W60L60NOCELB3	(0.38, 0.38) SDCM ≤3
910505101243	RC136B 31S_37S_43S/840 PSD W60L60NOCELB3	(0.38, 0.38) SDCM ≤3
910505101256	RC136B 31S_37S_43S/840 PSDW60L60OCELB3W5	(0.38, 0.38) SDCM ≤3
910505101257	RC136B 31S_37S_43S/840 PSUW60L60OCELB3W3	(0.38, 0.38) SDCM ≤3
911401881181	RC136B 31S_37S_43S/840 PSU W60L60 NOC W3	(0.38, 0.38) SDCM ≤3
911401880981	RC136B 31S_37S_43S/840 PSD W30L120 OC	(0.38, 0.38) SDCM ≤3
911401880481	RC136B 31S_37S_43S/840 PSU W60L60 OC	(0.38, 0.38) SDCM ≤3
911401881081	RC136B 28S_34S_40S/830 PSU W60L60 NOC W3	(0.43, 0.40) SDCM ≤3

Application Conditions

Order Code	Full Product Name	Maximum dim level
910505101241	RC136B 31S_37S_43S/840 PSD W60L60 OCELB3	3%
910505101242	RC136B 31S_37S_43S/840 PSU W60L60NOCELB3	-
910505101243	RC136B 31S_37S_43S/840 PSD W60L60NOCELB3	3%
910505101256	RC136B 31S_37S_43S/840 PSDW60L60OCELB3W5	3%
910505101257	RC136B 31S_37S_43S/840 PSUW60L60OCELB3W3	-
911401881181	RC136B 31S_37S_43S/840 PSU W60L60 NOC W3	-
911401880981	RC136B 31S_37S_43S/840 PSD W30L120 OC	3%
911401880481	RC136B 31S_37S_43S/840 PSU W60L60 OC	-
911401881081	RC136B 28S_34S_40S/830 PSU W60L60 NOC W3	-
911401881381	RC136B 31S_37S_43S/840 PSD W60L60 NOC W5	3%
911401880681	RC136B 28S_34S_40S/830 PSD W60L60 OC	3%

Order Code	Full Product Name	Protection class IEC
911401880681	RC136B 28S_34S_40S/830 PSD W60L60 OC	Safety class II
911401880781	RC136B 31S_37S_43S/840 PSD W60L60 OC	Safety class II
911401880881	RC136B 28S_34S_40S/830 PSD W30L120 OC	Safety class II
910505101244	RC136B 28S_34S_40S/830 PSD W30L120OCELB3	Safety class II
910505101245	RC136B 31S_37S_43S/840 PSD W30L120OCELB3	Safety class II
911401881581	RC136B 31S_37S_43S/840 PSD W60L60 OC W5	Safety class II
911401881481	RC136B 28S_34S_40S/830 PSD W60L60 OC W5	Safety class II
911401880281	RC136B 28S_34S_40S/830 PSU W60L60 NOC	Safety class I
911401880381	RC136B 31S_37S_43S/840 PSU W60L60 NOC	Safety class I
911401880581	RC136B 31S_37S_43S/840 PSD W60L60 NOC	Safety class II
911401881281	RC136B 31S_37S_43S/840 PSU W60L60 OC W3	Safety class I

Order Code	Full Product Name	Initial chromaticity
911401881381	RC136B 31S_37S_43S/840 PSD W60L60 NOC W5	(0.38, 0.38) SDCM ≤3
911401880681	RC136B 28S_34S_40S/830 PSD W60L60 OC	(0.43, 0.40) SDCM ≤3
911401880781	RC136B 31S_37S_43S/840 PSD W60L60 OC	(0.38, 0.38) SDCM ≤3
911401880881	RC136B 28S_34S_40S/830 PSD W30L120 OC	(0.43, 0.40) SDCM ≤3
910505101244	RC136B 28S_34S_40S/830 PSD W30L120OCELB3	(0.43, 0.40) SDCM ≤3
910505101245	RC136B 31S_37S_43S/840 PSD W30L120OCELB3	(0.38, 0.38) SDCM ≤3
911401881581	RC136B 31S_37S_43S/840 PSD W60L60 OC W5	(0.38, 0.38) SDCM ≤3
911401881481	RC136B 28S_34S_40S/830 PSD W60L60 OC W5	(0.43, 0.40) SDCM ≤3
911401880281	RC136B 28S_34S_40S/830 PSU W60L60 NOC	(0.43, 0.40) SDCM ≤3
911401880381	RC136B 31S_37S_43S/840 PSU W60L60 NOC	(0.38, 0.38) SDCM ≤3
911401880581	RC136B 31S_37S_43S/840 PSD W60L60 NOC	(0.38, 0.38) SDCM ≤3
911401881281	RC136B 31S_37S_43S/840 PSU W60L60 OC W3	(0.38, 0.38) SDCM ≤3

Order Code	Full Product Name	Maximum dim level
911401880781	RC136B 31S_37S_43S/840 PSD W60L60 OC	3%
911401880881	RC136B 28S_34S_40S/830 PSD W30L120 OC	3%
910505101244	RC136B 28S_34S_40S/830 PSD W30L120OCELB3	3%
910505101245	RC136B 31S_37S_43S/840 PSD W30L120OCELB3	3%
911401881581	RC136B 31S_37S_43S/840 PSD W60L60 OC W5	3%
911401881481	RC136B 28S_34S_40S/830 PSD W60L60 OC W5	3%
911401880281	RC136B 28S_34S_40S/830 PSU W60L60 NOC	-
911401880381	RC136B 31S_37S_43S/840 PSU W60L60 NOC	-
911401880581	RC136B 31S_37S_43S/840 PSD W60L60 NOC	3%
911401881281	RC136B 31S_37S_43S/840 PSU W60L60 OC W3	-

