



Philips GreenPerform Highbay: A versatile LED highbay that's designed to optimize performance

GreenPerform Highbay Rectangular

The GreenPerform Highbay Rectangular continues the GreenPerform family's enviable reputation for reliable performance, providing. Not only does it deliver Unified Glare Rating (UGR) control with its optimized optical design, it also promises leading system efficiency, compact dimensions and extended long-term quality. Optimized for almost all industrial applications, it is also fully compatible with IoT software such as the Interact scalable system.

Benefits

- Excellent energy savings
- Long-term quality and reliability
- Great design flexibility and convenience thanks to optimized optics and multiple control options

Features

- 140 lm/W system efficacy
- 70,000 hours lifetime @Ta 35°C
- Glare control (Near Beam), uniform illumination (Wide Beam) and maximal spacing (High-Rack Optic).
- Works seamlessly with the Interact IoT software and platform
- Compact and robust design

GreenPerform Highbay Rectangular

Application



- Warehouses
- Manufacturing
- Distribution center
- Exhibition hall

Specifications

Mounting type	Suspended
	Pipe
	Surface
Operating Temperature range	-30 to +50 °C (45 °C)
Light Source	LED
Mains Voltage	220-240V / 50-60Hz
Mains connection	Flying cable
Mechanical Accessories	Suspension kit
	Pipe kit
	Mounting bracket
Dimming	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
	Connected: Wireless control, compatible with SNH210 sensor
Control system input	DALI / Wireless
Integrated sensors	SNH210
Material	Housing: die-cast aluminum
Main color of the luminaire	RAL7043
Flicker / Pst / SVM	PSU: <20%
	PSD: <4%
	Connected: <4%


Luminous flux	10klm - 25klm
Power consumption	69W - 199W
Luminaire efficacy	Up to 145lm/W
Correlated color temperature - CCT	4000K
	6500K
	5000K
Color Rendering index - CRI	80
Beam angle	WB: 93° ± 5°
	NB: 58° ± 5°
	HRO: 44*88° ± 5°
Optical cover/lens material	PC
Optical cover/lens finish	Clear
Protection Class	Class I
IEC61140	
Mechanical impact protection	IK06
Ingress protection	IP65
Driver replaceable	Yes

Dimensional drawing



GreenPerform Highbay Rectangular

Dimensional drawing



General Information	
CE mark	CE mark
Light Technical	
Optical cover type	Transparent dome
Color rendering index (CRI)	>80
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Housing Color	Gray
Approval and Application	
Protection class IEC	Safety class I
Mech. impact protection code	IK06
Ingress protection code	IP65
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401590761	BY570P LED100/CW PSU WB GM	6500 K	145 lm/W	10,000 lm
911401590861	BY570P LED100/NW PSU WB GM	4000 K	145 lm/W	10,000 lm
911401590961	BY570P LED100/CW PSU HRO GM	6500 K	145 lm/W	10,000 lm
911401591161	BY570P LED150/CW PSU WB GM	6500 K	135 lm/W	15,000 lm
911401591261	BY570P LED150/NW PSU WB GM	4000 K	135 lm/W	15,000 lm
911401591361	BY570P LED150/CW PSU HRO GM	6500 K	135 lm/W	15,000 lm
911401591461	BY570P LED150/NW PSU HRO GM	4000 K	135 lm/W	15,000 lm
911401592361	BY570P LED100/NW PSD WB GM	4000 K	133 lm/W	10,000 lm
911401592461	BY570P LED100/NW PSD HRO GM	4000 K	133 lm/W	10,000 lm
911401592561	BY570P LED150/NW PSD WB GM	4000 K	126 lm/W	15,000 lm
911401592661	BY570P LED150/NW PSD HRO GM	4000 K	126 lm/W	15,000 lm
911401593361	BY570P LED150/CW PSD WB GM	6500 K	126 lm/W	15,000 lm
911401594161	BY570P LED150/CW PSU NB GM	6500 K	135 lm/W	15,000 lm
911401594261	BY570P LED150/NW PSU NB GM	4000 K	135 lm/W	15,000 lm
911401594861	BY570P LED100/NW PSD NB GM	4000 K	133 lm/W	10,000 lm
911401595061	BY570P LED150/NW PSD NB GM	4000 K	126 lm/W	15,000 lm
911401591961	BY570P LED250/CW PSU WB GM	6500 K	140 lm/W	25,000 lm
911401592061	BY570P LED250/NW PSU WB GM	4000 K	140 lm/W	25,000 lm
911401592161	BY570P LED250/CW PSU HRO GM	6500 K	140 lm/W	25,000 lm
911401592961	BY570P LED250/NW PSD WB GM	4000 K	128 lm/W	25,000 lm
911401593061	BY570P LED250/NW PSD HRO GM	4000 K	128 lm/W	25,000 lm

GreenPerform Highbay Rectangular

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401593761	BY570P LED250/CW PSD WB GM	6500 K	128 lm/W	25,000 lm
911401594561	BY570P LED250/CW PSU NB GM	6500 K	140 lm/W	25,000 lm
911401594661	BY570P LED250/NW PSU NB GM	4000 K	140 lm/W	25,000 lm
911401595361	BY570P LED250/CW PSD NB GM	6500 K	128 lm/W	25,000 lm
911401595461	BY570P LED250/NW PSD NB GM	4000 K	128 lm/W	25,000 lm
911401591561	BY570P LED200/CW PSU WB GM	6500 K	139 lm/W	20,000 lm
911401591661	BY570P LED200/NW PSU WB GM	4000 K	139 lm/W	20,000 lm
911401591761	BY570P LED200/CW PSU HRO GM	6500 K	139 lm/W	20,000 lm
911401591861	BY570P LED200/NW PSU HRO GM	4000 K	139 lm/W	20,000 lm
911401592761	BY570P LED200/NW PSD WB GM	4000 K	132 lm/W	20,000 lm
911401592861	BY570P LED200/NW PSD HRO GM	4000 K	132 lm/W	20,000 lm
911401593561	BY570P LED200/CW PSD WB GM	6500 K	132 lm/W	20,000 lm
911401594361	BY570P LED200/CW PSU NB GM	6500 K	139 lm/W	20,000 lm
911401594461	BY570P LED200/NW PSU NB GM	4000 K	139 lm/W	20,000 lm
911401595161	BY570P LED200/CW PSD NB GM	6500 K	132 lm/W	20,000 lm
911401595261	BY570P LED200/NW PSD NB GM	4000 K	132 lm/W	20,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401590761	BY570P LED100/CW PSU WB GM	69 W	911401592961	BY570P LED250/NW PSD WB GM	199 W
911401590861	BY570P LED100/NW PSU WB GM	69 W	911401593061	BY570P LED250/NW PSD HRO GM	199 W
911401590961	BY570P LED100/CW PSU HRO GM	69 W	911401593761	BY570P LED250/CW PSD WB GM	199 W
911401591161	BY570P LED150/CW PSU WB GM	111 W	911401594561	BY570P LED250/CW PSU NB GM	182 W
911401591261	BY570P LED150/NW PSU WB GM	111 W	911401594661	BY570P LED250/NW PSU NB GM	182 W
911401591361	BY570P LED150/CW PSU HRO GM	111 W	911401595361	BY570P LED250/CW PSD NB GM	199 W
911401591461	BY570P LED150/NW PSU HRO GM	111 W	911401595461	BY570P LED250/NW PSD NB GM	199 W
911401592361	BY570P LED100/NW PSD WB GM	75 W	911401591561	BY570P LED200/CW PSU WB GM	144 W
911401592461	BY570P LED100/NW PSD HRO GM	75 W	911401591661	BY570P LED200/NW PSU WB GM	144 W
911401592561	BY570P LED150/NW PSD WB GM	119 W	911401591761	BY570P LED200/CW PSU HRO GM	144 W
911401592661	BY570P LED150/NW PSD HRO GM	119 W	911401591861	BY570P LED200/NW PSU HRO GM	144 W
911401593361	BY570P LED150/CW PSD WB GM	119 W	911401592761	BY570P LED200/NW PSD WB GM	152 W
911401594161	BY570P LED150/CW PSU NB GM	111 W	911401592861	BY570P LED200/NW PSD HRO GM	152 W
911401594261	BY570P LED150/NW PSU NB GM	111 W	911401593561	BY570P LED200/CW PSD WB GM	152 W
911401594861	BY570P LED100/NW PSD NB GM	75 W	911401594361	BY570P LED200/CW PSU NB GM	144 W
911401595061	BY570P LED150/NW PSD NB GM	119 W	911401594461	BY570P LED200/NW PSU NB GM	144 W
911401591961	BY570P LED250/CW PSU WB GM	182 W	911401595161	BY570P LED200/CW PSD NB GM	152 W
911401592061	BY570P LED250/NW PSU WB GM	182 W	911401595261	BY570P LED200/NW PSD NB GM	152 W
911401592161	BY570P LED250/CW PSU HRO GM	182 W			

GreenPerform Highbay Rectangular

Temperature

Order Code	Full Product Name	Ambient temperature range
911401590761	BY570P LED100/CW PSU WB GM	-30 to +50 °C
911401590861	BY570P LED100/NW PSU WB GM	-30 to +50 °C
911401590961	BY570P LED100/CW PSU HRO GM	-30 to +50 °C
911401591161	BY570P LED150/CW PSU WB GM	-30 to +50 °C
911401591261	BY570P LED150/NW PSU WB GM	-30 to +50 °C
911401591361	BY570P LED150/CW PSU HRO GM	-30 to +50 °C
911401591461	BY570P LED150/NW PSU HRO GM	-30 to +50 °C
911401592361	BY570P LED100/NW PSD WB GM	-30 to +45 °C
911401592461	BY570P LED100/NW PSD HRO GM	-30 to +45 °C
911401592561	BY570P LED150/NW PSD WB GM	-30 to +45 °C
911401592661	BY570P LED150/NW PSD HRO GM	-30 to +45 °C
911401593361	BY570P LED150/CW PSD WB GM	-30 to +45 °C
911401594161	BY570P LED150/CW PSU NB GM	-30 to +50 °C
911401594261	BY570P LED150/NW PSU NB GM	-30 to +50 °C
911401594861	BY570P LED100/NW PSD NB GM	-30 to +45 °C
911401595061	BY570P LED150/NW PSD NB GM	-30 to +45 °C
911401591961	BY570P LED250/CW PSU WB GM	-30 to +50 °C
911401592061	BY570P LED250/NW PSU WB GM	-30 to +50 °C
911401592161	BY570P LED250/CW PSU HRO GM	-30 to +50 °C

Order Code	Full Product Name	Ambient temperature range
911401592961	BY570P LED250/NW PSD WB GM	-30 to +45 °C
911401593061	BY570P LED250/NW PSD HRO GM	-30 to +45 °C
911401593761	BY570P LED250/CW PSD WB GM	-30 to +45 °C
911401594561	BY570P LED250/CW PSU NB GM	-30 to +50 °C
911401594661	BY570P LED250/NW PSU NB GM	-30 to +50 °C
911401595361	BY570P LED250/CW PSD NB GM	-30 to +45 °C
911401595461	BY570P LED250/NW PSD NB GM	-30 to +45 °C
911401591561	BY570P LED200/CW PSU WB GM	-30 to +50 °C
911401591661	BY570P LED200/NW PSU WB GM	-30 to +50 °C
911401591761	BY570P LED200/CW PSU HRO GM	-30 to +50 °C
911401591861	BY570P LED200/NW PSU HRO GM	-30 to +50 °C
911401592761	BY570P LED200/NW PSD WB GM	-30 to +45 °C
911401592861	BY570P LED200/NW PSD HRO GM	-30 to +45 °C
911401593561	BY570P LED200/CW PSD WB GM	-30 to +45 °C
911401594361	BY570P LED200/CW PSU NB GM	-30 to +50 °C
911401594461	BY570P LED200/NW PSU NB GM	-30 to +50 °C
911401595161	BY570P LED200/CW PSD NB GM	-30 to +45 °C
911401595261	BY570P LED200/NW PSD NB GM	-30 to +45 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401590761	BY570P LED100/CW PSU WB GM	No
911401590861	BY570P LED100/NW PSU WB GM	No
911401590961	BY570P LED100/CW PSU HRO GM	No
911401591161	BY570P LED150/CW PSU WB GM	No
911401591261	BY570P LED150/NW PSU WB GM	No
911401591361	BY570P LED150/CW PSU HRO GM	No
911401591461	BY570P LED150/NW PSU HRO GM	No
911401592361	BY570P LED100/NW PSD WB GM	Yes
911401592461	BY570P LED100/NW PSD HRO GM	Yes
911401592561	BY570P LED150/NW PSD WB GM	Yes
911401592661	BY570P LED150/NW PSD HRO GM	Yes
911401593361	BY570P LED150/CW PSD WB GM	Yes
911401594161	BY570P LED150/CW PSU NB GM	No
911401594261	BY570P LED150/NW PSU NB GM	No
911401594861	BY570P LED100/NW PSD NB GM	Yes
911401595061	BY570P LED150/NW PSD NB GM	Yes
911401591961	BY570P LED250/CW PSU WB GM	No
911401592061	BY570P LED250/NW PSU WB GM	No
911401592161	BY570P LED250/CW PSU HRO GM	No

Order Code	Full Product Name	Dimmable
911401592961	BY570P LED250/NW PSD WB GM	Yes
911401593061	BY570P LED250/NW PSD HRO GM	Yes
911401593761	BY570P LED250/CW PSD WB GM	Yes
911401594561	BY570P LED250/CW PSU NB GM	No
911401594661	BY570P LED250/NW PSU NB GM	No
911401595361	BY570P LED250/CW PSD NB GM	Yes
911401595461	BY570P LED250/NW PSD NB GM	Yes
911401591561	BY570P LED200/CW PSU WB GM	No
911401591661	BY570P LED200/NW PSU WB GM	No
911401591761	BY570P LED200/CW PSU HRO GM	No
911401591861	BY570P LED200/NW PSU HRO GM	No
911401592761	BY570P LED200/NW PSD WB GM	Yes
911401592861	BY570P LED200/NW PSD HRO GM	Yes
911401593561	BY570P LED200/CW PSD WB GM	Yes
911401594361	BY570P LED200/CW PSU NB GM	No
911401594461	BY570P LED200/NW PSU NB GM	No
911401595161	BY570P LED200/CW PSD NB GM	Yes
911401595261	BY570P LED200/NW PSD NB GM	Yes

GreenPerform Highbay Rectangular

