



Philips GreenPerform Highbay G5: a versatile LED highbay with optimized performance and future-proof control system

GreenPerform Highbay G5

The GreenPerform Highbay G5 continues the GreenPerform family's enviable reputation for reliable performance. Not only does it deliver leading system efficacy and extended long-term quality, it also promises Unified Glare Rating (UGR) control with compact dimensions. GreenPerform Highbay G5 is also fully compatible with IoT software such as Interact, which is a scalable, future-proof control system. The family also has a series that supports cold room applications with 100% humidity and no condensation. All benefits that make this robust, optimized, and versatile family suitable for almost all industrial applications.

Benefits

- Excellent energy savings
- Long-term quality and reliability
- Visual comfort
- Wide range of applications
- Connected ready for cloud-based IoT software applications

GreenPerform Highbay G5

Features

- 160 lm/W system efficacy
- 75,000 hours lifetime @Ta 35°
- Glare control (Narrow Beam), uniform illuminance (Wide Beam)
- Works seamlessly with the Interact IoT software and platform
- Cold room application support

Application

- Manufacturing
- Warehouses
- Logistic center
- Exhibition hall

Specifications

Mounting type	Suspended
	Pipe
	Surface
Operating Temperature range	-30 to +50 °C
Light Source	LED
Mains Voltage	220-240V / 50-60Hz
Mains connection	Flying cable
Mechanical Accessories	Hook for suspension
	Mounting bracket for surface
Dimming	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
	Connected: Wireless control, compatible with SNH210 sensor
Control system input	DALI/Wireless
Integrated sensors	SNH210
Material	Housing: die-cast aluminium
Main color of the luminaire	RAL7012
Flicker / Pst / SVM	PSU: <30%
	PSD/Connected: <3.2%
Luminous flux	10klm-30klm
Power consumption	67W-205W


Luminaire efficacy	Up to 160lm/W
Correlated color temperature - CCT	4000K 6500K
Color Rendering index - CRI	80
Beam angle	WB: 85°
	NB: 55°
Optical cover/lens material	PC
Optical cover/lens finish	Clear
Protection Class	Class I
IEC61140	
Mechanical impact protection	IK08
Ingress protection	IP65
Driver replaceable	Yes
UGR	WB: 25
	NB: 22
Installation	Suspended
	Pipe
	Surface

Versions



GreenPerform Highbay G5

Dimensional drawing



General Information	
CE mark	CE mark
Light Technical	
Optical cover type	Lens
Color rendering index (CRI)	80
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-30 to +50 °C
Mechanical and Housing	
Housing Color	Dark gray
Approval and Application	
Protection class IEC	Safety class I
Ingress protection code	IP65
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401525991	BY698X G5 LED150/NW Connected WB GM	4000 K	150 lm/W	15,000 lm
911401526091	BY698X G5 LED150/NW Connected NB GM	4000 K	150 lm/W	15,000 lm
911401526191	BY698X G5 LED150/CW Connected WB GM	6500 K	150 lm/W	15,000 lm
911401526291	BY698X G5 LED150/CW Connected NB GM	6500 K	150 lm/W	15,000 lm
911401526391	BY698X G5 LED200/NW Connected WB GM	4000 K	150 lm/W	20,000 lm
911401526491	BY698X G5 LED200/NW Connected NB GM	4000 K	150 lm/W	20,000 lm
911401526591	BY698X G5 LED200/CW Connected WB GM	6500 K	150 lm/W	20,000 lm
911401526691	BY698X G5 LED200/CW Connected NB GM	6500 K	150 lm/W	20,000 lm
911401526791	BY698X G5 LED250/NW Connected WB GM	4000 K	150 lm/W	25,000 lm
911401526891	BY698X G5 LED250/NW Connected NB GM	4000 K	150 lm/W	25,000 lm
911401526991	BY698X G5 LED250/CW Connected WB GM	6500 K	150 lm/W	25,000 lm
911401527091	BY698X G5 LED250/CW Connected NB GM	6500 K	150 lm/W	25,000 lm
911401527191	BY698X G5 LED300/NW Connected WB GM	4000 K	150 lm/W	30,000 lm
911401527291	BY698X G5 LED300/NW Connected NB GM	4000 K	150 lm/W	30,000 lm
911401527391	BY698X G5 LED300/CW Connected WB GM	6500 K	150 lm/W	30,000 lm
911401527491	BY698X G5 LED300/CW Connected NB GM	6500 K	150 lm/W	30,000 lm
911401509891	BY698P G5 LED200/NW PSU WB GM	4000 K	160 lm/W	20,000 lm
911401509991	BY698P G5 LED200/NW PSU NB GM	4000 K	160 lm/W	20,000 lm
911401510091	BY698P G5 LED200/CW PSU WB GM	6500 K	160 lm/W	20,000 lm
911401510191	BY698P G5 LED200/CW PSU NB GM	6500 K	160 lm/W	20,000 lm
911401518591	BY698P G5 LED105/NW PSD WB GM	4000 K	150 lm/W	10,500 lm
911401518691	BY698P G5 LED105/NW PSD NB GM	4000 K	150 lm/W	10,500 lm
911401518991	BY698P G5 LED150/NW PSD WB GM	4000 K	150 lm/W	15,000 lm
911401519091	BY698P G5 LED150/NW PSD NB GM	4000 K	150 lm/W	15,000 lm
911401519391	BY698P G5 LED200/NW PSD WB GM	4000 K	150 lm/W	20,000 lm

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401519491	BY698P G5 LED200/NW PSD NB GM	4000 K	150 lm/W	20,000 lm
911401519591	BY698P G5 LED200/CW PSD WB GM	6500 K	150 lm/W	20,000 lm
911401509091	BY698P G5 LED105/NW PSU WB GM	4000 K	160 lm/W	10,500 lm
911401509291	BY698P G5 LED105/CW PSU WB GM	6500 K	160 lm/W	10,500 lm
911401509391	BY698P G5 LED105/CW PSU NB GM	6500 K	160 lm/W	10,500 lm
911401509491	BY698P G5 LED150/NW PSU WB GM	4000 K	160 lm/W	15,000 lm
911401509591	BY698P G5 LED150/NW PSU NB GM	4000 K	160 lm/W	15,000 lm
911401509691	BY698P G5 LED150/CW PSU WB GM	6500 K	160 lm/W	15,000 lm
911401509791	BY698P G5 LED150/CW PSU NB GM	6500 K	160 lm/W	15,000 lm
911401510291	BY698P G5 LED250/NW PSU WB GM	4000 K	160 lm/W	25,000 lm
911401510391	BY698P G5 LED250/NW PSU NB GM	4000 K	160 lm/W	25,000 lm
911401510491	BY698P G5 LED250/CW PSU WB GM	6500 K	160 lm/W	25,000 lm
911401510591	BY698P G5 LED250/CW PSU NB GM	6500 K	160 lm/W	25,000 lm
911401510691	BY698P G5 LED300/NW PSU WB GM	4000 K	160 lm/W	30,000 lm
911401510791	BY698P G5 LED300/NW PSU NB GM	4000 K	160 lm/W	30,000 lm
911401510891	BY698P G5 LED300/CW PSU WB GM	6500 K	160 lm/W	30,000 lm
911401510991	BY698P G5 LED300/CW PSU NB GM	6500 K	160 lm/W	30,000 lm
911401519791	BY698P G5 LED250/NW PSD WB GM	4000 K	150 lm/W	25,000 lm
911401519891	BY698P G5 LED250/NW PSD NB GM	4000 K	150 lm/W	25,000 lm
911401519991	BY698P G5 LED250/CW PSD WB GM	6500 K	150 lm/W	25,000 lm
911401520091	BY698P G5 LED250/CW PSD NB GM	6500 K	150 lm/W	25,000 lm
911401520191	BY698P G5 LED300/NW PSD WB GM	4000 K	150 lm/W	30,000 lm
911401520291	BY698P G5 LED300/NW PSD NB GM	4000 K	150 lm/W	30,000 lm
911401520391	BY698P G5 LED300/CW PSD WB GM	6500 K	150 lm/W	30,000 lm
911401520491	BY698P G5 LED300/CW PSD NB GM	6500 K	150 lm/W	30,000 lm

Operating and Electrical

GreenPerform Highbay G5

Order Code	Full Product Name	Power Consumption
911401525991	BY698X G5 LED150/NW Connected WB GM	98 W
911401526091	BY698X G5 LED150/NW Connected NB GM	98 W
911401526191	BY698X G5 LED150/CW Connected WB GM	98 W
911401526291	BY698X G5 LED150/CW Connected NB GM	98 W
911401526391	BY698X G5 LED200/NW Connected WB GM	133 W
911401526491	BY698X G5 LED200/NW Connected NB GM	133 W
911401526591	BY698X G5 LED200/CW Connected WB GM	133 W
911401526691	BY698X G5 LED200/CW Connected NB GM	133 W
911401526791	BY698X G5 LED250/NW Connected WB GM	166 W
911401526891	BY698X G5 LED250/NW Connected NB GM	166 W
911401526991	BY698X G5 LED250/CW Connected WB GM	166 W
911401527091	BY698X G5 LED250/CW Connected NB GM	166 W
911401527191	BY698X G5 LED300/NW Connected WB GM	203 W
911401527291	BY698X G5 LED300/NW Connected NB GM	203 W
911401527391	BY698X G5 LED300/CW Connected WB GM	203 W
911401527491	BY698X G5 LED300/CW Connected NB GM	203 W
911401509891	BY698P G5 LED200/NW PSU WB GM	126 W
911401509991	BY698P G5 LED200/NW PSU NB GM	126 W
911401510091	BY698P G5 LED200/CW PSU WB GM	126 W
911401510191	BY698P G5 LED200/CW PSU NB GM	126 W
911401518591	BY698P G5 LED105/NW PSD WB GM	72 W
911401518691	BY698P G5 LED105/NW PSD NB GM	72 W
911401518991	BY698P G5 LED150/NW PSD WB GM	102 W
911401519091	BY698P G5 LED150/NW PSD NB GM	102 W
911401519391	BY698P G5 LED200/NW PSD WB GM	134 W

Order Code	Full Product Name	Power Consumption
911401519491	BY698P G5 LED200/NW PSD NB GM	134 W
911401519591	BY698P G5 LED200/CW PSD WB GM	134 W
911401509091	BY698P G5 LED105/NW PSU WB GM	67 W
911401509291	BY698P G5 LED105/CW PSU WB GM	67 W
911401509391	BY698P G5 LED105/CW PSU NB GM	67 W
911401509491	BY698P G5 LED150/NW PSU WB GM	95 W
911401509591	BY698P G5 LED150/NW PSU NB GM	95 W
911401509691	BY698P G5 LED150/CW PSU WB GM	95 W
911401509791	BY698P G5 LED150/CW PSU NB GM	95 W
911401510291	BY698P G5 LED250/NW PSU WB GM	157 W
911401510391	BY698P G5 LED250/NW PSU NB GM	157 W
911401510491	BY698P G5 LED250/CW PSU WB GM	157 W
911401510591	BY698P G5 LED250/CW PSU NB GM	157 W
911401510691	BY698P G5 LED300/NW PSU WB GM	192 W
911401510791	BY698P G5 LED300/NW PSU NB GM	192 W
911401510891	BY698P G5 LED300/CW PSU WB GM	192 W
911401510991	BY698P G5 LED300/CW PSU NB GM	192 W
911401519791	BY698P G5 LED250/NW PSD WB GM	168 W
911401519891	BY698P G5 LED250/NW PSD NB GM	168 W
911401519991	BY698P G5 LED250/CW PSD WB GM	168 W
911401520091	BY698P G5 LED250/CW PSD NB GM	168 W
911401520191	BY698P G5 LED300/NW PSD WB GM	205 W
911401520291	BY698P G5 LED300/NW PSD NB GM	205 W
911401520391	BY698P G5 LED300/CW PSD WB GM	205 W
911401520491	BY698P G5 LED300/CW PSD NB GM	205 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401525991	BY698X G5 LED150/NW Connected WB GM	Yes
911401526091	BY698X G5 LED150/NW Connected NB GM	Yes
911401526191	BY698X G5 LED150/CW Connected WB GM	Yes
911401526291	BY698X G5 LED150/CW Connected NB GM	Yes
911401526391	BY698X G5 LED200/NW Connected WB GM	Yes
911401526491	BY698X G5 LED200/NW Connected NB GM	Yes
911401526591	BY698X G5 LED200/CW Connected WB GM	Yes
911401526691	BY698X G5 LED200/CW Connected NB GM	Yes
911401526791	BY698X G5 LED250/NW Connected WB GM	Yes
911401526891	BY698X G5 LED250/NW Connected NB GM	Yes
911401526991	BY698X G5 LED250/CW Connected WB GM	Yes
911401527091	BY698X G5 LED250/CW Connected NB GM	Yes
911401527191	BY698X G5 LED300/NW Connected WB GM	Yes
911401527291	BY698X G5 LED300/NW Connected NB GM	Yes
911401527391	BY698X G5 LED300/CW Connected WB GM	Yes
911401527491	BY698X G5 LED300/CW Connected NB GM	Yes
911401509891	BY698P G5 LED200/NW PSU WB GM	No
911401509991	BY698P G5 LED200/NW PSU NB GM	No
911401510091	BY698P G5 LED200/CW PSU WB GM	No
911401510191	BY698P G5 LED200/CW PSU NB GM	No
911401518591	BY698P G5 LED105/NW PSD WB GM	Yes
911401518691	BY698P G5 LED105/NW PSD NB GM	Yes
911401518991	BY698P G5 LED150/NW PSD WB GM	Yes

Order Code	Full Product Name	Dimmable
911401519091	BY698P G5 LED150/NW PSD NB GM	Yes
911401519391	BY698P G5 LED200/NW PSD WB GM	Yes
911401519491	BY698P G5 LED200/NW PSD NB GM	Yes
911401519591	BY698P G5 LED200/CW PSD WB GM	Yes
911401509091	BY698P G5 LED105/NW PSU WB GM	No
911401509291	BY698P G5 LED105/CW PSU WB GM	No
911401509391	BY698P G5 LED105/CW PSU NB GM	No
911401509491	BY698P G5 LED150/NW PSU WB GM	No
911401509591	BY698P G5 LED150/NW PSU NB GM	No
911401509691	BY698P G5 LED150/CW PSU WB GM	No
911401509791	BY698P G5 LED150/CW PSU NB GM	No
911401510291	BY698P G5 LED250/NW PSU WB GM	No
911401510391	BY698P G5 LED250/NW PSU NB GM	No
911401510491	BY698P G5 LED250/CW PSU WB GM	No
911401510591	BY698P G5 LED250/CW PSU NB GM	No
911401510691	BY698P G5 LED300/NW PSU WB GM	No
911401510791	BY698P G5 LED300/NW PSU NB GM	No
911401510891	BY698P G5 LED300/CW PSU WB GM	No
911401510991	BY698P G5 LED300/CW PSU NB GM	No
911401519791	BY698P G5 LED250/NW PSD WB GM	Yes
911401519891	BY698P G5 LED250/NW PSD NB GM	Yes
911401519991	BY698P G5 LED250/CW PSD WB GM	Yes
911401520091	BY698P G5 LED250/CW PSD NB GM	Yes

GreenPerform Highbay G5

Order Code	Full Product Name	Dimmable
911401520191	BY698P G5 LED300/NW PSD WB GM	Yes
911401520291	BY698P G5 LED300/NW PSD NB GM	Yes

Order Code	Full Product Name	Dimmable
911401520391	BY698P G5 LED300/CW PSD WB GM	Yes
911401520491	BY698P G5 LED300/CW PSD NB GM	Yes

Approval and Application

Order Code	Full Product Name	Mech. impact protection code
911401525991	BY698X G5 LED150/NW Connected WB GM	IK05
911401526091	BY698X G5 LED150/NW Connected NB GM	IK05
911401526191	BY698X G5 LED150/CW Connected WB GM	IK05
911401526291	BY698X G5 LED150/CW Connected NB GM	IK05
911401526391	BY698X G5 LED200/NW Connected WB GM	IK05
911401526491	BY698X G5 LED200/NW Connected NB GM	IK05
911401526591	BY698X G5 LED200/CW Connected WB GM	IK05
911401526691	BY698X G5 LED200/CW Connected NB GM	IK05
911401526791	BY698X G5 LED250/NW Connected WB GM	IK05
911401526891	BY698X G5 LED250/NW Connected NB GM	IK05
911401526991	BY698X G5 LED250/CW Connected WB GM	IK05
911401527091	BY698X G5 LED250/CW Connected NB GM	IK05
911401527191	BY698X G5 LED300/NW Connected WB GM	IK05
911401527291	BY698X G5 LED300/NW Connected NB GM	IK05
911401527391	BY698X G5 LED300/CW Connected WB GM	IK05
911401527491	BY698X G5 LED300/CW Connected NB GM	IK05
911401509891	BY698P G5 LED200/NW PSU WB GM	IK08
911401509991	BY698P G5 LED200/NW PSU NB GM	IK08
911401510091	BY698P G5 LED200/CW PSU WB GM	IK08
911401510191	BY698P G5 LED200/CW PSU NB GM	IK08
911401518591	BY698P G5 LED105/NW PSD WB GM	IK08
911401518691	BY698P G5 LED105/NW PSD NB GM	IK08
911401518991	BY698P G5 LED150/NW PSD WB GM	IK08
911401519091	BY698P G5 LED150/NW PSD NB GM	IK08
911401519391	BY698P G5 LED200/NW PSD WB GM	IK08

Order Code	Full Product Name	Mech. impact protection code
911401519491	BY698P G5 LED200/NW PSD NB GM	IK08
911401519591	BY698P G5 LED200/CW PSD WB GM	IK08
911401509091	BY698P G5 LED105/NW PSU WB GM	IK08
911401509291	BY698P G5 LED105/CW PSU WB GM	IK08
911401509391	BY698P G5 LED105/CW PSU NB GM	IK08
911401509491	BY698P G5 LED150/NW PSU WB GM	IK08
911401509591	BY698P G5 LED150/NW PSU NB GM	IK08
911401509691	BY698P G5 LED150/CW PSU WB GM	IK08
911401509791	BY698P G5 LED150/CW PSU NB GM	IK08
911401510291	BY698P G5 LED250/NW PSU WB GM	IK08
911401510391	BY698P G5 LED250/NW PSU NB GM	IK08
911401510491	BY698P G5 LED250/CW PSU WB GM	IK08
911401510591	BY698P G5 LED250/CW PSU NB GM	IK08
911401510691	BY698P G5 LED300/NW PSU WB GM	IK08
911401510791	BY698P G5 LED300/NW PSU NB GM	IK08
911401510891	BY698P G5 LED300/CW PSU WB GM	IK08
911401510991	BY698P G5 LED300/CW PSU NB GM	IK08
911401519791	BY698P G5 LED250/NW PSD WB GM	IK08
911401519891	BY698P G5 LED250/NW PSD NB GM	IK08
911401519991	BY698P G5 LED250/CW PSD WB GM	IK08
911401520091	BY698P G5 LED250/CW PSD NB GM	IK08
911401520191	BY698P G5 LED300/NW PSD WB GM	IK08
911401520291	BY698P G5 LED300/NW PSD NB GM	IK08
911401520391	BY698P G5 LED300/CW PSD WB GM	IK08
911401520491	BY698P G5 LED300/CW PSD NB GM	IK08

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401525991	BY698X G5 LED150/NW Connected WB GM	(0.385, 0.380) SDCM<5
911401526091	BY698X G5 LED150/NW Connected NB GM	(0.385, 0.380) SDCM<5
911401526191	BY698X G5 LED150/CW Connected WB GM	(0.316, 0.332) SDCM<5
911401526291	BY698X G5 LED150/CW Connected NB GM	(0.316, 0.332) SDCM<5
911401526391	BY698X G5 LED200/NW Connected WB GM	(0.385, 0.380) SDCM<5
911401526491	BY698X G5 LED200/NW Connected NB GM	(0.385, 0.380) SDCM<5
911401526591	BY698X G5 LED200/CW Connected WB GM	(0.316, 0.332) SDCM<5
911401526691	BY698X G5 LED200/CW Connected NB GM	(0.316, 0.332) SDCM<5
911401526791	BY698X G5 LED250/NW Connected WB GM	(0.385, 0.380) SDCM<5
911401526891	BY698X G5 LED250/NW Connected NB GM	(0.385, 0.380) SDCM<5
911401526991	BY698X G5 LED250/CW Connected WB GM	(0.316, 0.332) SDCM<5
911401527091	BY698X G5 LED250/CW Connected NB GM	(0.316, 0.332) SDCM<5
911401527191	BY698X G5 LED300/NW Connected WB GM	(0.385, 0.380) SDCM<5
911401527291	BY698X G5 LED300/NW Connected NB GM	(0.385, 0.380) SDCM<5
911401527391	BY698X G5 LED300/CW Connected WB GM	(0.316, 0.332) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401527491	BY698X G5 LED300/CW Connected NB GM	(0.316, 0.332) SDCM<5
911401509891	BY698P G5 LED200/NW PSU WB GM	(0.385, 0.380) SDCM<5
911401509991	BY698P G5 LED200/NW PSU NB GM	(0.385, 0.380) SDCM<5
911401510091	BY698P G5 LED200/CW PSU WB GM	(0.316, 0.332) SDCM<5
911401510191	BY698P G5 LED200/CW PSU NB GM	(0.316, 0.332) SDCM<5
911401518591	BY698P G5 LED105/NW PSD WB GM	(0.385, 0.380) SDCM<5
911401518691	BY698P G5 LED105/NW PSD NB GM	(0.385, 0.380) SDCM<5
911401518991	BY698P G5 LED150/NW PSD WB GM	(0.385, 0.380) SDCM<5
911401519091	BY698P G5 LED150/NW PSD NB GM	(0.385, 0.380) SDCM<5
911401519391	BY698P G5 LED200/NW PSD WB GM	(0.385, 0.380) SDCM<5
911401519491	BY698P G5 LED200/NW PSD NB GM	(0.385, 0.380) SDCM<5
911401519591	BY698P G5 LED200/CW PSD WB GM	(0.316, 0.332) SDCM<5
911401509091	BY698P G5 LED105/NW PSU WB GM	(0.385, 0.380) SDCM<5
911401509291	BY698P G5 LED105/CW PSU WB GM	(0.316, 0.332) SDCM<5
911401509391	BY698P G5 LED105/CW PSU NB GM	(0.316, 0.332) SDCM<5

GreenPerform Highbay G5

Order Code	Full Product Name	Initial chromaticity
911401509491	BY698P G5 LED150/NW PSU WB GM	(0.385, 0.380) SDCM<5
911401509591	BY698P G5 LED150/NW PSU NB GM	(0.385, 0.380) SDCM<5
911401509691	BY698P G5 LED150/CW PSU WB GM	(0.316, 0.332) SDCM<5
911401509791	BY698P G5 LED150/CW PSU NB GM	(0.316, 0.332) SDCM<5
911401510291	BY698P G5 LED250/NW PSU WB GM	(0.385, 0.380) SDCM<5
911401510391	BY698P G5 LED250/NW PSU NB GM	(0.385, 0.380) SDCM<5
911401510491	BY698P G5 LED250/CW PSU WB GM	(0.316, 0.332) SDCM<5
911401510591	BY698P G5 LED250/CW PSU NB GM	(0.316, 0.332) SDCM<5
911401510691	BY698P G5 LED300/NW PSU WB GM	(0.385, 0.380) SDCM<5
911401510791	BY698P G5 LED300/NW PSU NB GM	(0.385, 0.380) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401510891	BY698P G5 LED300/CW PSU WB GM	(0.316, 0.332) SDCM<5
911401510991	BY698P G5 LED300/CW PSU NB GM	(0.316, 0.332) SDCM<5
911401519791	BY698P G5 LED250/NW PSD WB GM	(0.385, 0.380) SDCM<5
911401519891	BY698P G5 LED250/NW PSD NB GM	(0.385, 0.380) SDCM<5
911401519991	BY698P G5 LED250/CW PSD WB GM	(0.316, 0.332) SDCM<5
911401520091	BY698P G5 LED250/CW PSD NB GM	(0.316, 0.332) SDCM<5
911401520191	BY698P G5 LED300/NW PSD WB GM	(0.385, 0.380) SDCM<5
911401520291	BY698P G5 LED300/NW PSD NB GM	(0.385, 0.380) SDCM<5
911401520391	BY698P G5 LED300/CW PSD WB GM	(0.316, 0.332) SDCM<5
911401520491	BY698P G5 LED300/CW PSD NB GM	(0.316, 0.332) SDCM<5

