



Trusted performance.. Everyday..

SmartBright Highbay

SmartBright Highbay is a high efficient and reliable LED luminaire. Designed as the point to point replacement for HPI 250W/400W luminaires, it offers customers all the benefits of LED lighting – reduced energy consumption, longer service time and less maintenance. In addition, with using high quality of the optical cover, it provides an excellent quality of light, which effectively improves the comfort of your environment.

Benefits

- \cdot Energy saving up to 65% comparing to HPI-P system
- · Comfort light quality
- · Safe & Reliable
- · Easy installation and retrofitting

Features

- · High efficacy: 130 lumens per watt
- · High quality optical Lens cover
- Lifetime of 30,000 hours @ Ta35℃ with end-to-end Philips production quality assurance
- Full family is in compliance with CB and EMC norms
- · Suitable for pole, hook, bracket mounting


Application


- Industry : Factories, warehouses, workshops, assembly lines, etc.
- · High ceiling indoor : Shopping malls, airports, stadium, etc.

SmartBright Highbay

Dimensional drawing







Product details



SmartBright Highbay G4



SmartBright Highbay G4

SmartBright Highbay

CE mark	CE mark
	CLIIIdik
Flammability mark	-
_ight Technical	
Optical cover type	Lens
Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	130 lm/W
Operating and Electrical	
nput Voltage	220 to 240 V
ine Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-20 to +45 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	Dark gray
Approval and Application	
Protection class IEC	Safety class I
Mech. impact protection code	IK06
ngress protection code	IP65
nitial Performance (IEC Compli	ant)
_uminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Flux
911401614508	BY239P LED240/CW PSU GM G2 C1000	6500 K	26,000 lm
911401614608	BY239P LED180/CW PSU GM G2 C1000	6500 K	19,500 lm
911401614708	BY239P LED120/CW PSU GM G2 C1000	6500 K	13,000 lm
911401639907	BY239P LED70/CW PSU GM G2	6500 K	7,800 lm
911401640007	BY239P LED70/NW PSU GM G2	4000 K	7,800 lm
911401640107	BY239P LED120/CW PSU GM G2	6500 K	13,000 lm
911401640207	BY239P LED120/NW PSU GM G2	4000 K	13,000 lm
911401640307	BY239P LED180/CW PSU GM G2	6500 K	19,500 lm
911401640407	BY239P LED180/NW PSU GM G2	4000 K	19,500 lm
911401640507	BY239P LED240/CW PSU GM G2	6500 K	26,000 lm
911401640607	BY239P LED240/NW PSU GM G2	4000 K	26,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401614508	BY239P LED240/CW PSU GM G2 C1000	200 W
911401614608	BY239P LED180/CW PSU GM G2 C1000	150 W
911401614708	BY239P LED120/CW PSU GM G2 C1000	100 W
911401639907	BY239P LED70/CW PSU GM G2	60 W
911401640007	BY239P LED70/NW PSU GM G2	60 W
911401640107	BY239P LED120/CW PSU GM G2	100 W

Order Code	Full Product Name	Power Consumption
911401640207	BY239P LED120/NW PSU GM G2	100 W
911401640307	BY239P LED180/CW PSU GM G2	150 W
911401640407	BY239P LED180/NW PSU GM G2	150 W
911401640507	BY239P LED240/CW PSU GM G2	200 W
911401640607	BY239P LED240/NW PSU GM G2	200 W

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401614508	BY239P LED240/CW PSU GM G2 C1000	(0.316, 0.332) SDCM<5
911401614608	BY239P LED180/CW PSU GM G2 C1000	(0.316, 0.332) SDCM<5
911401614708	BY239P LED120/CW PSU GM G2 C1000	(0.316, 0.332) SDCM<5
911401639907	BY239P LED70/CW PSU GM G2	(0.316, 0.332) SDCM<5
911401640007	BY239P LED70/NW PSU GM G2	(0.385, 0.380) SDCM<5
911401640107	BY239P LED120/CW PSU GM G2	(0.316, 0.332) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401640207	BY239P LED120/NW PSU GM G2	(0.385, 0.380) SDCM<5
911401640307	BY239P LED180/CW PSU GM G2	(0.316, 0.332) SDCM<5
911401640407	BY239P LED180/NW PSU GM G2	(0.385, 0.380) SDCM<5
911401640507	BY239P LED240/CW PSU GM G2	(0.316, 0.332) SDCM<5
911401640607	BY239P LED240/NW PSU GM G2	(0.385, 0.380) SDCM<5

SmartBright Highbay



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.