

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** PHILIPS

**Supplier's address:** Customer Care Philips, I.B.R.S./C.C.R.I. /Numéro 10461, 5600VB Eindhoven, NL

**Model identifier:** 8718696707531

## Type of light source:

|   |      |                                 |                            |
|---|------|---------------------------------|----------------------------|
| Lighting technology used:                           | LED  | Non-directional or directional: | DLS                        |
| Light source cap-type (or other electric interface) | GU10 |                                 |                            |
| Mains or non-mains:                                 | MLS  | Connected light source (CLS):   | No                         |
| Colour-tuneable light source:                       | No   | Envelope:                       | -                          |
| High luminance light source:                        | No   |                                 |                            |
| Anti-glare shield:                                  | No   | Dimmable:                       | Only with specific dimmers |

## Product parameters

| Parameter | Value | Parameter | Value |
|-----------|-------|-----------|-------|
|-----------|-------|-----------|-------|

### General product parameters:

|  |                          |  |   |
|--|--------------------------|--|---|
| Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer  | 4                        | Energy efficiency class  | F   |
| Useful luminous flux ( $\phi_{use}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°) | 300 in Narrow cone (90°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 4 000   |
| On-mode power ( $P_{on}$ ), expressed in W   | 3,9                      | Standby power ( $P_{sb}$ ), expressed in W and rounded to the second decimal   | 0,00  |
| Networked standby power ( $P_{net}$ ) for CLS, expressed in W and rounded to the second decimal  | -                        | Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set   | 97  |
| Outer dimensions without separate control gear, light-   | Height                   | 54   | Spectral power distribution in the range 250 nm to 800 nm, at full-load |
|  | Width                    | 50   |   |
|  | Depth                    | 50   |   |
|  |                          |  | See image in last page  |

|   |                   |  |                |
|---|-------------------|--|----------------|
| ing control parts and non-lighting control parts, if any (millimetre)   |                   |  |                |
| Claim of equivalent power <sup>(a)</sup>  | Yes               | If yes, equivalent power (W)                                       | 35             |
|   |                   | Chromaticity coordinates (x and y)                                 | 0,382<br>0,380 |
| <b>Parameters for directional light sources:</b>  |                   |  |                |
| Peak luminous intensity (cd)  | 800               | Beam angle in degrees, or the range of beam angles that can be set | 25             |
| <b>Parameters for LED and OLED light sources:</b>   |                   |  |                |
| R9 colour rendering index value   | 70                | Survival factor  | 0,90           |
| the lumen maintenance factor  | 0,96              |  |                |
| <b>Parameters for LED and OLED mains light sources:</b>   |                   |  |                |
| displacement factor (cos $\phi_1$ )   | 0,80              | Colour consistency in McAdam ellipses                              | 3              |
| Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage. | .. <sup>(b)</sup> | If yes then replacement claim (W)                                  | -              |
| Flicker metric (Pst LM)   | 1,0               | Stroboscopic effect metric (SVM)                                   | 0,4            |

(a)'.-' : not applicable;

(b)'.-' : not applicable;

