



1105/1100 DEEP IC Series
Incandescent Insulated Ceiling



1105/1103R
LyteLining™ Non-IC Remodeler Ring

Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Reflector Trim	Frame-In Kit — See Individual Frame-In Kit Specification Sheets			
1105 Matte Black 1105WH Matte White	Incandescent			
	Frame-In Kit	Ceiling Type	Lamping	Height
	1104IC/N 1104ICR	AirSeal® IC IC Remodeler	40W A19 75W PAR38, BR30 65W BR40	7 1/2" 7 1/2"
	1104IC/N 1104ICR	Non-IC Non-IC Remodeler	75W A19 90W PAR38 120W BR40 85W BR30	7 1/2" 7 1/2"
	1102PI 1103R	Non-IC Non-IC Remodeler	100W A19 150W A21, PAR38 BR40	7 3/16" 7 15/16"
	1100DICM 1100DAICM 1100IC 1100AICM	Deep IC Deep AirSeal® IC IC AirSeal® IC	60W A19 100W PAR38 100W BR40	9 1/4" 9 1/4" 7 5/16" 7 1/2"
	1104ICX/N	AirSeal® IC	100W PAR38 100W BR40 60W A19	7 1/4"

Features

- 1. Reflector:** Hydroformed aluminum, .040" minimum thickness; anobrite semi-specular finish for permanent reflectivity; matte white trim flange.
- 2. Step Baffle:** Aluminum step baffle or painted.
- 3. Frame-In Kit:** (1102PI standard frame shown). Other frames listed above and shown on the right. See Frame-In Kit specification sheets for more details.

Options & Accessories

Retaining Clips: **1955** - For Installing in Existing Ceiling
Extra Wide Flange Trim Ring: **1954** - 8-5/8" O.D

Labels


UL (Suitable for Damp Locations), I.B.E.W.

1105 Lytecaster Reflector 6 3/4"

Step Baffle Trim

Certified Test Report No. 2183

Computed by LSI Program **TEST-LITE** Recessed Lytecaster Downlight 6 1/2" Dia. Aperture, Matte Black Step Baffle Two 13W DTT Lamps, Lumen Rating = 860 LMS.



Angle	Mean CP
0	298
5	308
10	326
15	335
20	330
25	318
30	293
35	256
40	207
45	156
50	109
55	67
60	32
65	10
70	2
75	0
80	0
85	0
90	0

Zonal lumens and percentages			
Zone	Lumens	%Lamp	%Luminaire
0-30	269	15.65	43.00
0-40	428	24.89	68.38
0-60	611	35.57	97.73
0-90	626	36.40	100

****Efficiency = 36.4%**

Tested according to IES Procedures.
Test distance exceeds five times the greatest luminous opening of luminaire.

Coefficients of utilization											
Ceiling	80%			70%			50%			0%	
Wall	50	30	10	50	30	10	50	30	10	0	
% WALL RELECTANCE											
Room Cavity Ratio	1	.40	.39	.38	.39	.38	.38	.38	.37	.36	.34
	2	.37	.35	.34	.36	.35	.34	.35	.34	.33	.31
	3	.34	.32	.30	.33	.32	.30	.32	.31	.30	.28
	4	.31	.29	.27	.31	.29	.27	.30	.28	.27	.28
	5	.29	.26	.24	.28	.26	.24	.28	.26	.24	.23
	6	.26	.24	.22	.26	.24	.22	.25	.23	.22	.21
	7	.24	.21	.20	.24	.21	.20	.23	.21	.20	.19
	8	.22	.20	.18	.22	.19	.18	.21	.19	.18	.17
	9	.20	.18	.16	.20	.18	.16	.20	.17	.16	.15
	10	.18	.16	.14	.18	.16	.14	.18	.16	.14	.14
20% Floor Cavity Reflectance											


20% Floor Cavity Reflectance

Conversion Factors: 2 Lt. 13W Quad Tube: White, C.U. x 1.25. 1 Lt 13W Quad Tube: Black, C.U. x 1.3; White, C.U. x 1.5. 150W A21: Black, C.U. x 1.25; White, C.U. x 1.7. 100W A19: Black, C.U. x 1.25; White C.U. x 1.7.

The coefficients of utilization remain the same.

Certified Test Report No. 2108

Computed by LSI Program **TEST-LITE** Recessed Lytecaster Downlight 6 1/4" Dia. Aperture, Matte Black, Black Step Baffle One 150W PAR38 Flood Lamp. Lumen Rating = 1740 LMS.



Angle	Mean CP
0	5295
5	4790
10	3537
15	2043
20	1014
25	544
30	351
35	207
40	94
45	22
50	3
55	0
60	0
65	0
70	0
75	0
80	0
85	0
90	0

Zonal lumens and percentages			
Zone	Lumens	%Lamp	%Luminaire
0-30	1335	77	89.13
0-40	1470	84.48	98.13
0-60	1498	86.10	100
0-90	1498	86.10	100

****Efficiency = 86.1%**

Tested according to IES Procedures. Test distance exceeds five times the greatest luminous opening of luminaire.

Coefficients of utilization											
Ceiling	80%			70%			50%			0%	
Wall	50	30	10	50	30	10	50	30	10	0	
% WALL RELECTANCE											
Room Cavity Ratio	1	.98	.96	.95	.96	.95	.93	.93	.92	.91	.84
	2	.94	.92	.89	.92	.90	.89	.90	.88	.87	.82
	3	.90	.88	.85	.89	.87	.85	.87	.85	.84	.80
	4	.87	.84	.82	.87	.84	.82	.85	.83	.81	.78
	5	.85	.81	.79	.84	.81	.79	.82	.80	.78	.76
	6	.82	.79	.77	.82	.79	.76	.80	.78	.76	.74
	7	.80	.76	.74	.79	.76	.74	.78	.75	.74	.72
	8	.77	.74	.72	.77	.74	.72	.76	.73	.71	.70
	9	.75	.72	.70	.75	.72	.70	.74	.71	.69	.68
	10	.73	.70	.68	.73	.70	.68	.72	.69	.68	.66
20% Floor Cavity Reflectance											

20% Floor Cavity Reflectance

Conversion Factors: 150W PAR38 FL: White, C.U. x 1.1. 150W BR40FL: Black, C.U. x 0.95; White C.U. x 1.1.



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.