Product Information Sheet

COMMISSION DELEGATED REGULATION (ELL) 2019/2015 with regard to energy labelling of light

commission D sources	ELEGATED REGUI	ATION (EU) 2019/2	015 with regard to energ	gy labelling of light		
Supplier's name	or trade mark:	PHILIPS				
Supplier's address: Customer Care Philips, I.B.R.S./C.C.R.I. /Numéro 10461, 5600VB Eindhoven, NL						
Model identifie	r: 9290020683					
Type of light so	urce:					
Lighting technology used:		LED	Non-directional or directional:	DLS		
Light source cap-type		GU10				
(or other electric interface)						
Mains or non-mains:		MLS	Connected light source (CLS):	No		
Colour-tuneable	_	No	Envelope:	-		
High luminance light source:		No				
Anti-glare shield	d:	No	Dimmable:	Only with spe- cific dimmers		
Product parameters						
Parameter		Value	Parameter	Value		
		General product p	parameters:			
Energy consumption in on- mode (kWh/1000 h), rounded up to the nearest integer		4	Energy efficiency class	F		
Useful luminous flux (фuse), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)		345 in Nar- row cone (90°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	3 000		
On-mode power (P _{on}), expressed in W		4,0	Standby power (P _{sb}), expressed in W and rounded to the sec- ond decimal	0,00		
Networked standby power (P _{net}) for CLS, expressed in W and rounded to the second decimal		-	Colour rendering in- dex, rounded to the nearest integer, or the range of CRI-val- ues that can be set	90		
Outer dimen-	Height	54	Spectral power dis-	See image		
sions without	Width	50	tribution in the	in last page		
separate con- trol gear, light-	Depth	50	range 250 nm to 800 nm, at full-load			

ing control parts and non-lighting control parts, if any (millimetre)					
Claim of equivalent power ^(a)	Yes	If yes, equivalent power (W)	50		
		Chromaticity coordinates (x and y)	0,434 0,403		
Parameters for directional light sources:					
Peak luminous intensity (cd)	700	Beam angle in degrees, or the range of beam angles that can be set	36		
Parameters for LED and OLED light sources:					
R9 colour rendering index value	0	Survival factor	0,90		
the lumen maintenance factor	0,93				
Parameters for LED and OLED mains light sources:					
displacement factor (cos φ1)	0,88	Colour consistency in McAdam ellipses	6		
Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage.	_(b)	If yes then replace- ment claim (W)	-		
Flicker metric (Pst LM)	1,0	Stroboscopic effect metric (SVM)	0,4		

(a)'-': not applicable; (b)'-': not applicable;

