



Day-Brite / CFI FluxStream LED sealed strip is a high performing luminaire delivering smooth diffuse light ideal for light industrial, commercial and residential applications with unparalleled energy efficiency.

Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lumens: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering guide

Example: FSX440L840-UNV

Series	Length (nominal)	Lumens <sup>1</sup> (nominal)	Color temp. (K)	Voltage	Driver	Options
FSX						
FSX	4' 4' length	40L 4000 lumens 60L 6000 lumens	830 80 CRI, 3000K 835 80 CRI, 3500K	UNV Universal Voltage 120-277V 120 120V 277 277V 347 347V	blank DIM <sup>3</sup> SDIM <sup>3</sup>	Non-dimming 0-10V 1% dimming Step dimming to 40% input power
	8' 8' length	80L 8000 lumens 120L 12000 lumens  Other lumen packages may be ordered in increments of 1000lm up to 6000 lumens in 4' length or up to 12000 lumens in 8' length.	840 80 CRI, 4000K 850 80 CRI, 5000K			EM06 <sup>2,3</sup> Factory wired Philips Bodine integral emergency pack. Nominal 700lm SWZCSH <sup>4</sup> Interact Pro scalable high bay sensor with integral daylight & occupancy sensing, advanced grouping with dwell time MD360W <sup>5</sup> 120-277V motion detector, factory installed on end cap (ON/OFF) MD360WD <sup>5</sup> 120-277V motion detector, factory installed on end cap (ON/DIM) IP65 IP65 rated protection from water and dust WCW6/6 <sup>6</sup> Factory wired 6' 18/6 white cord for use with 0-10V DIM option plus EM06 WCW6/5 <sup>6</sup> Factory wired 6' 18/5 white cord for use with 0-10V DIM option WCW6/4 <sup>6</sup> Factory wired 6' 16/4 white cord for use with EM06 or SDIM options  Factory wired 6' 16/3 white cord is standard

- Nominal delivered lumens at 25°C ambient.
- EM06 on 8' models illuminates 4' section in emergency mode.
- 3 wire cord is standard. Order proper cord option for dimming or emergency.
- High bay motion detector. Motion sensing zone is extremely limited if used below 15' mounting height.
- Not available with SWZCSH option.
- 6' is standard cord length. For optional 10', 15', or 20' cord length, replace the "6" in the option code with desired length.

### Accessories (order separately, see last page for details)

- FSXWG4 - 4' wire guard (order two for 8' models)
- FSTH - Sliding hanger bracket (set of two)
- DACH48 - Adjustable cable hanger kit (order two per fixture)

### General notes

Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.

# FSX FluxStream LED sealed strip

## 4' and 8', up to 12,000 lumens

### Features

- Compact design for installation in tight spaces.
- Each unit comes standard with a 6' 16/3 wired white cord.
- Sliding hanger bracket set included.
- 4' and 8' lengths available to accommodate many field applications.
- Up to 100,000 hour predicted L70 LED lumen maintenance provides long service life to reduce maintenance costs.
- Can be surface mounted on ceilings or walls, or suspended via chain, or cables with the sliding hanger brackets.
- Ideal for cold applications (-20°C).
- 0-10v dimming driver as standard. Step dimming (100/40%) is optional. Note that special cords are required to utilize dimming or step dimming.
- Optional wet location motion detector factory installed on end cap.
- Luminaire housing tested to IK08 impact standards.
- Fluxstream luminaires are Designlights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (<http://www.designlights.org/QPL>).
- 5 year manufacturer's limited warranty. Visit <https://www.genlyte.com/en-us/support/warranties> for complete warranty information.

### Construction/Finish

- Continuous white polycarbonate extruded housing.
- Frosted polycarbonate diffuser provides wide light distribution and superior glare control.
- White plastic end caps.

### Electrical

- Standard luminaire is non-dimming.
- Dimming to 1% on 0-10V controls optional available. Step dimming (SDIM) option available (100/40%).
- LED boards and drivers are RoHS (Restriction of Hazardous Substances) compliant. Total system life rated at 50,000 hours. Predicted L70 lifetime based on LED manufacturer's supplied LM-80 data and in-situ laboratory testing.

### Labels

- cETLus listed to meet UL1598 Standards suitable for use in wet locations.

### Interact Pro scalable sensor for Foundation, Advanced & Enterprise tiers (SWZCSH and an evolution of SpaceWise)

- SWZCSH is a connected sensor with integral occupancy and daylight sensing and supports wireless mesh connectivity.
- The sensor works in the Foundation mode (similar to SpaceWise) when configured without a gateway or in an Interact Pro Advanced or Enterprise mode if a compatible gateway is used.
- Interact Pro includes an App, a portal and a broad portfolio of wireless luminaires, lamps and retrofit kits all working on the same system.
- Startup is implemented via Interact Pro App (Android or iPhone) & BlueTooth connectivity. The App provides flexibility to choose between a gateway or non gateway mode for setup.
- Setup with the gateway requires wired internet access to the gateway. It is possible to add a gateway at a later point.
- Prepare project configuration steps remotely and use IRT9015 remote


onsite to identify and group devices together.

- Compatible with:
  - UID8451/10 wireless dimmer switch
  - SWS200 wireless scene switch
  - Battery powered IP42 presence sensor OCC sensor IA CM WH 10/1
  - Battery powered IP42 presence & daylight sensor OCC-DL sensor IA CM IP42 WH
  - LCN3110/05 battery powered IP65 presence sensor OCC sensor IA CM IP65 WH
  - LCN3120/05 battery powered IP65 presence & daylight sensor OCC-DL sensor IA CM IP65 WH
- For more information on Interact Pro visit: [www.interact-lighting.com/interactproscalablesystem](http://www.interact-lighting.com/interactproscalablesystem)

# FSX FluxStream LED sealed strip

4' and 8', up to 12,000 lumens

## Dimensions



## Ambient Temperature Data

Configuration	Ambient
FSX440L	-20°C to 40°C
FSX460L	-20°C to 35°C
FSX880L	-20°C to 40°C
FSX8120L	-20°C to 35°C
EM06 option	Minimum 0°C

## FluxStream LED sealed strip, 4', 6000 nominal delivered lumens

## LER - 116

Catalog No.	FSX460L840-UNV-DIM
Test No.	38882
S/MH	1.3
Lamp Type	LED
Lumens/Lamp	6025
Input Watts	52

Comparative yearly lighting energy cost per 1000 lumens - \$2.07 based on 3000 hrs. and \$.08 pwr KWH.

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.

Photometric values based on test performed in compliance with LM-79.

Candlepower					
Angle	End	45	Cross	Back-45	
0	1518	1546	1555	1546	
5	1512	1541	1551	1541	
15	1460	1497	1514	1497	
25	1356	1405	1436	1405	
35	1202	1277	1325	1277	
45	1010	1117	1192	1117	
55	784	936	1046	936	
65	500	753	892	753	
75	258	577	738	577	
85	53	392	589	392	
95	6	269	419	269	
105	6	174	302	174	
115	6	106	202	106	
125	6	63	126	63	
135	7	36	73	36	
145	7	18	38	18	
155	7	11	15	11	
165	7	8	8	8	
175	7	7	7	7	

## Light Distribution

Degrees	Lumens	% Luminaire
0-30	1210	20.1
0-40	2001	33.2
0-60	3674	61.0
0-90	5347	88.7
0-180	6025	100.0

## Average Luminance

Angle	End	45°	Cross
45	20106	15613	14994
55	18992	14191	13912
65	16107	12897	13006
75	12966	11774	12332
85	6492	10282	11925

## Coefficients of Utilization

EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)


pcc	80			70			50		
	70	50	30	70	50	30	50	30	
pw									
RCR									
0	116	116	116	112	112	112	105	105	
1	104	98	93	100	94	90	88	84	
2	93	84	76	89	81	74	76	70	
3	85	73	64	81	71	62	66	59	
4	77	64	55	74	62	53	58	51	
5	71	57	48	68	55	46	52	44	
6	65	51	42	62	50	41	47	39	
7	60	46	37	58	45	36	42	35	
8	56	42	33	54	41	33	39	31	
9	52	39	30	50	37	30	35	28	
10	49	35	27	47	35	27	33	26	

# FSX FluxStream LED sealed strip

4' and 8', up to 12,000 lumens

**Signify  
interact**

## Easy. Effective. Smart.



### Meet Interact

A smart, wireless luminaire level lighting control system (LLLC). A complete solution that combines modern and intuitive technologies for easy installation and specification.

Works with or without gateway

**No IT**

**No light point restrictions**

**Up to 75%** out of the box savings

**Fast & easy**

### Capabilities



Luminaire integrated occupancy and daylight sensing



BMS integration



Human-centric lighting



Connectivity & insights



Full Automation\*



Security

\*Grouping, zoning, dimming, high-end trimming, scenes, scheduling, manual controls

### Benefits



**Up to 80% installation savings<sup>1</sup>**

Compared to installation costs of wired systems



**Up to 5 min faster setup time<sup>2</sup>**

Compared to similar wireless systems



**Less than 2 year payback**

Implement deep energy-saving strategies and claim utility rebates



**1.8x more energy savings**

Compared to conventional control systems



**Up to 2x utility rebates**

Network Interact ready devices and get more utility rebates<sup>3</sup>

1. Versus legacy systems based on installer interviews

2. Based on installer analysis done by Genlyte for a typical multi-zone space

3. Utility programs across US


### Just lights and an App



1. Install the Interact ready fixtures with embedded smart sensor
2. Install the wireless wall switch
3. Configure your setup with the Interact App
4. Leverage the IRT9015 remote accessory to accelerate your setup process
5. Optionally add a gateway for insights and management

**Learn more about Interact:**

Interact includes an app, a web portal, and a comprehensive range of Interact ready wireless luminaires, lamps, retrofit kits, and control devices like switches and sensors that operate within the same system.



# FSX FluxStream LED sealed strip

4' and 8', up to 12,000 lumens

FluxStream LED sealed strip, 4', 4000 nominal delivered lumens

LER - 122

Catalog No.	FSX440L840-UNV-DIM	Candlepower					Light Distribution			Average Luminance			
		Angle	End	45	Cross	Back-45	Degrees	Lumens	% Luminaire	Angle	End	45°	Cross
Test No.	38883	0	1039	1039	1039	1039	0-30	814	20.6	45	12692	10010	9728
S/MH	1.3	5	1017	1036	1044	1036	0-40	1346	34.0	55	11149	9111	9073
Lamp Type	LED	15	979	1004	1017	1004	0-60	2458	62.1	65	9964	7762	8544
Lumens/Lamp	3955	25	907	939	963	939	0-90	3530	89.3	75	7669	7099	7672
Input Watts	32	35	803	852	888	852	0-180	3955	100.0	85	2984	6682	7541
		45	671	742	798	742							
		55	484	621	701	621							
		65	326	466	599	466							
		75	161	355	467	355							
		85	26	258	375	258							
		95	0	177	288	177							
		105	0	114	210	114							
		115	0	70	144	70							
		125	0	38	91	38							
		135	0	18	52	18							
		145	0	6	26	6							
		155	0	2	8	2							
		165	0	1	2	1							
		175	0	0	0	0							

Coefficients of Utilization									
EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)									
pcc	80			70			50		
	70	50	30	70	50	30	50	30	
RCR									
0	116	116	116	113	113	113	105	105	
1	104	98	93	100	95	90	88	85	
2	94	84	77	90	82	75	76	70	
3	85	73	65	81	71	63	66	60	
4	77	65	55	74	63	54	59	51	
5	71	58	48	68	56	47	52	45	
6	65	52	42	63	50	41	47	40	
7	61	47	38	58	45	37	43	35	
8	56	42	34	54	41	33	39	32	
9	53	39	30	51	38	30	36	29	
10	49	36	28	47	35	27	33	26	

## Accessories/Options



Catalog Code	Description
FSTH	Sliding hanger bracket (set of two) - one set included with fixture
DACH48	Adjustable cable hanger kit (order two per fixture)
EM06	Factory wired Philips Bodine integral emergency pack (nominal 700lm)
MD360W	120-277V motion detector, factory installed on end cap (ON/OFF)
MD360WD	120-277V motion detector, factory installed on end cap (ON/DIM)
WCW6/6	Factory wired 6' 18/6 white cord for use with 0-10V DIM option plus EM06
WCW6/5	Factory wired 6' 16/5 white cord for use with 0-10V dimming
WCW6/4	Factory wired 6' 16/4 white cord for use with EM06 or SDIM

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



a signify business

Signify North America Corp.  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.