

CHLORIDE

by Signify

Exit/Emergency

Symmetry series

Remote lamp heads



SR Series (Dual)



S Series (Single)

Project:

Location:

Cat.No:

Type:

Lamps:

Qty:

Notes:

Example: SRH6W

Series	Lamp Wattage/Voltage	Housing Color
SR – 6 V Symmetry Series	6 V	W – White
SR2 – 12 V Symmetry Series	H6 – 6 W Halogen Bi-Pin	B – Black
	H7 – 7 W Halogen Bi-Pin	
	H10 – 10 W Halogen Bi-Pin	
	H12 – 12 W Halogen Bi-Pin	
	12 V	
	T12 – 12 W Halogen Bi-Pin	
	H12F – 12 W Halogen MR16 Flood	
	H20F – 20 W Halogen MR16 Flood	
	H20S – 20 W Halogen MR16 Spot	
	12 V LED	
	M7F – 7 W MR16 LED, 35°	

Example: SH76W

S	Series	Lamp Wattage/Voltage	Backplate Color	Options
S – Symmetry Series	6 V, Tungsten T-5 Wedge Base	12 V, Tungsten	W – White	G – Gasketed for Outdoor Use ²
	T66 – 6 W, 6 VDC	T912 – 9 W, 12 VDC	B – Black	
	T76 – 7 W, 6 VDC	T1212 – 12 W, 12 VDC		
	T96 – 9 W, 6 VDC	T1812 – 18 W, 12 VDC		
	6 V, Halogen T-2 Wedge Base	12 V, Halogen		
	H76 – 7 W, 6 VDC	T12 – 12 W, 12 VDC		
	H106 – 10 W, 6 VDC	12 V, Halogen MR16 Style ¹		
	H126 – 12 W, 6 VDC	H20F – 20 W, 12 VDC		
		H12F – 12W, 12 VDC		
	6 V, Halogen MR11 Style	12 V LED		
	MR5 – Single 5 W	M7F – 7 W MR16 LED, 35°		
	MR10 – Double 5 W			

Footnotes

¹ Halogen 20 W, 12 VDC lamp is a MR16 style.

² A form fitted gasket is supplied to be installed between the luminaire and junction box to protect against water entry. This product is not recommended for use in areas where high wind or high pressure spray washdown could occur.



SR/SR2/S Symmetry series remote lamp heads

6V, 12V

codes and standards

- UL 924 listed (SR, SR2 Series)
- NFPA 101, NEC, IBC, BOCA, and OSHA illumination standard
- Meets ADA specifications for wall mounted lighting fixtures

construction

- The product backplate is constructed of impact-resistant, UL 94 V-0, 5 VA thermoplastic.
- Thermoplastic backplate is designed to mount securely to a single gang recessed wall or ceiling junction box.
- Standard backplate finish is white and is available in black as an option.
- The textured cover (SR, SR2 Series) is UV-stabilized, impact-resistant thermoplastic.
- The SR/SR2 Series is suitable for use in damp locations only while the S Series allows for a gasketing option for outdoor use.

installation


- Furnished low voltage supply wires (12") are connected at the junction box to either a 6 VDC or 12 VDC emergency power source and supplied separately.
- The backplate is secured via a universal knockout pattern to a recessed junction box (hardware supplied by others).
- Keyhole knockout slots are provided for additional support or mounting options.
- If option "G" (gasketed) is selected (S Series), additional caulking may be required around edges of the backplate to provide a proper weather seal.

lamps

- Illumination is provided by halogen or tungsten lamps and a high performance, specular parabolic reflector design which can be adjusted 180° vertically and horizontally.
- A wide variety of lamps are available to meet specific egress requirements.
- The SR/SR2 Series is available with 12 V, 7 W MR16 LED lamps.

dimensions

SR, SR2 units



S units

