

# CHLORIDE

by  Signify

## Exit/Emergency

Synthesis CHT series

Single Phase Uninterruptible  
Power Supply, 14.0KVA



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Model Example: CHTGG14.0S0

CHT	14.0									
Series	Input Voltage	Output Voltage	Unit Size	Battery Time	Nol	Qty Ckt Breakers	Breakers On 2nd Voltage	Qty Nol Ckt Breakers	Nol Voltage	Qty Nol 2nd Voltage
CHT - Chloride Synthesis CHT UPS System for Emergency Lighting Applications	G - 120/240 V J - 277 V L - 120/208 V D <sup>2</sup> - 480 V	G - 120/240 V J - 277 V L - 120/208 V Y - 120/277 V	14.0 - 14.0 kVA	S - 90 min X - 10 min Y - 20 min	0 - None 1 - Yes T - NOL w/TDT	00X - Hardwire 01X - 1 OCB 02X - 2 OCB 03X - 3 OCB 04X - 4 OCB . . 20X - 20 OCB . . 01A - 1 OCBA 02A - 2 OCBA 03A - 3 OCBA . . . 010A - 10 OCBA (maximum pole spaces 20)	00 - 2nd Voltage Hardwire or No 2nd Voltage 01 02 03 . . 19	A - 1 B - 2 C - 3 D - 4 E - 5 F - 6 G - 7 H - 8 I - 9 J - 10 K - 11 L - 12 M - 13 N - 14 O - 15 P - 16 Q - 17 R - 18 S - 19 T - 20 Z - None	1 - First 2 - Second 3 - Both 0 - No NOL	A - 1 B - 2 C - 3 D - 4 E - 5 F - 6 G - 7 H - 8 I - 9 J - 10 K - 11 L - 12 M - 13 N - 14 O - 15 P - 16 Q - 17 R - 18 S - 19 Z - No NOL

#### Footnotes

<sup>1</sup> Optimum operating temperature of batteries is 77°F (25°C).  
 Temperatures above 85°F (30°C) adversely impact battery life.  
<sup>2</sup> Fault current rating = 10 kAIC @ 480 V.

#### unit check list

Catalog No: \_\_\_\_\_

VA Rating: 14000

Battery Type: Sealed Lead Calcium

Operating Time: 90/20/10 Min.

Utility Input: \_\_\_\_\_ VAC, Single Phase

Output Circuit Breakers:

	Normally ON	Normally OFF	Trip Alarm
Qty: _____ AC Volts: _____ Amps: _____	<input type="checkbox"/>	<input type="checkbox"/>	YES <input type="checkbox"/> NO <input type="checkbox"/>
Qty: _____ AC Volts: _____ Amps: _____	<input type="checkbox"/>	<input type="checkbox"/>	YES <input type="checkbox"/> NO <input type="checkbox"/>
Qty: _____ AC Volts: _____ Amps: _____	<input type="checkbox"/>	<input type="checkbox"/>	YES <input type="checkbox"/> NO <input type="checkbox"/>
Qty: _____ AC Volts: _____ Amps: _____	<input type="checkbox"/>	<input type="checkbox"/>	YES <input type="checkbox"/> NO <input type="checkbox"/>

Remarks: \_\_\_\_\_



# CHT Synthesis Single Phase Uninterruptible Power Supply

14.0 KVA

---

## codes and standards

- UL 924 listed

## construction

- Free standing, NEMA 1 enclosure with lockable control access panel.
- Double conversion, no interruption.
- Solid state pulse width modulated inverter.
- Internal, make before break maintenance by-pass.
- Standard, UL 924 compliant, 90 minute battery back up.
- UL 924 auxiliary equipment 10 and 20 minute back up available.
- Microprocessor control and diagnostic system.
- LCD readout system status panel.
- Local 25 event logging/display.
- User programmable automatic testing.
- Load integrity testing.
- Fault annunciating audible alarm.
- Current limiting start sequence.
- Optional output circuit breakers (OCB) and circuit breakers with trip alarm (OCBA).
- Optional normally off load (NOL) energizes only during power outage, normally off load with time delay (TDT) also available.
- Seismic anchoring compatible.
- 87% throughput efficiency, 85% emergency efficiency.
- Operating temperature range 32°F (0°C) to 104°F (40°C)1.
- Fault current rating 42 kAIC2.
- Audible noise less than 50 dB at 3 ft on "A" weighted scale.
- Automatic low battery voltage disconnect.

## application

- The solid state pulse width modulated (PWM) inverter offers enhanced load compatibility.
- It operates incandescent, magnetic and electronic ballast fluorescent, high power factor compact fluorescent and high intensity discharge (HID) luminaries.
- Provides conditioned, uninterruptible power for other types of critical loads.
- Consult factory for non-lighting load applications.

## electronics - input

- Input power factor correcting to 0.99.
- Frequency range 60 Hz,  $\pm 2.5$  Hz.
- Input harmonic current distortion < 5% THD.
- UL1449, ANSI/IEEE C62.41 surge suppression.

## electronics - output

- Sine wave output.
- Voltage regulation  $\pm 2\%$ .
- Frequency regulation - synchronized to utility, free running 60 Hz,  $\pm 0.5\%$ .
- Output voltage distortion maximum 3% THD with linear load.
- Load power factor capability 0.7 lead to 0.7 lag.
- Overload capability 125% for 10 seconds.


## warranty

- Standard warranty: (requires execution of factory start-up within 120 days of shipment) Chloride will provide parts and on-site labor for the first 12 months following start-up of the product, and parts only for an additional 12 months. If factory start-up is not executed within 120 days of shipment, Chloride will provide a parts warranty for 12 months from the date of shipment.
- Extended warranty available: consult factory for extended warranty and service option.

# CHT Synthesis Single Phase Uninterruptible Power Supply

14.0 KVA

## dimensions



## system input/output

System Rating (kW/kVA)	14.0
Input Volt. (V) : Input Curr. (A)	120/240 : 77.0 277 : 68.2 120/208 : 88.8 480 : 39.4
Output Volt. : Output Current*	120/240 : 116.7/58.3 277 : 50.4 120/208 : 116.7/67.3 120/277 : 116.7/50.4
OCB Pole Spaces Available	
Without Trip Alarm	20
With Trip Alarm	10
Heat Rejection (btu/hr)	6684
Weight (lbs)	
Electronics	1100
Empty Battery Cabinet	350
90 Min Battery	3126
20 Min Battery	2348
10 Min Battery	2146

\* Multi-voltage total loads not to exceed system rating.

## system one-line diagram

