



# Solar Panel Sub System

## 115W 17V Panel subsystem Vmpp 18V

A Range of Solar panels from 20 W to 325 W specially designed for Philips Solar Street lighting, Flood lighting and Solar Indoor Systems

### Product data

<b>General Information</b>	
CE mark	CE mark
Warranty period	3 years
<b>Operating and Electrical</b>	
Panel type	Poly crystalline
Panel voltage	17 V
Panel peak wattage	115 W
Cable connection kit	Included
Cable	Cable 1.0 m 4.0 sqmm with Molex Connectors
<b>Temperature</b>	
Ambient temperature range	-40 to +85 °C
<b>Mechanical and Housing</b>	
Overall length	1,125 mm
Overall width	666 mm

Overall height	35 mm
Dimensions (Height x Width x Depth)	35 x 666 x 1125 mm
<b>Approval and Application</b>	
Ingress protection code	IP67 [Dust penetration-protected, watertight]
<b>Product Data</b>	
Order product name	115W 17V Panel subsystem Vmpp 18V
Full product name	115W 17V Panel subsystem Vmpp 18V
Full product code	911401803602
Order code	911401803602
Material Nr. (12NC)	911401803602
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30

Solar Panel Sub System

Dimensional drawing

