



Essential SmartBright LED Downlight

DN027B G3 LED9/CW 9W 220-240V D125 RD

Essential SmartBright LED Downlight, 9 W, 950 lm, 6500 K, Beam angle 110°, White

Essential SmartBright G2 LED Downlight is value for money product with high efficacy, good quality and reliability. It offers multiple configurations from 300lm to 2000lm output, to replace conventional downlight. It can be used for shopping mall, retail store, residential and office. It's an ideal product family to distribute in trade market.

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Lighting Technology	LED
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	950 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	105.00 lm/W
Color rendering index (CRI)	80


Light source color	865 cool daylight
Optic type	Beam angle 110°
Luminaire light beam spread	110°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Inrush current	2.25 A
Inrush time	0.101 ms
Power Consumption	9 W
Power Factor (Fraction)	0.9
Cable	Cable 0.2 m without plug
Number of products on MCB of 16 A type B 86	

Essential SmartBright LED Downlight

Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No
Mechanical and Housing	
Housing Material	Metal-Plastic
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Matte
Overall length	150 mm
Overall width	150 mm
Overall height	42 mm
Overall diameter	150 mm
Dimensions (Height x Width x Depth)	42 x 150 x 150 mm
Approval and Application	
Ingress protection code	IP20/40 [Finger-protected, Emitting surface]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II



Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(IEC6500K, 0.313, 0.337) < 5SDCM
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.012 %
Median useful life L70B50	30,000 hour(s)
Application Conditions	
Suitable for random switching	No
Product Data	
Order product name	DN027B G3 LED9/CW 9W 220-240V D125 RD
Full product name	DN027B G3 LED9/CW 9W 220-240V D125 RD
Full product code	871951434500300
Order code	929002672938
Material Nr. (12NC)	929002672938
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514345003
Numerator - Packs per outer box	24
EAN/UPC - Case	8719514345010

Dimensional drawing



Essential SmartBright LED Downlight

Photometric data



General uniform lighting - DN027B G3 LED9/CW 9W 220-240V D125 RD

Light Distribution Diagram - DN027B G3 LED9/CW 9W 220-240V D125 RD

