



MASTER LEDspot LV

MASTER LED 7.5-50W+ 827 MR16 36D Dim

Delivering intense accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot lighting. MASTER LEDspot LV is designed to replace halogen or incandescent spots. It realizes natural colors, enables cozy and comfortable ambience for residential, hospitality and emphasizes the beauty of merchandise in retail. New smaller housing provides perfect fitting with majority of luminaires in a market with a MR16 GU 5.3 holder. It not only employs Philips' patented solution to guarantee the broadest possible compatibility with standard 12V halogen electronic transformers, it also delivers high beam intensity which is equivalent to halogen MR16 spots. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers. Its high SDCM ensure stricter color consistency, that is maintained over product life. MASTER LEDspot LV delivers huge energy savings and minimizes maintenance cost without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within short period time.

Product data


General Information		Correlated Color Temperature (Nom)	2700 K
Cap-Base	GU5.3	Luminous Efficacy (rated) (Nom)	88.00 lm/W
Nominal lifetime	40,000 hour(s)	Color Consistency	<4
Switching Cycle	50,000	Color rendering index (CRI)	80
Lighting Technology	LED	LLMF At End Of Nominal Lifetime (Nom)	70 %
EU RoHS compliant	Yes	Operating and Electrical	
Light Technical		Line Frequency	- Hz
Color Code	827 [CCT of 2700K]	Input Frequency	- Hz
Beam Angle (Nom)	36 degree(s)	Power Consumption	7.5 W
Luminous Flux	660 lm	Lamp Current (Nom)	720 mA
Luminous Intensity (Nom)	1,700 cd	Wattage Equivalent	50 W
Color Designation	Warm White (WW)	Starting Time (Nom)	0.5 s

MASTER LEDspot LV

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case Maximum (Nom)	93 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Shape	MR16
Approval and Application	
Suitable For Accent Lighting	Yes


Product Data	
Order product name	MASTER LED 7.5-50W+ 827 MR16 36D Dim
Full product name	MASTER LED 7.5-50W+ 827 MR16 36D Dim
Full product code	871951435809600
Order code	929003072708
Material Nr. (12NC)	929003072708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514358096
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514358102

Dimensional drawing




Product	D	C
MASTER LED 7.5-50W+ 827 MR16 36D Dim	50 mm	46.5 mm

Photometric data



Technical Information 12 V Page 10




Accent Lighting Spots - MASTER LED 7.5-50W+ 827 MR16 36D Dim

Spectral Power Distribution Colour - MASTER LED 7.5-50W+ 827 MR16 36D Dim


MASTER LEDspot LV

Photometric data




Light Distribution Diagram - MASTER LED 7.5-50W+ 827 MR16 36D Dim

Lifetime



Life Expectancy Diagram - MASTER LED 7.5-50W+ 827 MR16 36D Dim



Lumen Maintenance Diagram - MASTER LED 7.5-50W+ 827 MR16 36D Dim

