

# LED G25

## 3.5G25/PER/UD50/CL/G/E26/D 4/2PFT20

Philips G25 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	950 [CCT of 5000K]
Color Code	950 [CCT of 5000K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	350 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<4
Color rendering index (CRI)	95
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	3.5 W

Lamp Current (Nom)	40 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.4 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
Ambient temperature range	-4 °F to 104 °F

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	G25
UL Wet/ damp/ dry location	Wet location


Approval and Application	
Energy Certifications	Energy Star
EyeComfort	Yes
T20 compliant	Yes

# LED G25

LED Innovations	EyeComfort
<b>Application Conditions</b>	
can it be used in closed luminaires	No
<b>Product Data</b>	
Order product name	3.5G25/PER/UD50/CL/G/E26/D 4/2PFT20
Full product name	3.5G25/PER/UD50/CL/G/E26/D 4/2PFT20



Order code	573337
Material Nr. (12NC)	929003084903
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677573331
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677573336

## Dimensional drawing




Product	D	C
3.5G25/PER/UD50/CL/G/E26/D 4/2PFT20	3-3/16 inch	4-11/16 inch

## Photometric data



General uniform lighting - 3.5G25/PER/UD50/CL/G/E26/D 4/2PFT20

Spectral Power Distribution Colour - 3.5G25/PER/UD50/CL/G/E26/D 4/2PFT20



Light Distribution Diagram - 3.5G25/PER/UD50/CL/G/E26/D 4/2PFT20

# LED G25

## Lifetime



Life Expectancy Diagram - 3.5G25/PER/UD50/CL/G/E26/D 4/2PFT20

Lumen Maintenance Diagram - 3.5G25/PER/UD50/CL/G/E26/D 4/2PFT20

