

LM-79-08 Test Report

for

Philips Lighting (China) Investment Co., Ltd

Building 9, Lane 888, Tianlin Road, Minhang District, Shanghai China

TYPEB LED TUBE

Model: 9290019348

Laboratory: Leading Testing Laboratories

NVLAP CODE: 200960-0

3rd Floor, Bld. 2, NO. 96 Longchuanwu Rd Qianjiang Economy Dev. Zone, Yuhang Dist,
Hangzhou, Zhejiang Province, China 311100

Tel: +86 571 86376106

www.ledtestlab.com

Report No.: HZ18050046c

The laboratory that conducted the testing detailed in this report has been accredited for SSL by NVLAP.

Review by:



Engineer: April Zou

Jun. 05, 2018

Approved by:



Manager: Jim Zhang

Jun. 05, 2018

Note: This report does not imply product certification, approval, or endorsement by NVLAP, NIST, or any agency of the Federal Government.

Test Summary

Sample Tested: **9290019348**

Luminous Efficacy (Lumens /Watt)	Total Luminous Flux (Lumens)	Power (Watts)	Power Factor
144.3	2140.0	14.83	0.9825
CCT (K)	CRI	Stabilization Time (Light & Power)	
3942	83.1	60	

Table 1: Executive Data Summary

Note: The above results are recorded/ derived from measurements made using an Integrating Sphere.

Test specifications:

Date of Receipt : May 25, 2018

Date of Test : May 31, 2018

Test item : Total Luminous Flux, Luminous Distribution Intensity, Luminous Efficacy, Correlated Color Temperature, Color Rendering Index, Chromaticity Coordinate, Electrical parameters

Reference Standard : IESNA LM-79-2008 Approved Method for the Electrical and Photometric Measurements of Solid-State Lighting Products

TABLE OF CONTENT

LM-79-08 Test Report.....	1
Test Summary.....	2
Sample Photo.....	4
TEST RESULTS	5
Goniophotometer Method	6
Spectral Power Distribution - Sphere Spectroradiometer Method	7
Chromaticity Diagram - Sphere Spectroradiometer Method.....	8
Nominal CCT Quadrangles – Sphere Spectroradiometer Method	9
Zonal Lumen Tabulation- Goniophotometer Method	10
Luminous Intensity Distribution Plots- Goniophotometer Method.....	12
Luminous Intensity Data- Goniophotometer Method.....	13
EQUIPMENT LIST	15
TEST METHODS	15
Seasoning of SSL Product.....	15
Sphere-Spectroradiometer Method- Photometric and Electrical Measurements.....	15
Goniophotometer Method	16
Photometric and Electrical Measurements.....	16
Color Characteristics Measurements.....	16
Color Spatial Uniformity	16

Sample Photo



Figure 1- Overview of the sample

Equipment Under Test (EUT)

Name	: TYPEB LED TUBE
Model	: 9290019348
Electrical Ratings	: 120-277V, 50/60Hz, 15.5W
Product Description	: 15.5T8-6U PRO/24-840/BB21/G FB
Manufacturer	: Philips Lighting (China) Investment Co., Ltd
Address	: Building 9, Lane 888, Tianlin Road, Minhang District, Shanghai China

TEST RESULTS

Test ambient temperature was 25.0°C.

Base orientation was light down. Test was conducted without a dimmer in the circuit.

The stabilization time of the sample was 60 minutes, and the total operating time including stabilization was 65 minutes.

Sphere-Spectroradiometer Method

Parameter	Result	
Test Voltage (V)	120.0	277.0
Voltage frequency (Hz)	60	60
Test Current (A)	0.126	0.057
Power Factor	0.9825	0.9298
Test Power (W)	14.83	14.72
THD A%	17.81	20.16
Luminous Efficacy (lm/W)	144.3	144.7
Total Luminous Flux (lm)	2140.0	2130.0
Color Rendering Index (CRI)	83.1	
R9	5.9	
Correlated Color Temperature (CCT) (K)	3942	
Chromaticity Chroma x	0.3840	
Chromaticity Chroma y	0.3819	
Chromaticity Chroma u	0.2254	
Chromaticity Chroma v	0.3362	
Duv	0.0013	
Chromaticity Chroma u'	0.2254	
Chromaticity Chroma v'	0.5044	

Special Color Rendering Indices	
R1	81.2
R2	91.1
R3	96
R4	80.5
R5	81.5
R6	87.6
R7	84.7
R8	62.4
R9	5.9
R10	78.8
R11	79.4
R12	64.8
R13	83.9
R14	98.3
Rf	82
Rg	94

Table 2: Test data per Sphere-Spectroradiometer Method

Note: According to CIE 1976 (u' , v') diagram, $u' = u = 4x/(-2x+12y+3)$, $v' = 3v/2 = 9y/(-2x+12y+3)$.

Goniophotometer Method

Test ambient temperature was 24.7°C.

The photometric distance is 30m.

Luminous data was taken at 0.5°vertical intervals and 10°horizontal intervals.

Parameter	Result
Test Voltage (V)	120.0
Voltage frequency (Hz)	60
Test Current (A)	0.127
Power Factor	0.9795
Test Power (W)	14.93
Luminous Efficacy (lm/W)	142.1
Total Luminous Flux (lm)	2121.7
Beam Angle (°)	107.7 (0°-180°)/ 198.5 (90°-270°)
Center Beam Candle Power (cd)	380
Maximum Beam Candle Power (cd)	382.7 (At: C=90.0, Gamma=10.0)
Spacing Criteria	1.24 (0°-180°)/ 1.36 (90°-270°)
Zonal Lumens in the 0°-60°Zone	44.93%
Zonal Lumens in the 60°-90°Zone	25.22%
Zonal Lumens in the 90°-120°Zone	15.57%
Zonal Lumens in the 120°-180°Zone	14.28%

Table 3: Test data per Goniophotometer Method

Spectral Power Distribution - Sphere Spectroradiometer Method




Chart 1: Spectral Power Distribution

Spectral Distribution over Visible Wavelength							
WL(nm)	Radiant(Watts)	WL(nm)	Radiant(Watts)	WL(nm)	Radiant(Watts)	WL(nm)	Radiant(Watts)
380	3.98E-04	485	1.40E-02	590	3.75E-02	695	5.41E-03
385	3.83E-04	490	1.52E-02	595	3.78E-02	700	4.63E-03
390	4.24E-04	495	1.68E-02	600	3.74E-02	705	3.96E-03
395	4.57E-04	500	1.87E-02	605	3.66E-02	710	3.37E-03
400	5.16E-04	505	2.04E-02	610	3.55E-02	715	2.88E-03
405	5.97E-04	510	2.17E-02	615	3.40E-02	720	2.48E-03
410	7.85E-04	515	2.29E-02	620	3.22E-02	725	2.11E-03
415	1.14E-03	520	2.38E-02	625	3.01E-02	730	1.81E-03
420	1.76E-03	525	2.46E-02	630	2.80E-02	735	1.54E-03
425	2.94E-03	530	2.54E-02	635	2.56E-02	740	1.32E-03
430	4.79E-03	535	2.62E-02	640	2.33E-02	745	1.13E-03
435	7.95E-03	540	2.72E-02	645	2.09E-02	750	9.69E-04
440	1.33E-02	545	2.82E-02	650	1.88E-02	755	8.31E-04
445	2.34E-02	550	2.92E-02	655	1.66E-02	760	7.16E-04
450	3.53E-02	555	3.04E-02	660	1.47E-02	765	6.11E-04
455	3.56E-02	560	3.15E-02	665	1.29E-02	770	5.28E-04
460	2.63E-02	565	3.28E-02	670	1.12E-02	775	4.57E-04
465	2.12E-02	570	3.40E-02	675	9.74E-03	780	3.90E-04
470	1.80E-02	575	3.53E-02	680	8.44E-03		
475	1.45E-02	580	3.62E-02	685	7.29E-03		
480	1.34E-02	585	3.73E-02	690	6.28E-03		

Table 4: Spectral Power Distribution Numerical Data per Sphere - Spectroradiometer Method

Chromaticity Diagram - Sphere Spectroradiometer Method




Chart 2: Chromaticity Diagram per Sphere - Spectroradiometer Method

Note: The location on the diagram of the tristimulus coordinates are indicated by the blue diamond.

Nominal CCT Quadrangles – Sphere Spectroradiometer Method




Chart 3: Plot of Lamp x/y coordinates on CIE 1931 Chromaticity Diagram

Zonal Lumen Tabulation- Goniophotometer Method

$\gamma(^{\circ})$	Lumens	% Total
0- 10	36.054	1.70%
10- 20	104.183	4.91%
20- 30	161.12	7.59%
30- 40	201.682	9.51%
40- 50	223.41	10.53%
50- 60	226.773	10.69%
60- 70	214.538	10.11%
70- 80	188.985	8.91%
80- 90	131.67	6.21%
90-100	101.484	4.78%
100-110	119.993	5.66%
110-120	108.905	5.13%
120-130	93.228	4.39%
130-140	76.968	3.63%
140-150	59.955	2.83%
150-160	42.48	2.00%
160-170	24.284	1.14%
170-180	6.031	0.28%
Total	2121.7	100%

$\gamma(^{\circ})$	Lumens	% Total
0- 60	953.222	44.93%
60- 90	535.193	25.22%
0-90	1488.415	70.15%
90- 180	633.328	29.85%
0- 180	2121.7	100%

Table 5: Zonal Lumen Data




Chart 4: Illuminance Plot (Footcandles)

Luminous Intensity Distribution Plots- Goniophotometer Method




Chart 5: Isocandela Plot




Chart 6: Polar Candela Distribution

Luminous Intensity Data- Goniophotometer Method

Table--1

UNIT: cd

C (DEG) y (DEG)	0	10	20	30	40	50	60	70	80	90	100	110	120	130	140	150	160	170	180
0	380	380	380	380	380	380	380	380	380	380	380	380	380	380	380	380	380	380	380
5	378	379	379	380	380	381	381	382	382	382	382	382	382	381	381	380	380	379	379
10	372	373	374	376	377	379	380	381	382	383	383	382	381	380	379	377	376	374	373
15	362	364	366	369	372	375	378	380	381	382	382	380	379	376	374	371	368	366	364
20	349	351	354	359	363	368	373	376	379	380	379	377	374	370	366	361	357	354	352
25	332	335	340	346	353	360	366	371	375	376	375	373	368	362	356	349	343	338	336
30	312	316	322	330	340	349	358	365	370	371	371	367	361	352	343	334	326	320	316
35	290	294	302	313	325	337	349	357	363	366	364	359	351	341	329	317	307	299	295
40	265	270	280	293	309	324	338	349	356	359	357	351	341	328	313	298	285	275	270
45	239	244	256	273	291	310	326	339	347	351	349	341	329	314	296	278	261	249	244
50	211	217	231	251	273	295	314	329	338	342	339	331	317	299	278	257	237	222	215
55	181	189	206	229	255	280	301	318	329	333	330	320	305	284	260	235	211	193	186
60	151	159	180	207	237	265	289	307	318	323	320	309	292	269	242	213	185	164	155
65	120	130	155	186	219	250	276	295	307	311	308	297	279	254	224	192	160	134	124
70	89.1	101	131	167	203	235	262	282	294	299	295	284	265	239	207	171	135	105	92.1
75	59.9	74.0	109	149	187	220	247	266	278	282	279	267	248	222	190	153	113	77.7	61.6
80	33.1	50.7	89.6	131	170	202	228	246	258	262	259	248	228	201	169	133	92.4	54.0	34.1
85	12.5	32.3	69.8	108	138	160	176	189	196	200	198	191	178	160	135	104	68.0	33.4	12.5
90	1.85	14.2	39.4	66.6	82.0	98.5	111	122	130	132	130	123	112	96.0	76.9	59.1	32.0	10.3	0.79
95	5.32	21.4	52.3	83.6	113	133	148	160	167	170	167	159	146	128	107	79.5	46.9	21.0	4.59
100	10.7	26.3	55.7	92.1	124	152	173	190	202	206	203	192	174	150	122	89.8	57.1	27.5	9.92
105	17.4	29.7	57.3	91.0	124	152	174	191	200	204	201	190	173	151	125	93.7	59.6	32.8	16.9
110	25.2	34.2	59.5	89.2	119	147	171	188	197	199	196	187	171	149	122	92.5	62.0	38.5	24.8
115	33.1	41.6	60.7	88.4	115	140	162	178	187	190	187	178	163	142	118	91.6	64.4	44.9	32.9
120	40.9	49.2	62.5	88.1	112	134	153	168	176	179	176	168	154	136	114	91.2	67.3	51.4	41.0
125	48.7	56.0	65.6	86.3	108	128	145	158	166	168	166	158	146	130	111	90.6	70.4	57.9	48.9
130	56.2	62.5	69.1	85.5	104	123	137	149	155	158	156	149	139	125	108	90.3	72.8	64.2	56.4
135	63.0	68.6	73.4	85.4	101	116	130	140	146	148	146	141	132	119	105	89.7	76.1	69.9	63.2
140	68.7	73.5	76.9	85.6	97.4	111	122	131	136	138	137	132	124	114	101	90.0	79.5	74.2	68.9
145	74.6	77.7	80.0	87.2	95.9	104	114	122	127	129	127	124	117	108	99.6	90.2	80.5	78.8	73.9
150	79.9	81.5	82.9	88.2	95.6	101	108	113	116	118	118	115	111	104	97.6	89.2	82.3	82.7	77.9
155	83.7	84.9	85.0	87.1	93.9	99.4	103	107	110	111	110	108	105	101	93.9	87.9	84.4	84.5	81.1
160	86.4	86.9	86.7	87.6	90.0	93.2	98.2	102	104	105	105	103	99.8	94.1	90.2	87.9	85.6	85.5	84.5
165	84.1	83.2	84.9	83.5	85.8	91.7	93.1	94.9	95.7	96.5	96.5	96.1	91.6	88.7	84.3	80.4	79.8	80.8	80.2
170	75.1	67.6	72.4	78.2	78.2	77.6	80.1	85.2	91.6	93.4	85.0	75.8	74.4	73.5	71.8	68.2	66.0	65.4	65.6
175	51.7	51.4	51.1	50.7	51.8	58.4	63.0	57.9	53.5	55.5	58.0	57.3	52.0	49.7	49.8	49.2	48.0	47.7	48.4
180	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7

Table 6: Luminous Intensity Data

Table--2

UNIT: cd

C (DEG) y (DEG)	190	200	210	220	230	240	250	260	270	280	290	300	310	320	330	340	350		
0	380	380	380	380	380	380	380	380	380	380	380	380	380	380	380	380	380		
5	378	378	378	377	377	377	377	377	377	377	377	377	377	377	377	377	378		
10	373	372	372	372	372	372	372	372	372	372	372	372	371	371	371	371	371		
15	363	363	363	364	365	366	366	367	367	366	366	365	363	362	361	361	361		
20	351	351	351	353	355	357	359	360	360	359	358	356	354	351	349	348	348		
25	334	335	337	340	344	347	350	352	352	351	349	346	342	338	335	332	331		
30	315	317	321	326	331	336	340	343	344	342	340	335	329	324	318	314	312		
35	294	297	302	309	317	324	330	333	335	333	329	323	315	307	299	293	290		
40	270	274	282	292	302	312	319	323	325	323	318	311	301	290	280	271	266		
45	244	250	261	273	287	298	307	313	315	313	307	298	286	272	259	247	240		
50	216	225	239	255	271	285	296	302	305	302	295	285	270	254	237	223	213		
55	188	199	217	236	255	271	284	291	294	291	284	271	255	236	216	198	185		
60	159	174	195	218	240	258	272	280	283	280	272	258	240	218	195	173	157		
65	130	149	174	200	225	245	259	268	271	268	259	245	225	201	174	149	128		
70	101	125	155	184	209	230	245	254	257	255	246	231	210	185	156	125	100		
75	73.1	102	136	167	193	214	230	239	242	239	230	215	195	168	138	104	73.7		
80	49.1	82.4	117	148	174	195	211	220	223	220	211	196	177	152	120	85.1	50.6		
85	29.5	60.2	91.6	120	143	159	171	178	180	177	171	161	148	127	98.6	65.8	32.3		
90	7.98	26.0	45.6	64.4	80.5	93.3	103	108	110	108	103	94.1	83.5	70.2	54.1	35.1	13.3		
95	15.3	35.0	60.9	82.0	98.3	112	122	126	129	127	123	114	102	88.4	68.5	43.6	18.8		
100	20.0	43.5	71.3	95.5	120	140	155	162	165	162	155	141	123	101	76.3	46.7	21.9		
105	24.4	45.2	72.5	99.1	123	140	153	160	163	160	153	143	126	102	74.5	47.0	25.9		
110	29.9	46.9	71.5	96.2	118	137	150	158	161	158	151	139	120	97.4	72.7	48.2	31.3		
115	36.4	49.5	70.7	92.8	113	130	142	150	153	150	143	131	114	93.4	71.5	50.8	37.4		
120	43.2	53.1	70.7	89.7	108	123	134	142	144	142	135	124	108	90.4	71.3	54.2	41.3		
125	50.2	57.2	71.5	87.4	103	116	127	133	135	133	127	117	103	88.1	72.2	58.1	49.1		
130	56.5	61.6	73.0	86.1	99.2	111	120	125	127	125	120	111	99.6	86.9	73.7	61.0	55.9		
135	62.5	65.9	75.0	85.6	96.3	106	113	118	120	118	113	106	96.7	86.2	75.6	63.6	60.6		
140	68.5	69.7	76.7	85.7	94.2	102	108	112	113	112	108	102	94.4	86.0	76.3	68.4	66.2		
145	73.4	72.5	76.7	85.8	92.6	98.5	103	106	107	106	103	98.6	92.7	86.2	74.8	71.5	72.4		
150	77.6	74.8	79.8	82.6	89.8	95.9	99.3	102	102	102	99.4	96.0	91.3	82.0	79.0	72.5	76.9		
155	77.4	77.5	81.0	84.7	85.8	87.6	95.9	97.8	98.3	97.8	96.0	91.8	86.2	84.2	80.1	76.2	80.5		
160	80.8	80.0	82.1	84.9	87.9	88.1	85.7	91.0	92.6	91.6	90.4	89.0	88.3	84.7	81.1	78.0	83.1		
165	77.6	76.9	77.7	81.7	84.8	88.4	89.4	88.6	85.6	86.5	87.5	86.1	82.9	82.1	80.6	78.8	82.4		
170	65.1	64.7	66.9	70.1	70.4	72.4	77.9	83.9	85.2	85.0	85.1	84.4	80.4	75.1	74.0	76.0	77.9		
175	48.1	48.6	49.2	50.4	52.8	56.8	60.5	62.2	61.2	60.5	61.3	62.7	63.3	63.7	65.4	66.5	57.4		
180	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7		

Table 7: Luminous Intensity Data

EQUIPMENT LIST

Test Equipment	Model	Equipment No.	Calibration Date	Calibration Due date
Goniophotometer system	GO-R5000	HZTE011-01	Aug. 23, 2017	Aug. 22, 2018
Digital Power Meter	PF2010A	HZTE028-01	Aug. 10, 2017	Aug. 09, 2018
AC Power Supply	DPS1060	HZTE001-06	Aug. 10, 2017	Aug. 09, 2018
DC Power Supply	WY12010	HZTE004-03	Aug. 10, 2017	Aug. 09, 2018
Temperature recorder	JM624U	HZTE018-08	Aug. 17, 2017	Aug. 16, 2018
Temperature and humidity recorder	JR900	HZTE018-01	Aug. 16, 2017	Aug. 15, 2018
Standard source	D908	HZTE012-01	Aug. 20, 2017	Aug. 19, 2018
Integrate Sphere system	2M	HZTE015-01	Aug. 23, 2017	Aug. 22, 2018
Digital Power Meter	WT210	HZTE008-01	Aug. 10, 2017	Aug. 09, 2018
AC Power Supply	PCR 500L	HZTE001-07	Aug. 10, 2017	Aug. 09, 2018
DC Power Supply	IT6154	HZTE004-04	Aug. 10, 2017	Aug. 09, 2018
Standard source	SCL-1400	HZTE012-02	Aug. 20, 2017	Aug. 19, 2018
Temperature and humidity recorder	JR900	HZTE018-02	Aug. 16, 2017	Aug. 15, 2018
Temperature Meter	TES1310	HZTE017-01	Aug. 17, 2017	Aug. 16, 2018

Table 8: Test Equipment List

TEST METHODS

Seasoning of SSL Product

For the purpose of rating new SSL products, SSL products shall be tested with no seasoning. Therefore, no seasoning was performed.

Sphere-Spectroradiometer Method- Photometric and Electrical Measurements

A Labsphere Model CDS 2100 Spectroradiometer and Two Meter Sphere was used to measure correlated color temperature, chromaticity coordinates, and the color rendering index for each SSL unit. The coating reflectance of each sphere is 98%. The measure geometry is 4π . Self-absorption correction is conducted in testing. Bandwidth of spectroradiometer is 350nm-1050nm.

Ambient temperature was measured at a position inside the sphere. Each SSL unit was operated on the client provided driver at the rated input voltage in its designated orientation.

The stabilization time typically ranges from 30 min (small integrated LED lamps) to 2 or more hours for large SSL luminaires). It can be judged that stability is reached when the variation (maximum – minimum) of at least 3 readings of the light output and electrical power over a period of 30 min, taken 15 minutes apart, is less than 0.5 %.

Electrical measurements including voltage, current, and power were measured using the Yokogawa Power Analyzer.

The standard reference of the integrated sphere system is halogen incandescent lamp, the intensity distribution type is omni-directional, and is traceable to the National Institute of Standards and Technology.

The uncertainty of integrating sphere system reported in this document is expanded uncertainty is 2.1% with a coverage factor $k=2$.

Goniophotometer Method

Photometric and Electrical Measurements

An EVERFINE Type C Model GO-R5000 Goniophotometer was used to measure the intensity at each angle of distribution for each sample. The photometric distance is 2.475m for near-field measurement or 30m for far-field measurement. Bandwidth of spectroradiometer is 380nm-780nm.

Ambient temperature was measured at the same height of the sample mounted on the Goniophotometer equipment. Each SSL unit was operated on the client provided driver at the rated input voltage in its designated orientation.

The stabilization time typically ranges from 30 min (small integrated LED lamps) to 2 or more hours for large SSL luminaires). It can be judged that stability is reached when the variation (maximum – minimum) of at least 3 readings of the light output and electrical power over a period of 30 min, taken 15 minutes apart, is less than 0.5 %.

Electrical measurements including voltage, current, and power were measured using the Everfine Digital Power Meter.

Some graphics were created with Photometric Plus software.

The standard reference of the Goniophotometer system is halogen incandescent lamp, the intensity distribution type is omni-directional, and is traceable to the National Institute of Metrology P.R. China.

The uncertainty of goniophotometer system reported in this document is expanded uncertainty is 2.3% with a coverage factor $k=2$.

Color Characteristics Measurements


The color characteristics of SSL products include chromaticity coordinates, correlated color temperature, and color rendering index. These characteristics of SSL products may be spatially non-uniform, and thus, in order that they can be specified accurately, the color quantities shall be measured as values that are spatially average, weighted to intensity, over the angular range where light is intentionally emitted from the SSL product. The color characteristics measurements are using gonio-spectroradiometer.

Color Spatial Uniformity

The characteristics of SSL products may be spatially non-uniform, the chromaticity coordinate shall be measured at two vertical planes ($C=0^\circ/180^\circ$ and $C=90^\circ/270^\circ$) and at 10° or less intervals for vertical angle until the light output dropped to below 10% of the peak intensity. The averaged weighted chromaticity coordinate

was calculated from these points. The data was then analyzed to check for delta color differences of the u' , v' chromaticity coordinates. The spatial non-uniformity of chromaticity, $\Delta u'v'$, is determined as the maximum deviation (distance on the CIE (u' , v') diagram) among all measured points from the spatially averaged chromaticity coordinate.

The geometry for the chromaticity measurement using gonio-spectroradiometer is shown as following.



*** End of Report ***

This report is considered invalidated without the Special Seal for Inspection of the LTL. This report shall not be altered, increased or deleted. The results shown in this test report refer only to the sample(s) tested. Without written approval of LTL, this test report shall not be copied except in full and published as advertisement.