



PHILIPS

dynalite 

User Interfaces  
EU

# Inspired design, **ultimate control**

Beautiful interface solutions with user friendly functionality for every interior

# Antumbra Series



The stunning Antumbra range has a surprising number of features, packaged in a choice of three designs that redefine the concept of minimalist chic. When you first encounter Antumbra, it detects your body's own electrical field and wakes up with a striking wall-wash lighting effect. With its array of inbuilt features, the Antumbra range offers an unparalleled balance of form and function.





The innovative use of **field effect technology** allows the keypad to automatically detect your presence by your body's own electrical field.

A **wall-wash lighting effect** is triggered when approached, to welcome interaction. The built-in light sensor detects ambient light levels and ensures the wall-wash effect activates at a comfortable brightness level.

Each keypad contains an **integrated temperature sensor**, allowing temperature monitoring at different locations throughout a building and obviating the need for third-party BMS or HVAC sensors and controls.



Designed in two halves, the communication and application modules enable the keypad **to be installed in two stages**, without the need for further programming when the fascia is installed.

Labeling for the Antumbra keypads is available in a **choice of Arabic, Chinese, English, Hebrew, Japanese and Korean** with font size options. An additional library of icons has been created to give a visual representation of button functions that transcends language barriers.

All indicators and sensors are completely hidden, giving a **smooth streamlined finish**.

A selection of rim and fascia finish options is available for each Antumbra keypad. These can be mixed and matched to suit.

# AntumbraButton



The AntumbraButton range has large mechanical buttons available in 2, 4 or 6 button variants. Different finish options are available for the fascia and rim of the keypad – all color options can be mixed and matched. Customized labeling of text and icons can be added.



Two-button



Four-button



Six-button

#### Corona fascia finishes



Magnesium



Silver



White

#### Flare fascia finishes



Aluminum



Gold



Noir (Black)



Prestige  
(Rose Gold)



Jet (Gray)




Vintage  
(Bronze)

#### Rim finishes




Aluminium



Chrome



Magnesium



White





**Antumbra**Display





The AntumbraDisplay features six buttons and a central LCD display to present multiple pages of functions and system information, including lighting scene or level, air conditioning, fan, current temperature and set-point. Different color finish options are available for the fascia and rim. Fascia and rim finishes can be mixed and matched.

#### Corona fascia finishes



Magnesium



Silver



White

#### Flare fascia finishes



Aluminum



Gold



Noir (Black)



Prestige  
(Rose Gold)



Jet (Gray)




Vintage  
(Bronze)

#### Rim finishes




Aluminium



Chrome



Magnesium



White



# AntumbraTouch



The AntumbraTouch range has a smooth glass finish and uses capacitive touch technology to detect finger pressure with no moving parts. Descriptive text and icon labeling describes functionality and is available in a range of languages.


## Fascia finishes



Magnesium



Silver



White

## Rim finishes




Aluminium



Chrome




Magnesium



White







# Antumbra Configurator

The Antumbra Configurator is a streamlined, intuitive design tool that helps you to customize the right Antumbra product for your project, both functionally and aesthetically. Build your perfect interface with no need to memorize complex part numbers or ordering codes.

Follow the Configurator's easy steps to select from the full variety of panel types, orientations, fascia/rim finishes, and button labeling options. When you are satisfied with your choices, you can download a PDF of your final design for easy inclusion in your purchase order.

[www.philips.com/antumbra](http://www.philips.com/antumbra)

# Revolution Series



The ultimate in choice and flexibility. Select from a vast range of standard plate finishes or custom finishes. Each button can be custom engraved with text or icons that help describe its functionality, and engraving is back-lit.



#### **Led indicators**

Display feedback of users current selection.

#### **Button sizes**

Single, double, and triple height buttons enhance configuration possibilities.

#### **Button engraving**

Buttons can be labeled to identify function or area, providing intuitive operation.

#### **Fascia options**

Suitable for an extensive range of materials providing unlimited décor matching possibilities.

#### **Back-lit buttons**

Improves keypad visibility in all lighting conditions.

#### **Custom features**

Optional features include key switches for unique control solutions.





## Standard options

(throughout range)

- The Revolution Series come in single or double column configurations
- Custom keypads can be created for any commercial or residential use and engraved to your specific requirements
- Button configurations are listed on page 21.


## Fascia finishes




Brushed  
Stainless  
Steel




Black  
Borosilicate  
Glass



White  
Optically  
Clear Starfire  
Glass



Polished  
Brass



White (Powder  
Coated Stainless)


## Button colors



Silver



Charcoal



White



# Classic Series

Contemporary styled stainless steel panels that are perfectly suited to any commercial or industrial environment.

Available in a wide range of standard options which include network sockets and key switches. Each plate and button cap can be custom engraved.

**Square button** silver caps with black bezel and black engraving.

High quality brushed stainless steel finish.

## Standard options

- Button configurations are listed on page 22.



**LED indicators** provide tactile and visual feedback.

Caps are easily removed for **engraving** for easy function identification.

**Robust keypads** are perfect for commercial and residential applications.

### Fascia finish



Brushed Stainless Steel

### Standard button color



Silver





# Standard Series

Anything but standard, beautifully formed and highly functional. Built with the full Philips Dynalite feature set, these simple yet elegant keypads bring the full power of the automated system to a touch of a button.



Smooth action buttons with LED indicators provide tactile and visual feedback and are easily removed for engraving.

Incorporates a miniature DyNet control network socket under the snap-on keypad cover, enabling system adjustments and programming from any user control keypad on the network.

Aesthetically pleasing, providing integrated automation in commercial buildings and homes.

Available in two configurations: single column, up to five buttons and a dual column design for up to ten buttons.







### Standard options

(throughout range)

- Two grid plates available, one or two columns (up to five or ten buttons)
- Smooth action switches with LED indicator
- Optional engraved buttons
- The button configurations are listed on page 22.

### DLPE fascia finish



Silver

### Button and Bezel color



Charcoal Gray





# Custom keypads

Build a custom keypad to meet your needs; choose from a multitude of button sizes, colors and layouts; key switches to lock-out unauthorized use, and network sockets for connection to the Dynalite lighting control and home automation network.

## Optional features

Vast range of optional features can be ordered, including displays, key switches, engraving and sockets for unique control solutions.

## Fascia finishes

Extensive range of materials providing unlimited décor matching possibilities.

## Button and fascia engraving


Clearly labeled button functions ensuring intuitive system operation.





# Color Touchscreen

The Dynalite Color Touchscreen adds a new dimension of control. The touchscreen supports a range of sensing features that provide end-users with the ultimate in automation system interaction. The screen interface can be customized to control all automation elements from one location.



## Fascia finish



Black Borosilicate Glass

Fascia color matches AntumbraTouch (black) and Revolution keypads.

## Touchscreen features:

- Intuitive controls
- Built-in time clock
- Temperature and humidity sensor
- Proximity sensor with halo response

Intuitive floor plans and sliders can be displayed for easy user navigation.



# Apps



The new Dynalite control app has a simple streamlined interface that delivers intuitive automated control into the hands of the end-user.

DynamicTouch offers a completely tailored solution for customers who want a unique and finely tuned bespoke user interface for their office or home.

EnvisionTouch comfortably exceeds most clients' smart home control requirements and runs on both Android and iOS.

#### **Other software user interface options.**

For small to medium businesses, the Philips Dynalite Ethernet Gateway provides a customizable browser based interface.

For larger enterprises, Philips Dynalite System Manager provides multi-user site-wide access.

## Dynalite control app


The new Philips Dynalite control app is available for iOS. It provides portable control of the Philips Dynalite system in both residential and commercial applications. Wrapped in a modern and intuitive user interface, this app allows users to manage scenes, control individual channels and apply schedules.

**Plug-and-play** – Connect the app to the Philips Dynalite system and it's ready to use.

**Scene management** – Recall and edit pre-defined lighting scenes and control individual lighting channels.

**Scene scheduling** – Trigger lighting scenes based on a schedule.

**Simple connection** – Connect to the PDEG – Philips Dynalite Ethernet Gateway, through your local Wi-Fi network.



iPhone with Dynalite Control  
– an intuitive automated control app.



## DynamicTouch

Available for Apple devices only.

Fully customizable app for home or commercial control.



iPhone with DynamicTouch  
– a totally customizable app.

## EnvisionTouch

Available in two versions: iOS for Apple devices; and Android.

Self-configuring application with standardized templates and functionality to speed up and simplify commissioning & installation processes.



Android phone with EnvisionTouch  
– a self configuring app.



# Ordering information

Technical information and product ordering codes for user interfaces and options are outlined in this section. Please contact your local Signify Representative or Distributor for more information and advice.



# Antumbra Series

## Ordering information

### PA6BPE-BC-X

#### Philips Antumbra

#### Button Only

6 = Six buttons  
4 = Four buttons  
2 = Two buttons

#### Panel Type

BP = Button Panel  
DP = Display Panel  
TP = Touch Panel

#### Shape

E = European  
A = American / Australian

#### Button Finish

##### Corona

(Button and Display only)

M = Magnesium  
S = Silver  
W = White

##### Glass

(Touch only)

B = Black  
S = Silver  
W = White

##### Flare

(Button and Display only)

A = Aluminum  
G = Gold  
J = Jet (Gray)

N = Noir (Black)

P = Prestige (Rose Gold)


V = Vintage (Bronze)

#### Rim Finish

A = Aluminum  
C = Chrome  
M = Magnesium  
W = White

#### Button Labeling

L = Labeling  
S = Standard labeling  
X = No labeling  
Not applicable to Antumbra Display



## Demo sales pack


A single box with application module, communications module and examples of labelling, rims, colors and finishes.

#### Ordering code

913703030609

PD-ADK-EU

Antumbra EU demo Kit



Antumbra Online Configurator Tool  
[www.philips.com/antumbra](http://www.philips.com/antumbra)

# Revolution Series

## Ordering information

#### Button color

White

Charcoal

Silver

#### Cover finish

Brushed Stainless Steel

Black Borosilicate Glass

White Optically Clear Starfire Glass

Polished Brass (Gold Plated Polished Stainless)


Antique Bronze

White (Powder Coated Stainless)

No Cover

## Dimensions

### DR2PE




## Button configurations



A



B



C



D




E




F



G




H




I




J



K



L



M


# Classic Series

## Ordering information

Ordering code	
913703200009	0 button, DyNet network socket
913703200309	1 button ON/OFF
913703200409	2 Button ON, OFF
913703200609	4 button preset 1-3, OFF
913703201809	6 button preset 1-4, ▲, ▼
913703201909	8 button preset 1-7, OFF
913703202209	8 button preset 1-7, OFF with keypad enable keyswitch
913703202109	8 button preset 1-4, ▲, ▼, OFF, PROGRAM, keyswitch and DyNet network socket
913703202509	8 button preset 1-4, ▲, ▼, OFF, PROGRAM
913703202609	8 button preset 1-4, ▲, ▼, OFF, PROGRAM, keyswitch
913703202909	10 button preset, 1-7, ▲, ▼, OFF
913703203009	12 button preset 1-11, OFF
913703203109	12 button preset 1-8, ▲, ▼, OFF, PROGRAM

## Dimensions

### DPNE-SF




# Standard Series

## Ordering information

Ordering code	
913703044909	1-button
913703045009	2-button
913703045109	5-button
913703045209	6-button
913703045309	7-button
913703045409	10-button

## Dimensions

### DLPE



# Color Touchscreen


## Ordering information

Ordering code

913703334309 Black Glass fascia


## Dimensions

### PDTS




## Dynalite Control, DynamicTouch & EnvisionTouch apps

If you have an iPhone, you can get the app from the app store. If you have an Android phone, you can get the app from the Play store.



Dynalite control  
App Store



DynamicTouch  
App Store



EnvisionTouch  
App Store



EnvisionTouch  
Play Store





[www.lighting.philips.com/dynalite](http://www.lighting.philips.com/dynalite)

© 2020 Signify Holding. All rights reserved.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent – or other industrial or intellectual property rights. Document order number: UIEU0112 Data subject to change.

UIEU0112-1020-AZZAUS-R2