



UVB Broadband TL – Fluorescent reliability in UV phototherapy

UVB Broadband TL

The UVB Broadband TL lamps emit radiation in the 'B' bandwidth of the UV spectrum (290 to 315 nm) and are therefore suitable for phototherapy systems designed to treat skin diseases such as psoriasis.

Avantages

- Photo-sensitizing agent - free treatment

Fonctions

- Emission range from 290-320 nm. Peak at 302 nm

Application

- Psoriasis

Mises en garde et sécurité


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

UVB Broadband TL

Versions



Schéma dimensionnel



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 40W/12 RS SLV/25	40,5 mm	1199,4 mm	1206,5 mm	1204,1 mm	1213,6 mm
TL 20W/12 RS SLV/25	40,5 mm	589,8 mm	596,9 mm	594,5 mm	604 mm

Renseignements généraux	
Culot	G13
Application principale	Systèmes de photothérapie
Description du système	Rapid Start (RS)
Données techniques sur l'éclairage	
Code de couleur	12
Désignation de couleur	Ultra Violet B
Mécanique et boîtier	
Forme de l'ampoule	T12

Fonctionnement et électricité

Order Code	Full Product Name	Courant de la lampe (nom.)	Tension (nom.)	Puissance (nominale) (nom.)
323238	TL 20W/12 RS SLV/25	0,37 A	59 V	19,3 W

Order Code	Full Product Name	Courant de la lampe (nom.)	Tension (nom.)	Puissance (nominale) (nom.)
323246	TL 40W/12 RS SLV/25	0,43 A	101 V	39 W

Renseignements généraux

Order Code	Full Product Name	Durée de vie jusqu'à 50% des défaillances (nom.)	Durée de vie utile (nom.)
323238	TL 20W/12 RS SLV/25	1000 h	1000 h

Order Code	Full Product Name	Durée de vie jusqu'à 50% des défaillances (nom.)	Durée de vie utile (nom.)
323246	TL 40W/12 RS SLV/25	9000 h	9000 h

UV

Order Code	Full Product Name	Rayonnement UV-B 5 h (CEI)	Rayonnement UV-B 100 h (CEI)
323238	TL 20W/12 RS SLV/25	2,4 W	2,3 W

Order Code	Full Product Name	Rayonnement UV-B 5 h (CEI)	Rayonnement UV-B 100 h (CEI)
323246	TL 40W/12 RS SLV/25	4,7 W	4,1 W

