



# MSR Gold™ SA Double Ended

## MSR Gold™ 575 SA/2 DE 1CT/40

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	SFC-11 [SFC-11]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	750 hour(s)
Light Technical	
Color Code	2
Luminous Flux	41,000 lm
Chromaticity Coordinate X (Nom)	294
Chromaticity Coordinate Y (Nom)	317
Correlated Color Temperature (Nom)	7500 K
Luminous Efficacy (rated) (Nom)	71 lm/W
Color rendering index (CRI)	70


Arc Length O (Nom)	5.0 mm
Operating and Electrical	
Power Consumption	575 W
Lamp Current (Nom)	7 A
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	MSR Gold 575 SA/2 DE 1CT/40
Full product name	MSR Gold™ 575 SA/2 DE 1CT/40
Full product code	872790091464100

MSR Gold™ SA Double Ended

Order code	91464100
Material Nr. (12NC)	928175105114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900914641


Numerator - Packs per outer box	40
EAN/UPC - Case	8727900914658

Dimensional drawing



Product	D (max)	O	A (min)	A (max)	A	C (max)
MSR Gold 575 SA/2 DE 1CT/40	18.5 mm	5.0 mm	69.6 mm	70.4 mm	70 mm	92 mm

Photometric data



Spectral Power Distribution Colour - MSR Gold 575 SA/2 DE 1CT/40

